

TAI-SAW TECHNOLOGY CO., LTD. No. 3, Industrial 2nd Rd., Ping-Chen Industrial District,

No. 3, Industrial 2nd Rd., Ping-Chen Industrial District, Taoyuan, 324, Taiwan, R.O.C. TEL: 886-3-4690038 FAX: 886-3-4697532

E-mail: tstsales@mail.taisaw.com Web: www.taisaw.com

Product Specifications Approval Sheet

Product Description: C	rystal Unit SMD	2.5x2.0 12.0MHz
TST Part No.: TZ2094	A	
Customer Part No.:		
Customer signature req	uired	
Company:		
Division:		
Approved by :		
Date:		
		V. (
Checked by:	Yifan Chen	litan
Approved by:	Kelly Huang	Kelly Huang
Date:	03/31/2014	7

- 1. Customer signed back is required before TST can proceed with sample build and receive orders.
- 2. Orders received without customer signed back will be regarded as agreement on the specifications.
- 3. Any specifications changes must be approved upon by both parties and a new revision of specifications shall be released to reflect the changes.



TAI-SAW TECHNOLOGY CO., LTD. Crystal Unit SMD 2.5x2.0 12.0MHz

MODEL NO.: TZ2094A REV. NO.: 1

Revise:

Rev.	Rev. Page	Rev. Account	Date	Ref. No.	Revised by
1	N/A	Initial release	03/31/14'	N/A	Yifan Chen



MODEL NO.: TZ2094A REV. NO.: 1

Features:

- Surface Mount Hermetic Package
- Excellent Reliability Performance
- Good Frequency Perturbation and Stability over temperature
- Ultra Miniature Package

RoHS Compliant Lead free Lead-free soldering

Description and Applications:


Surface mount 2.5mmx2.0mm crystal unit for use in wireless communications devices, especially for a need of ultra miniature package for mobility.

Electrical Specifications:


TZ2094A	Specification
Nominal Frequency	12.000000 MHz
Mode of Oscillation	Fundamental
Storage Temperature Range	-40°C to +125°C
Operating Temperature Range	-30°C to +85°C
Frequency Stability over Operating Temperature Range	+/-15 ppm (referred to the value at 25°C)
Frequency Make Tolerance (FL)	+/-10 ppm @ 25°C +/- 3°C
Equivalent Series Resistance (ESR)	180 Ω max
Nominal Drive Level	10uW typical and 100uW max
Shunt Capacitance (Co)	3.0 pF max
Load Capacitance (CL)	12 pF
Insulation Resistance	500 MΩ min./DC 100V
Aging	+/-1ppm
Marking	Laser Marking
Unit Weight	9.5 +/-0.5mg


Mechanical Dimensions (mm):

Base 1





	Pin Connection
#1 pin	IN/OUT
#2 pin	GND
#3 pin	IN/OUT
#4 pin	GND






Base 2






Recommended Land Pattern: (unit: mm)




Marking:

Line 1: Frequency (12.0)

Line 2: TST Logo + Date Code + Product Code (\square is TST internal tracking code, could be a~z and A~Z)




The inner vision of PIN#1,PIN#4 side is XTAL blank mounting pad.



Product Code Table: (Under line With Even Year and Odd Year for Nothing)

Year				Product Code		
2013	2015	2017	2019	2021	2023	
2014	2016	2018	2020	2022	2024	


Reel Dimensions (mm):



TAI-SAW TECHNOLOGY CO., LTD.

TST DCCRelease document

Tape Dimensions (mm):




[NOTE]:


- 1. Unless otherwise specified tolerance on dimension +/-0.1 mm.
- 2. Material: conductive polystyrene with color black.
- 3. 10 pitch cumulative tolerance +/-0.2 mm.

Packing Quantity/Packing:

3K pcs maximum per reel



Reflow Profile:



Note: 1.Max peak temperature: 260+/-5 deg C; Time: 10+/-2 sec

2. Temperature: 217+/-5 deg C; Time: 90~100 sec

Reliability Specifications

Test name	Test process / method	Reference standard			
Mechanical c	Mechanical characteristics				
resistance to Soldering heat (IR reflow)	Temp./ Duration: 260°C /10sec x2 times Total time: 4min.(IR-reflow)	-300(301)M(II)			
Vibration	Total peak amplitude : 1.5mm Vibration frequency : 10 to 55 Hz Sweep period : 1.0 minute Vibration directions : 3 mutually perpendicular Duration : 2 hr / direc.	MIL-STD 202F method 201A			
Mechanical Shock	directions : 3 impacts per axis Acceleration : 3000g's, +20/-0 % Duration : 0.3 ms (total 18 shocks) Waveform : Half-sine	MIL-STD 202F method 213C			
Solderability	Solder Temperature:265±5°C Duration time: 5±0.5 seconds.	MIL-STD 883G method 2003			
Environmenta	l characteristics	•			
Thermal Shock	Heat cycle conditions -55 °C (30min) ←→ 125 °C (30min) * cycle time : 10 times	MIL-STD 883G method 1010.7			
Humidity test	Temperature : 70 ± 2 °C Relative humidity : 90~95% Duration : 96 hours	MIL-STD 202F method 103B			
Dry heat (Aging test)	Temperature : 125 ± 2 °C Duration : 168 hours	MIL-STD 883G method 1008.2 condition C			
PCT test	Pressure: 2.06kg/cm ² (2.03*10 ⁵ pa) Temperature : 121 ± 2 °C Relative humidity : 100% Duration : 24 hours	EIAJED-4701-3 B-123A			