

1A, 20V - 150V Schottky Barrier Surface Mount Rectifier

FEATURES


- AEC-Q101 qualified
- Low power loss, high efficiency
- Ideal for automated placement
- Guard ring for overvoltage protection
- High surge current capability
- Moisture sensitivity level: level 1, per J-STD-020
- RoHS Compliant
- Halogen-free according to IEC 61249-2-21

APPLICATIONS

- Low voltage, high freq. inverter
- DC/DC converter
- Freewheeling diodes
- Reverse battery protection
- Car lighting

MECHANICAL DATA

- Case: DO-214AC (SMA)
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 2 whisker test
- · Polarity: Indicated by cathode band
- Weight: 0.060g (approximately)









DO-214AC (SMA)



PARAMETER	SYMBOL	SS	SS	SS	SS	SS	SS	SS	SS	UNIT
		12H	13H	14H	15H	16H	19H	110H	115H	ļ
Marking code on the device		SS12	SS13	SS14	SS15	SS16	SS19	SS110	SS115	
Repetitive peak reverse voltage	V_{RRM}	20	30	40	50	60	90	100	150	V
Reverse voltage, total rms value	V _{R(RMS)}	14	21	28	35	42	63	70	105	V
Forward current	I _F	1			Α					
Peak forward surge current, 8.3ms single half sine-wave superimposed on rated load	I _{FSM}	40			А					
Critical rate of rise of off- state voltage	dV/dt	10,000			V/µs					
Junction temperature	TJ	- 55 to +125 - 55 to +150			°C					
Storage temperature	T _{STG}	- 55 to +150			°C					

1



THERMAL PERFORMANCE					
PARAMETER	SYMBOL	ТҮР	UNIT		
Junction-to-lead thermal resistance	$R_{\Theta JL}$	28	°C/W		
Junction-to-ambient thermal resistance	$R_{\Theta JA}$	88	°C/W		

PARAMETER		CONDITIONS	SYMBOL	TYP	MAX	UNIT
	SS12H SS13H SS14H	I _F = 1A, T _J = 25°C	V	-	0.50	V
	SS15H SS16H			-	0.75	V
	SS19H SS110H			-	0.80	V
Forward voltage ⁽¹⁾	SS115H			-	0.95	V
rorward voltage	SS12H SS13H SS14H	I _F = 1A, T _J = 100°C	- V _F	-	0.40	V
	SS15H SS16H			-	0.65	V
	SS19H SS110H			-	0.70	V
	SS115H			-	0.85	V
	SS12H SS13H SS14H SS15H SS16H	T _J = 25°C	- _R	-	0.2	mA
	SS19H SS110H SS115H			-	0.1	mA
	SS12H SS13H SS14H	T _J = 100°C		-	6	mA
Reverse current @ rated $V_R^{(2)}$	SS15H SS16H			-	5	mA
	SS19H SS110H SS115H			-	-	mA
	SS12H SS13H SS14H	T _J = 125°C		-	-	mA
	SS15H SS16H			-	-	mA
	SS19H SS110H SS115H			-	2	mA

Notes:

- 1. Pulse test with PW = 0.3ms
- 2. Pulse test with PW = 30ms



ORDERING INFORMATION				
ORDERING CODE ⁽¹⁾	PACKAGE	PACKING		
SS1xH	DO-214AC (SMA)	7,500 / Tape & Reel		

Notes:

1. "x" defines voltage from 20V(SS12H) to 150V(SS115H)



CHARACTERISTICS CURVES

 $(T_A = 25^{\circ}C \text{ unless otherwise noted})$

Fig.1 Forward Current Derating Curve




Fig.3 Typical Reverse Characteristics





Fig.2 Typical Junction Capacitance

Fig.4 Typical Forward Characteristics







Fig.5 Maximum Non-Repetitive Forward Surge Current






CHARACTERISTICS CURVES

 $(T_A = 25^{\circ}C \text{ unless otherwise noted})$

Fig.6 Typical Transient Thermal Characteristics









PACKAGE OUTLINE DIMENSIONS


DO-214AC (SMA)





DIM. Unit		(mm)	Unit ((inch)
Dilvi.	Min.	Max.	Min.	Max.
Α	1.99	2.50	0.078	0.098
A1	0.10	0.20	0.004	0.008
b	1.27	1.58	0.050	0.062
С	0.15	0.31	0.006	0.012
D	2.29	2.83	0.090	0.111
E	4.95	5.33	0.195	0.210
E1	4.06	4.60	0.160	0.181
L	0.90	1.41	0.035	0.056

SUGGESTED PAD LAYOUT



Symbol	Unit (mm)	Unit (inch)
Α	1.68	0.066
В	1.52	0.060
С	3.93	0.155
D	2.41	0.095
E	5.45	0.215

MARKING DIAGRAM



= Marking Code P/N G = Green Compound

= Date Code ΥW F = Factory Code



Taiwan Semiconductor

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.