



DGD0211C

1.5A HIGH SPEED SINGLE GATE DRIVER

Description


The DGD0211C single high speed / low side MOSFET and IGBT driver is capable of driving 1.9A of peak current. The DGD0211C logic inputs are compatible with standard TTL and CMOS levels (down to 3.3V) to interface easily with MCUs. The DGD0211C provides non-inverting and inverting inputs.

Because of fast propagation times of 35ns typical and rise/fall times of 15ns typical, the DGD0211C is well suited for high speed applications like switch mode power supplies and PFC circuits.

The DGD0211C is offered in TSOT25 package and the operating temperature extends from -40°C to +125°C.

Applications

- DC-DC Converters
- Line Drivers
- Motor Controls
- Switch Mode Power Supplies



Typical Configuration

Ordering Information (Note 4)

Part Number	Marking	Reel Size (inches)	Tape Width (mm)	Quantity Per Reel
DGD0211CWT-7	D0211C	7	8	3,000

No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free

3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

Marking Information

Notes:



D0211C = Product Type Marking Code YY = Year (ex: 20 = 2020) WW = Week (01 to 53)

Features

- Efficient Low Cost Solution for Driving MOSFETs and IGBTs
- Wide Supply Voltage Operating Range: 4.5V to 18V
- 1.9A Source / 1.8A Sink Output Current Capability
- Non-Inverting and Inverting Input Configuration
- Fast Propagation Delay (35ns Typ)
- Fast Rise and Fall Times (15ns Typ)
- Logic Input (IN, IN*) 3.3V Capability
- Extended Temperature Range: -40°C to +125°C
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please <u>contact us</u> or your local Diodes representative. <u>https://www.diodes.com/quality/product-definitions/</u>

Mechanical Data

- Case: TSOT25 (Type TH)
- Case Material: Molded Plastic. "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 3 per J-STD-020
- Terminals: Finish Matte Tin Plated Leads. Solderable per MIL-STD-202, Method 208⁽²³⁾
- Weight: 0.012 grams (Approximate)




TSOT25

^{4.} For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.




Pin Diagrams



Pin Descriptions

Pin Number	Pin Name	Function
1	Vcc	Supply Input
2	COM	Supply Return
3	IN	Non-Inverting Logic Input, see Input/Output Response Table (Connect to Vcc to Enable Output)
4	IN*	Inverting Logic Input, see Input/Output Response Table (Connect to COM to Enable Output)
5	OUT	Gate Drive Output

Functional Block Diagrams





Absolute Maximum Ratings (@TA = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Low-Side Fixed Supply Voltage	Vcc	-0.3 to +22	V
Output Voltage (OUT)	Vout	-0.3 to Vcc+0.3	V
Logic Input Voltage (IN, IN*)	Vin	-0.3 to Vcc+0.3	V

Thermal Characteristics (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Power Dissipation Linear Derating Factor (Note 5)	PD	0.54	W
Thermal Resistance, Junction to Ambient (Note 5)	Reja	188	°C/W
Operating Temperature	TJ	+150	
Lead Temperature (Soldering, 10s)	TL	+300	°C
Storage Temperature Range	Tstg	-55 to +150	

Note: 5. When mounted on a standard JEDEC 2-layer FR-4 board.

Recommended Operating Conditions

Parameter	Symbol	Min	Max	Unit
Supply Voltage	VB	4.5	18	V
Output Voltage (OUT)	Vs	0	Vcc	V
Logic Input Voltage (IN, IN*)	Vin	0	5	V
Ambient Temperature	T _A	-40	+125	°C



DC Electrical Characteristics (VBIAS (VCC, VBS) = 12V, @TA = +25°C, unless otherwise specified.) (Note 6)

Parameter	Symbol	Min	Тур	Max	Unit	Conditions
Logic "1" Input Voltage	VIH	2.4	1.6	_	V	—
Logic "0" Input Voltage	VIL	—	1.3	0.8	V	—
Logic "1" Input Bias Current	I _{IN+}	—	_	5	μA	$V_{IN} = 3V, V_{IN^*} = 0V$
Logic "0" Input Bias Current	lin-	—	—	2	μA	$V_{IN} = 0V, V_{IN^*} = 3V$
High Level Output Voltage, VBIAS - Vo	Voн	—	25	-	mV	—
Low Level Output Voltage	V _{OL}	—	25		mV	—
Quiescent Vcc Supply Current	lccq	—	50	100	μA	VIN = 0V or 3V
Output High Short Circuit Pulsed Current	Io+	—	1.9	_	Α	—
Output Low Short Circuit Pulsed Current	lo-	—	1.8	—	Α	—
Output Reverse Current Withstand	Irvs	—	250	_	mA	—


Note: 6. The V_{IN} and I_{IN} parameters are applicable to the logic input pin: IN and IN^{*}. The V_0 and I_0 parameters are applicable to the output pin: OUT.

AC Electrical Characteristics (V_{CC} = 12V, @T_A = +25°C, unless otherwise specified.)

Parameter	Symbol	Min	Тур	Max	Unit	Conditions
Turn-On Rise Time	tr		15	25	ns	CL = 1000pF
Turn-Off Fall Time	tf	_	15	25	ns	CL = 1000pF
Turn-On Propagation Delay	ton	_	35	50	ns	—
Turn-Off Propagation Delay	toff	_	35	55	ns	—



Timing Waveforms





Input/Output Response Table

IN	IN*	OUT
0	0	0
0	1	0
1	0	1
1	1	0



Typical Performance Characteristics (V_{CC} = 12V, @T_A = +25°C, unless otherwise specified.)




Figure 2. Turn-on Propagation Delay vs. Supply Voltage




Figure 4. Turn-off Propagation Delay vs. Supply Voltage




Figure 6. Rise Time vs. Supply Voltage




Figure 3. Turn-on Propagation Delay vs. Temperature




Figure 5. Turn-off Propagation Delay vs. Temperature





Figure 7. Rise Time vs. Temperature



Typical Performance Characteristics (continued)






Figure 10. Quiescent Current vs. Supply Voltage




Figure 12. Output Source Current vs. Supply Voltage







Figure 9. Fall Time vs. Temperature







Typical Performance Characteristics (continued)








Figure 16. Logic 1 Input Voltage vs. Supply Voltage





Figure 18. Logic 0 Input Voltage vs. Supply Voltage






Figure 17. Logic 1 Input Voltage vs. Temperature





Figure 19. Logic 0 Input Voltage vs. Temperature



Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.




TSOT25 (Type TH)					
Dim	Min	Max	/ Тур		
Α		1.10			
A1	0.01	0.10			
A2	0.70	1.00	0.90		
b	0.30	0.50			
С	0.08	0.20			
D	2.90 BSC				
E	2.80 BSC				
E1	1.60 BSC				
е	0.95 BSC				
e1	1.90 BSC				
L1	0.60 REF				
All Di	imensi	ons in n	nm		

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

TSOT25 (Type TH)

TSOT25 (Type TH)



Dimensions	Value (in mm)
С	0.950
Х	0.700
Y	1.000
Y1	3.199

E1



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2020, Diodes Incorporated

www.diodes.com