



Transmittal, reproduction, dissemination and/or editing of this document as well as utilization of its contents and communication thereof to others without express authorization are prohibited.

未经允许禁止传输、复制、编辑该文档，以及利用其内容进行交流

REVISION RECORD			
REV	CN	DESCRIPTION	DATE



General information:

1. Dimension shall be interpreted per ASME Y14.5-2009
2. Operating temperature: -40° C~+105° C
3. RoHS Compliance
4. Undimensioned Tolerances:

Pitch Range mm	In mm		Nominal Dimension		Range		Tolerance				
	Over	TO	Over	TO	Over	TO					
6	10	TO	30	60	100	150	0.1/0				
10	24	TO	30	60	100	150	<				
±0.15		±0.20		±0.30		±0.50		±0.70	±1.00	±1.30	±2°

Material:

Insulator	PAG6	UI 94 V-0
Snop pin	STEEL	

订货号 Order No.	21E203	名称 Name	21E203固定器	未注公差 Tolerance	表面 Surface
项目 Item	签字 Signature	图号 Drawing No.	Notes	公差表 Tolerances Table	VDI21
设计 Design	徐骏 Signature	材料 Material		版本号 Revision Number	重量 Weight
审核 Check	程治 Signature	物料号 Item No.	411851003	M1	比例 Scale
工艺 Check	-				1:1
标准化 Unity	-				mm
批准 Approve	马晓轩 Signature				
	日期 Date				
	12/21/21"				

第1页/共1页 1 of 1  
SUPU 宁波舜普电子有限公司  
NINGBO SUPU ELECTRONICS CO.,LTD.