



**RoHS**  
COMPLIANT



### Surface Mount Fast Recovery Rectifiers

Reverse Voltage - 50 to 1000 V

Forward Current - 1 A

#### FEATURES

- For surface mounted applications
- Low profile package
- Glass Passivated Chip Junction
- Easy to pick and place
- Fast reverse recovery time
- Lead free in comply with EU RoHS 2011/65/EU directives

#### MECHANICAL DATA

- Case: SOD-123FL
- Terminals: Solderable per MIL-STD-750, Method 2026
- Approx. Weight: 15mg 0.00053oz

#### PINNING

PIN	DESCRIPTION
1	Cathode
2	Anode



Simplified outline SOD-123FL and symbol

#### Absolute Maximum Ratings and Characteristics

Ratings at 25 °C ambient temperature unless otherwise specified. Single phase, half wave, 60 Hz, resistive or inductive load. For capacitive load, derate current by 20%.






Parameter	Symbols	F1	F2	F3	F4	F5	F6	F7	Units		
Maximum Repetitive Peak Reverse Voltage	V <sub>RRM</sub>	50	100	200	400	600	800	1000	V		
Maximum RMS voltage	V <sub>RMS</sub>	35	70	140	280	420	560	700	V		
Maximum DC Blocking Voltage	V <sub>DC</sub>	50	100	200	400	600	800	1000	V		
Maximum Average Forward Rectified Current at T <sub>c</sub> = 125 °C	I <sub>F(AV)</sub>	1						A			
Peak Forward Surge Current 8.3 ms Single Half Sine Wave Superimposed on Rated Load	I <sub>FSM</sub>	30						A			
Maximum Forward Voltage at 1 A	V <sub>F</sub>	1.3						V			
Maximum DC Reverse Current T <sub>a</sub> = 25 °C at Rated DC Blocking Voltage T <sub>a</sub> = 125 °C	I <sub>R</sub>	5 100						μA			
Typical Junction Capacitance at V <sub>R</sub> =4V, f=1MHz	C <sub>j</sub>	15						pF			
Maximum Reverse Recovery Time <sup>(1)</sup>	t <sub>rr</sub>	150			250	500		ns			
Typical Thermal Resistance <sup>(2)</sup>	R <sub>θJA</sub>	85						°C/W			
Operating and Storage Temperature Range	T <sub>j</sub> , T <sub>stg</sub>	-55 ~ +150						°C			

( 1 ) Measured with I<sub>F</sub> = 0.5 A, I<sub>R</sub> = 1 A, I<sub>rr</sub> = 0.25 A.

( 2 ) P.C.B. mounted with 2.0" X 2.0" (5 X 5 cm) copper pad areas.



**RoHS**  
COMPLIANT






**RoHS**  
COMPLIANT



## PACKAGE OUTLINE


Plastic surface mounted package; 2 leads

SOD-123FL



UNIT		A	C	D	E	e	g	H <sub>E</sub>	<
mm	max	1.15	0.20	2.9	1.9	1.2	0.9	3.8	$5^\circ$
	min	0.95	0.12	2.6	1.7	0.9	0.7	3.5	
mil	max	45	7.9	114	75	47	35	150	$5^\circ$
	min	37	4.7	102	67	35	28	138	

The recommended mounting pad size



Marking

Type number	Marking code
FR101W	F1
FR102W	F2
FR103W	F3
FR104W	F4
FR105W	F5
FR106W	F7
FR107W	