


MODEL

NHE520FSR



Features

This is a high sensitivity type of Nicera Hall element using evaporated InSb film.
 It performs effectively in low magnetic fields due to the high sensitivity.
 The input and output resistance values are suitable for transistor circuits.

Applications

- Brushless motors
- DVD drive, CD-ROM drive, floppy disk drive
- Other small precision motors
- Non-contacting magnetic sensors
- Position sensors, rotation sensors, current sensors
- Magnetic flux sensors other than those above

Specification


◆ Halogen free products ◆

Nicera supply halogen free products.

For these products, "HF" is put at the end of model names as below,

NHE520FSR-HF

◆ Dimensional Drawing ◆



◆ Absolute Maximum Ratings ◆

| Item | Symbol | Limit | Unit |
|-----------------------|------------------|------------|------|
| Max. Input Current | I _{cm} | 20(at25°C) | mA |
| Operating Temp. Range | T _{opr} | -40~110 | °C |
| Storage Temp. Range | T _{stg} | -40~125 | °C |

◆ Electrical Characteristics (T=25°C) ◆

| Item | Symbol | Conditions | Min. | Typ. | Max. | Unit |
|--------------------------------------|-------------------|---|------|------|------|------|
| Output Voltage | V _H | V _c =1V B=50mT | 168 | | 428 | mV |
| Offset Voltage | V _o | V _c =1V B=0mT | -7 | | 7 | mV |
| Input Resistance | R _{in} | I=1mA | 240 | | 550 | Ω |
| Output Resistance | R _{out} | I=1mA | 240 | | 550 | Ω |
| Temp. Coefficient of V _H | ※1 α _H | Standard 20°C Average 0~40°C B=50mT I _c =5mA | | -1.8 | | %/°C |
| Temp. Coefficient of R _{in} | ※2 α _R | B=0mT I _c =0.1mA | | -1.8 | | %/°C |

※1: $\alpha_H = [1/V_H(T_1)] \times [(V_H(T_3) - V_H(T_2)) / (T_3 - T_2)] \times 100$

※2: $\alpha_R = [1/R_{in}(T_1)] \times [(R_{in}(T_3) - R_{in}(T_2)) / (T_3 - T_2)] \times 100$

T₁=20°C, T₂=0°C, T₃=40°C

◆ Classification of Output Voltage I ◆

| Model | Rank | V _H (mV) | Conditions |
|-----------|---------|---------------------|---|
| NHE520FSR | 4* | 168~204 | Constant Voltage Drive V _H =V _H M-V _o V _H M=Measured Hall Voltage (at 50mT) V _o =Offset Voltage(at 0 mT) |
| | 5 | 196~236 | |
| | 6 | 228~274 | |
| | 7 | 266~320 | |
| | 8 | 310~370 | |
| 9* | 360~428 | | |

* Rank 4&9 need to be discussed individually, according to the production condition.

Please contact us for the details.

◆ Packaging ◆

| Model | Packaging | Reel Max. (pcs) | Carton Max. (pcs) |
|-----------|-------------|-----------------|-------------------|
| NHE520FSR | Taping reel | 3,000 | 72,000 |

◆ Characteristics Curve ◆

