

2.4GHz 8010 Chip Antenna: ANT8010R24003KM1

Applications:

WLAN, 802.11b/g, Bluetooth, etc...

Features

SMD, high reliability, ultra compact, Omni-directional...



Part number

ANT 8010 R 2400 3K M1
 (1) (2) (3) (4) (5)


(1) Size Code	8.0x1.0mm
(2) Packing	Tape and reel
(3) Frequency	2.4GHz
(4) Packing Number	3K
(5) Code	M1

Electrical Specification

Working Frequency Range	2400 ~2484 MHz
Peak Gain	1.5 dBi (Typ.)
Impedance	50 Ohm
VSWR	2.5 (Max)
Polarization	Linear
Azimuth Beamwidth	Omni-directional
Operation Temperature(°C)	-40~85

The specification is defined on EVB.

Dimension and Terminal Configuration




Dimension (mm)	
L	8.10±0.15
W	1.00±0.15
T	1.00±0.10
D1	0.40±0.15
D2	0.40±0.15


No.	Terminal Name
1	Feeding
2	Soldering

Evaluation Board Reference

PCB Dimension



Antenna Layout Reference





- Unit : mm
- : Chip Antenna
- : Land Pattern

2.4GHz 8010 Chip Antenna: ANT8010R24003KM1


Electrical Characteristics

Return Loss & Radiation


VSWR&Efficiency






Radiation Pattern






ZX-Plane



ZY-Plane



XY-Plane




2.4GHz 8010 Chip Antenna: ANT8010R24003KM1

Taping Specifications


Reel and Taping Specification

Reel Specification



TYPE	SIZE		A	φB	φC	φD	W	φM
8010	7"	3K/Reel	5.5±0.5	13.5±1.0	16.5±1.0	55±1.0	18.5±2.0	178±2.0


Taping Specification



Packaging	Type	A	B	W	E	F	G	H	T	φD	P
Paper Type	8010	1.30±0.20	8.30±0.20	16.0±0.20	1.50±0.10	7.5±0.10	3.85±0.10	1.65±0.05	1.5±0.10	1.50 +0.10 -0	4.0±0.1

Recommended Reflow Profile

Pb free solder



Soaking		Working		Soldering		Peak	
Temp.	Time	Temp.	Time	Temp.	Time	Temp.	
T1	T2	t1	T3	t2	T4	t3	T5
150°C	180°C	60 to 120sec	230°C	more than 30sec	247 to 253°C	within 10sec	260°C Max.

March 2021 Ver.H01