

SMD Wire Wound Common Mode Filters---SCM Series



Feature

- Compact Size
- High impedance but very high rated current and low RDC.
- Wide impedance range for EMI suppression
- RoHS compliant.
- Operating temperature range $-40^{\circ}\text{C} \sim 125^{\circ}\text{C}$.

Application


- EMI suppression for Power lines.
- Communications, Computers, Noise suppression, etc.
- CAN BUS.

Production identification

$\frac{\text{SCM}}{\text{①}}$ $\frac{\text{7060}}{\text{②}}$ - $\frac{\text{701}}{\text{③}}$ $\frac{\text{T}}{\text{④}}$

- ① Series name: SMD Common Mode Choke
- ② Size: $7.0 \times 6.0 \times 3.8\text{mm}$
- ③ Impedance: 700Ω
- ④ Taping Code

Series Shape and Dimensions (Unit:mm)



Series	A	B	C _{Max}	D _{Typ}	E _{Typ}	F _{Typ}	G _{Typ}	a	b	c	d	SPQ
SCM7060	7.0 ± 0.5	6.0 ± 0.5	3.8	3.5	1.5	1.5	1.75	2.2	1.5	2.5	1.5	1500
SCM9070	9.0 ± 0.5	7.0 ± 0.5	4.8	5.7	1.5	2.0	1.70	3.0	1.75	5.0	1.5	1500
SCM1211	12.0 ± 0.5	10.8 ± 0.5	6.4	7.0	2.7	2.5	2.5	2.7	2.9	6.8	2.3	1000

Electrical Characteristics

Part Number	Impedance@100 MHz(Ω)		Rated Voltage Max(Vdc)	Insulation Resistance Min(M Ω)	DC Resistance Max(m Ω)	Rated Current Max(A)
	Min	Typ				
SCM7060-301T	225	300	80	10	10.0	5.0
SCM7060-701T	500	700	80	10	15.0	4.0
SCM7060-102T	800	1020	80	10	17.0	3.0
SCM7060-132T	910	1300	80	10	21.0	2.5

SMD Wire Wound Common Mode Filters---SCM Series



Electrical Characteristics

Part Number	Impedance@100 MHz(Ω)		Rated Voltage Max(Vdc)	Insulation Resistance Min(M Ω)	DC Resistance Max(m Ω)	Rated Current Max(A)
	Min	Typ				
SCM9070-701T	500	700	50	10	10.0	5.0
SCM9070-102T	750	1000	50	10	13.0	4.0
SCM1211-701T	500	700	125	10	6.0	8.0
SCM1211-102T	750	1000	125	10	14.0	6.0

Typical Impedance vs. Frequency Curves

