

Vishay General Semiconductor

# Surface-Mount TMBS<sup>®</sup> (Trench MOS Barrier Schottky) Rectifier



SMA (DO-214AC)

Cathode O Anode

### **ADDITIONAL RESOURCES**



PRIMARY CHARACTERISTICS			
I <sub>F(AV)</sub>	2.0 A		
V <sub>RRM</sub>	100 V		
I <sub>FSM</sub>	60 A		
$V_F$ at $I_F$ = 2.0 A	0.56 V		
T <sub>J</sub> max.	150 °C		
Package	SMA (DO-214AC)		
Circuit configuration	Single		

## FEATURES

- Low profile package
- Ideal for automated placement
- Trench MOS Schottky technology
- Low power losses, high efficiency
- Low forward voltage drop
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- AEC-Q101 qualified available
  Automotive ordering code; base P/NHM3
- Material categorization: for definitions of compliance please see <u>www.vishay.com/doc?99912</u>

## **TYPICAL APPLICATIONS**

For use in low voltage, high frequency inverters, freewheeling, DC/DC converters, and polarity protection applications.

### **MECHANICAL DATA**

Case: SMA (DO-214AC)

Molding compound meets UL 94 V-0 flammability rating Base P/N-M3 - halogen-free, RoHS-compliant, and commercial grade

Base P/NHM3\_X - halogen-free, RoHS-compliant and AEC-Q101 qualified

("\_X" denotes revision code e.g. A, B,....)

**Terminals:** matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

M3 suffix meets JESD 201 class 2 whisker test, HM3 suffix meets JESD 201 class 2 whisker test

Polarity: color band denotes the cathode end

<b>MAXIMUM RATINGS</b> ( $T_A = 25 \text{ °C}$ unless otherwise noted)				
PARAMETER	SYMBOL	VSSA210	UNIT	
Device marking code		V2B		
Maximum repetitive peak reverse voltage	V <sub>RRM</sub>	100	V	
Maximum DC forward current	I <sub>F</sub> <sup>(1)</sup>	2.0	- A	
	I <sub>F</sub> <sup>(2)</sup>	1.7		
Peak forward surge current 10 ms single half sine-wave superimposed on rated load	I <sub>FSM</sub> 60		A	
Operating junction and storage temperature range	T <sub>J</sub> , T <sub>STG</sub>	-40 to +150	°C	

#### Notes

<sup>(1)</sup> Mounted on 8 mm x 8 mm pad areas, 1 oz. FR4 PCB

<sup>(2)</sup> Free air, mounted on recommended copper pad area

For technical questions within your region: <u>DiodesAmericas@vishay.com</u>, <u>DiodesAsia@vishay.com</u>, <u>DiodesEurope@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>





**VSSA210** 



## Vishay General Semiconductor

<b>ELECTRICAL CHARACTERISTICS</b> ( $T_A = 25$ °C unless otherwise noted)						
PARAMETER	TEST CONDITIONS		SYMBOL	TYP.	MAX.	UNIT
Instantaneous forward voltage	I <sub>F</sub> = 2.0 A	T <sub>A</sub> = 25 °C	V <sub>F</sub> <sup>(1)</sup>	0.61	0.70	V
		T <sub>A</sub> = 125 °C	VF \''	0.56	0.65	
Reverse current	V <sub>R</sub> = 70 V	T <sub>A</sub> = 25 °C	I <sub>R</sub> <sup>(2)</sup>	1.0	-	μA
		T <sub>A</sub> = 125 °C		0.95	-	mA
	$V_{\rm P} = 100 \text{ V}$	T <sub>A</sub> = 25 °C		3.5	150	μA
		T <sub>A</sub> = 125 °C		2.2	15	mA
Typical junction capacitance	4.0 V, 1 MHz		CJ	175	-	pF

#### Notes

 $^{(1)}\,$  Pulse test: 300  $\mu s$  pulse width, 1 % duty cycle

<sup>(2)</sup> Pulse test: Pulse width  $\leq$  40 ms

<b>THERMAL CHARACTERISTICS</b> ( $T_A = 25 \text{ °C}$ unless otherwise noted)				
PARAMETER	SYMBOL	VSSA210	UNIT	
Typical thermal resistance	R <sub>0JA</sub> <sup>(1)</sup>	135	°C/W	
	R <sub>0JM</sub> <sup>(2)</sup>	25	C/ W	

#### Notes

<sup>(1)</sup> Free air, mounted on recommended PCB 1 oz. pad area; thermal resistance  $R_{\theta JA}$  - junction to ambient

 $^{(2)}$  Units mounted on PCB with 8 mm x 8 mm copper pad areas;  $R_{\theta JM}$  - junction to mount

ORDERING INFORMATION (Example)					
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE	
VSSA210-M3/61T	0.064	61T	1800	7" diameter plastic tape and reel	
VSSA210-M3/5AT	0.064	5AT	7500	13" diameter plastic tape and reel	
VSSA210HM3_A/H (1)	0.064	Н	1800	7" diameter plastic tape and reel	
VSSA210HM3_A/I <sup>(1)</sup>	0.064		7500	13" diameter plastic tape and reel	

#### Note

(1) AEC-Q101 qualified

## **RATINGS AND CHARACTERISTICS CURVES** ( $T_A = 25$ °C unless otherwise noted)




Fig. 1 - Maximum Forward Current Derating Curve




Fig. 2 - Forward Power Loss Characteristics


Revision: 27-Feb-2020

2

Document Number: 89404

For technical questions within your region: <u>DiodesAmericas@vishay.com</u>, <u>DiodesAsia@vishay.com</u>, <u>DiodesEurope@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>

## Vishay General Semiconductor



www.vishay.com

SHAY







Fig. 4 - Typical Reverse Characteristics






Mounting Pad Layout





Document Number: 89404

For technical questions within your region: <u>DiodesAmericas@vishay.com</u>, <u>DiodesAsia@vishay.com</u>, <u>DiodesEurope@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>








Fig. 6 - Typical Transient Thermal Impedance



Vishay

# Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.