

# JIANGSU CHANGJING ELECTRONICS TECHNOLOGY CO., LTD.

# **AD-2N7002K Plastic-Encapsulated MOSFET**

### AD-2N7002K N-Channel Power MOSFET

| V <sub>(BR)DSS</sub> | R <sub>DS(on), typ</sub> | lο    |
|----------------------|--------------------------|-------|
| 60V                  | 0.9Ω @ 10V               | 340mA |

# SOT-23 1. GATE 2. SOURCE 1 2

# **FEATURES**

- High density cell design for low R<sub>DS(ON)</sub>
- Voltage controlled small signal switch
- High saturation current capability
- AEC-Q101 qualified

# **APPLICATIONS**


- Battery switch
- Load switch
- Power tools
- LED applications
- DC/DC Converter
- Motor drive applications

## **MARKING**





 $\overline{7}$ 2K = Device code



AD-2N7002K www.jscj-elec.com

# MAXIMUM RATINGS (T<sub>j</sub> = 25°C unless otherwise specified)

| Parameter  | Symbol                            | Value     | Unit |
|--|-----------------------------------|-----------|------|
| Drain-source voltage                             | V <sub>DS</sub>                   | 60        | V    |
| Gate-source voltage                              | V <sub>GS</sub>                   | ±20       | V    |
| Continuous drain current                         | I <sub>D</sub> <sup>1)</sup>      | 340       | mA   |
| Maximum power dissipation                        | P <sub>D</sub> 1)                 | 0.35      | W    |
| Single pulsed avalanche energy                   | E <sub>AS</sub> 3)                | 500       | mJ   |
| Thermal resistance from junction to ambient      | R <sub>0JA</sub> <sup>4)</sup>    | 357       | °C/W |
| Operating junction and storage temperature range | T <sub>j</sub> , T <sub>stg</sub> | -55 ~ 150 | °C   |

# ELECTRICAL CHARACTERISTICS (T<sub>j</sub> = 25°C unless otherwise specified)

| Parameter                           | Symbol Test condition         |  | Min   | Тур | Max  | Unit |
|-------------------------------------|-------------------------------|--|-------|-----|------|------|
| Static characteristics              |                               |  |       |     |      |      |
| Drain-source breakdown voltage      | V <sub>(BR)DSS</sub>          | V <sub>GS</sub> = 0V, I <sub>D</sub> = 250μA                                 | 60    | -   | -    | V    |
| Zero gate voltage drain current     | I <sub>DSS</sub>              | V <sub>DS</sub> = 48V, V <sub>GS</sub> = 0V                                  | -     | -   | 1.0  | μA   |
|                                     | I <sub>GSS1</sub>             | $V_{GS} = \pm 20V, V_{DS} = 0V$  | -     | -   | ±10  | μA   |
| Gate-body leakage current           | I <sub>GSS2</sub>             | $V_{GS} = \pm 10V, V_{DS} = 0V$  | -     | -   | ±200 | nA   |
|                                     | I <sub>GSS3</sub>             | $V_{GS} = \pm 5V$ , $V_{DS} = 0V$  | -     | -   | ±100 | nA   |
| Gate threshold voltage 5)           | V <sub>GS(th)</sub>           | $V_{DS} = V_{GS}$ , $I_D = 1mA$  | 1.0   | 1.3 | 2.5  | V    |
| Drain-source on-state resistance 5) | В                             | V <sub>GS</sub> = 10V, I <sub>D</sub> = 500mA                                | -     | 0.9 | 2.5  | Ω    |
| Drain-source on-state resistance of | R <sub>DS(on)</sub>           | V <sub>GS</sub> = 4.5V, I <sub>D</sub> = 200mA                               | -     | 1.1 | 3    |      |
| Dynamic characteristics 5) 6)       |                               |  |       |     |      |      |
| Input capacitance                   | Ciss                          |  | -     | -   | 40   |      |
| Output capacitance                  | Coss                          | $V_{DS} = 10V, V_{GS} = 0V, f = 1MHz$  | -     | -   | 30   | pF   |
| Reverse transfer capacitance        | Crss                          |  | -     | -   | 10   |      |
| Switching parameters 5) 6)          |                               |  |       |     |      |      |
| Turn-on delay time                  | t <sub>d(on)</sub>            | $V_{GS} = 10V$ , $V_{DS} = 50V$ , $R_{G} = 50\Omega$ ,                       | -     | -   | 10   | no   |
| Turn-off delay time                 | $t_{d(off)}$                  | $R_{GS} = 50\Omega$ , $R_L = 250\Omega$                                      | -     | -   | 15   | ns   |
| Reverse recovery time               | t <sub>rr</sub>               | $V_{GS} = 0V$ , $I_S = 300$ mA, $V_R = 25V$ , $d_{1s}/d_t = -100$ A/ $\mu$ s |       | 30  |      | ns   |
| Diode characteristics               |                               |  |       |     |      |      |
| Drain-source diode forward voltage  | V <sub>SD</sub> <sup>5)</sup> | Is = 300mA, V <sub>GS</sub> = 0V   | -     | -   | 1.5  | V    |
| Deceyared shares                    | 0                             | $V_{GS} = 0V$ , $I_S = 300$ mA, $V_R = 25V$ ,                                |       | 20  |      | »C   |
| Recovered charge                    | Qr                            | $d_{ls}/d_t = -100A/\mu s$   |       | 30  |      | nC   |
| Gate-source breakdown voltage       | BV <sub>GSO</sub>             | I <sub>GS</sub> = ±1mA (open drain)  | ±21.5 | -   | ±30  | V    |

<sup>1)</sup> Maximum allowed temperature  $T_j$  = 25°C.

<sup>1)</sup> Pulse width  $\leq$  10µs, duty cycle  $\leq$  1%.


3) Test condition:  $V_{DD} = 25V$ ,  $V_{GS} = 10V$ , L = 0.5 mH,  $R_G = 25\Omega$ , starting at  $T_J = 25^{\circ}C$ .


4) Measured with the device mounted on 1 inch<sup>2</sup> FR-4 board with 2oz. copper, in a still air environment with  $T_a = 25^{\circ}C$ .


5) Pulse test: Pulse width  $\leq$  300µs, duty cycle  $\leq$  2%.


6) Guaranteed by design, not subject to production.


# TYPICAL CHARACTERISTICS

















# **SOT-23 PACKAGE OUTLINE DIMENSIONS**








| Symbol | Dimensions | In Millimeters | Dimensions In Inches |       |  |
|--------|------------|----------------|----------------------|-------|--|
| Зупрог | Min        | Max            | Min                  | Max   |  |
| Α      | 0.900      | 1.150          | 0.035                | 0.045 |  |
| A1     | 0.000      | 0.100          | 0.000                | 0.004 |  |
| A2     | 0.900      | 1.050          | 0.035                | 0.041 |  |
| b      | 0.300      | 0.500          | 0.012                | 0.020 |  |
| С      | 0.080      | 0.150          | 0.003                | 0.006 |  |
| D      | 2.800      | 3.000          | 0.110                | 0.118 |  |
| E      | 1.200      | 1.400          | 0.047                | 0.055 |  |
| E1     | 2.250      | 2.550          | 0.089                | 0.100 |  |
| е      | 0.950      | TYP            | 0.037                | TYP   |  |
| e1     | 1.800      | 2.000          | 0.071                | 0.079 |  |
| L      | 0.550      | REF            | 0.022                | REF   |  |
| L1     | 0.300      | 0.500          | 0.012                | 0.020 |  |
| θ      | 0°         | 8°             | 0°                   | 8°    |  |

# **SOT-23 SUGGESTED PAD LAYOUT**




## Note:

- 1. Controlling dimension in millimeters.
- 2. General tolerance: ±0.05mm.
- 3. The pad layout is for reference purpose only.

# **SOT-23 TAPE AND REEL**

# SOT-23 Embossed Carrier Tape





#### Packaging Description:

SOT-23 parts are shipped in tape. The carrier tape is made from a dissipative (carbon filled) polycarbonate resin. The cover tape is a multilayer film (Heat Activated Adhesive in nature) primarily composed of polyester film, adhesive layer, sealant, and anti-static sprayed agent. These reeled parts in standard option are shipped with 3,000 units per 7" or 17.8cm diameter reel. The reels are clear in color and is made of polystyrene plastic (anti-static coated).

| Dimensions are in millimeter   |      |      |      |       |      |      |      |      |      |      |
|--------------------------------|------|------|------|-------|------|------|------|------|------|------|
| Pkg type A B C d E F P0 P P1 W |      |      |      |       |      |      |      | W    |      |      |
| SOT-23                         | 3.15 | 2.77 | 1.22 | Ø1.50 | 1.75 | 3.50 | 4.00 | 4.00 | 2.00 | 8.00 |

# SOT-23 Tape Leader and Trailer





| Dimensions are in millimeter  |         |       |       |        |        |       |      |       |
|---|---------|-------|-------|--------|--------|-------|------|-------|
| Reel Option         D         D1         D2         G         H         I         W1         W2 |         |       |       |        |        |       |      | W2    |
| 7"Dia   | Ø178.00 | 54.40 | 13.00 | R78.00 | R25.60 | R6.50 | 9.50 | 12.30 |

| REEL     | Reel Size | Box        | Box Size(mm) | Carton      | Carton Size(mm) | G.W.(kg) |
|----------|-----------|------------|--------------|-------------|-----------------|----------|
| 3000 pcs | 7 inch    | 30,000 pcs | 203×203×195  | 120,000 pcs | 438×438×220     |          |

#### **PUBLISHED BY**

JIANGSU CHANGJING ELECTRONICS TECHNOLOGY CO., LTD.

13th Floor, C Block, Tengfei Building, Yan Chuang Yuan, Nanjing Jiangbei New Area, China

### **LEGAL DISCLAIMER**

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples, hints or typical values stated herein and/or any information regarding the application of the device, JSCJ hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of JSCJ in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

#### INFORMATION

For further information on technology, delivery terms and conditions as well as prices, please contact your nearest JSCJ office (<a href="https://www.jscj-elec.com">www.jscj-elec.com</a>).

#### **WARNINGS**

Due to technical requirements, products may contain dangerous substances. For information on the types in question, please contact your nearest JSCJ office.

Except as otherwise explicitly approved by JSCJ in a written document signed by authorized representatives of JSCJ, JSCJ's products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.