

N-Ch MOSFET

General Description

The WSD45N10GDN56 is the highest performance SGT N-Ch MOSFET with extreme high cell density, which provide excellent RDSON and gate charge for most of the synchronous buck converter applications.

The WSD45N10GDN56 meet the RoHS and Green Product requirement, 100% EAS guaranteed with full function reliability approved.

Features

- Advanced high cell density Trench technology
- Super Low Gate Charge
- Excellent Cdv/dt effect decline
- Green Device Available


Product Summery

BVDSS	RDSON	ID
100V	17.5mΩ	45A

Applications

- DC-DC Converter.
- Motor Control.

DFN5X6 Pin Configuration



Absolute Maximum Ratings

Symbol	Parameter	Rating	Units	
V_{DS}	Drain-Source Voltage	100	V	
V_{GS}	Gate-Source Voltage	±20	V	
I _D @T _C =25℃	Continuous Drain Current, V _{GS} @ 10V	45	Α	
I _D @T _C =100℃	Continuous Drain Current, V _{GS} @ 10V	33	Α	
I _D @T _A =25℃	Continuous Drain Current, V _{GS} @ 10V	12	Α	
I _D @T _A =70°C	Continuous Drain Current, V _{GS} @ 10V	9.6	Α	
I _{DM} ^a	Pulsed Drain Current	130	Α	
E _{AS} ^b	Single Pulse Avalanche Energy	169	mJ	
I _{AS} b	Avalanche Current	26	Α	
P _D @T _C =25℃	Total Power Dissipation	95	W	
P _D @T _A =25℃	Total Power Dissipation 5.0		W	
T _{STG}	Storage Temperature Range -55 to 150		°C	
T_J	Operating Junction Temperature Range	-55 to 150	$^{\circ}$	

Thermal Data

Symbol	Parameter	Тур.	Max.	Unit
R _{θJA} ^c	Thermal Resistance Junction-ambient		60	°C/W
$R_{ heta JC}$	Thermal Resistance Junction-Case		2.4	°C/W

Note a: Pulse width limited by max. junction temperature.

Note b: UIS tested and pulse width limited by maximum junction temperature 150° C (initial temperature $T_j=25^{\circ}$ C).

Note c: Surface Mounted on 1in² pad area.

N-Ch MOSFET

Electrical Characteristics (T_J=25 °C, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit
BV _{DSS}	Drain-Source Breakdown Voltage	V _{GS} =0V , I _D =250uA	100			V
$\triangle BV_{DSS}/\triangle T_{J}$	BVDSS Temperature Coefficient	Reference to 25°C , I _D =1mA		0.0		V/℃
R _{DS(ON)} d	Static Drain-Source On-Resistance ²	V _{GS} =10V , I _D =26A		14.5	17.5	mΩ
$V_{GS(th)}$	Gate Threshold Voltage	V _{GS} =V _{DS} , I _D =250uA	1.2	2.0	3.0	V
$ riangle V_{GS(th)}$	V _{GS(th)} Temperature Coefficient			-5		mV/℃
ı	Drain-Source Leakage Current	V_{DS} =80V , V_{GS} =0V , T_J =25 $^{\circ}\mathrm{C}$		-	1	uA
I _{DSS}		V_{DS} =80V , V_{GS} =0V , T_J =55 $^{\circ}\mathrm{C}$		-	30	uA
I _{GSS}	Gate-Source Leakage Current	V_{GS} = $\pm 20V$, V_{DS} = $0V$		-	±100	nA
R _g e	Gate Resistance	V _{DS} =0V , V _{GS} =0V , f=1MHz		1.0		Ω
Qg ^e	Total Gate Charge (10V)	V _{DS} =50V , V _{GS} =10V , I _D =26A		42	59	
Q _{gs} e	Gate-Source Charge			12		nC
Q_{gd}^e	Gate-Drain Charge			12		
T _{d(on)} e	Turn-On Delay Time	V_{DD} =30V , V_{GEN} =10V , R_{G} =6 Ω I_{D} =1A ,RL=30 Ω		19	35	
T _r e	Rise Time			9	17]
T _{d(off)} e	Turn-Off Delay Time			36	65	ns
T _f e	Fall Time			22	40	
C _{iss} e	Input Capacitance	V _{DS} =30V , V _{GS} =0V , f=1MHz		1800		
C _{oss} e	Output Capacitance			215		pF
C _{rss} e	Reverse Transfer Capacitance			42		

Diode Characteristics


Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit
Is	Continuous Source Current	V _G =V _D =0V , Force Current		-	26	Α
V_{SD}^d	Diode Forward Voltage	V_{GS} =0V , I_S =1A , T_J =25 $^{\circ}$ C		-	1.3	V
t _{rr}	Reverse Recovery Time	I- 004 IVII 4004/ T 05%		44		nS
Q _{rr}	Reverse Recovery Charge	IF=20A , dI/dt=100A/μs , T _J =25℃		95		nC


Note d : Pulse test ; pulse width $\leq 300 \mu s$, duty cycle $\leq 2\%$.

Note e: Guaranteed by design, not subject to production testing.




Typical Characteristics






Safe Operation Area




Thermal Transient Impedance




Square Wave Pulse Duration (sec)




Output Characteristics




Drain-Source On Resistance



Gate-Source On Resistance




Gate Threshold Voltage







Drain-Source On Resistance




Source-Drain Diode Forward





Gate Charge





Attention

- 1, Any and all Winsok power products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your Winsok power representative nearest you before using any Winsok power products described or contained herein in such applications.
- 2, Winsok power assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all Winsok power products described or contained herein.
- 3, Specifications of any and all Winsok power products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- 4, Winsok power Semiconductor CO., LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- 5,In the event that any or all Winsok power products (including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.
- 6, No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of Winsok power Semiconductor CO., LTD.
- 7, Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production. Winsok power believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.
- 8, Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the Winsok power product that you Intend to use.
- 9, this catalog provides information as of Sep.2014. Specifications and information herein are subject to change without notice.