# JK-SMD500L PPTC DEVICES


Part Number: Q/JKTD-12-500





Page No: 1 OF 3





Terminal pad materials: Tin-Plated Nickle-copper

Terminal pad solderability: Meets EIA specification RS 186-9E and ANSI/J-STD-002 Category 3.

Marking: JK500L=2920(500)

Table1 :DIMENTION(Unit : mm)

Model	Maulsina	A		В		C		D
Model	Marking	Min.	Max.	Min.	Max.	Min.	Max	Min.
JK-SMD500L	JK500L	6.73	7.98	4.80	5.44	0.60	1.50	0.30

### Table2:PERFORMANCE RATINGS:

Model	V <sub>max</sub>	I <sub>max</sub>	I <sub>hold</sub>	I <sub>trip</sub>	P <sub>d</sub>	Maxin Time To		Resis	stance
Model	(Vdc)	(A)	(A)	(A)	Typ (W)	Current	Time	Rimin	R1 <sub>max</sub>
			(A)	(A)	(**)	(A)	(Sec)	$(\Omega)$	$(\Omega)$
JK-SMD500L	12.0	40	5.0	10.00	1.500	25.00	5.00	0.005	0.031

### Table3:Test Conditions and Standards

Item	Test conditions	Standard		
Initial Resistance	25℃	0.005~0.031Ω		
$ m I_H$	25℃, 5.00A, 30min	No Trip		
Ttrip	25℃, 25.00A	≤5.0s		
Trip endurance	12V, 40A, 1hr	No arcing or burning		

Operating Temperature: -40℃ TO 85℃

Packaging: Bulk, 1500pcs per bag

SHENZHEN JINRUI ELECTRONIC MATERIAL CO.,LTD

6 F DISTRICT NO. 3000046 BLDG Hi-Tech SCIENCE &

INDUSTRY PARK SHANGKENG COMMUNITY GUANLAN STREET BAOAN SHENZHEN

TEL: 0755-26546327 26584158

Web Site: www.jkpptc.com

FAX: 0755-26546562

E-mail:customer@jkpptc.com

# JK-SMD500L PPTC DEVICES

Part Number: Q/JKTD-12-500




Edition: A0

Page No: 2 OF 3



#### **Solder reflow conditions**



Reflow Profile	Time -
Hetlow Profile	i ime

Profile Feature	Pb-Free Assembly		
Average ramp up rate (Ts <sub>MAX</sub> to Tp)	3°C/second max.		
Preheat			
<ul> <li>Temperature min. (Ts<sub>MIN</sub>)</li> </ul>	150°C		
<ul> <li>Temperature max. (Ts<sub>MAX</sub>)</li> </ul>	200°C		
<ul> <li>Time (ts<sub>MIN</sub> to ts<sub>MAX</sub>)</li> </ul>	60-120 seconds		
Time maintained above:			
• Temperature (T <sub>L</sub> )	217°C		
• Time (t <sub>L</sub> )	60-150 seconds		
Peak/Classification temperature (Tp)	260°C		
Time within 5°C of actual peak temperat	ure		
Time (tp)	30 seconds max.		
Ramp down rate	3°C/second max.		
Time 25°C to peak temperature	8 minutes max.		

Note: All temperatures refer to topside of the package, measured on the package

- Recommended reflow methods: IR, vapor phase oven, hot air oven, N2 environment for lead-free.
- Devices are not designed to be wave soldered to the bottom side of the board.
- Recommended maximum paste thickness is 0.25mm (0.010inch).
- Devices can be cleaned using standard industry methods and solvents.
- Soldering temprature profile meets RoHs leadfree process.

Notes: If reflow temperatures exceed the recommended profile, devices may not meet the performance requirements

SHENZHEN JINRUI ELECTRONIC MATERIAL CO.,LTD

6 F DISTRICT NO. 3000046 BLDG Hi-Tech SCIENCE &

INDUSTRY PARK SHANGKENG COMMUNITY GUANLAN STREET BAOAN SHENZHEN

TEL: 0755-26546327 26584158

Web Site: www.jkpptc.com

FAX: 0755-26546562

E-mail:customer@jkpptc.com

## JK-SMD500L PPTC DEVICES


Part Number: Q/JKTD-12-500





Edition: A0

Page No: 3 OF 3



**Solder reflow conditions** 

### Storage

The maximum ambient temperature shall not exceed  $38\,^\circ\!\!\mathrm{C}$ . Storage temperatures higher than  $38\,^\circ\!\!\mathrm{C}$  could result in the deformation of packaging materials. The maximum relative humidity recommended for storage is 60%. High humidity with high temperature can accelerate the oxidation of the solder plating on the termination and reduce the solderability of the components. Sealed plastic bags with desiccant shall be used to reduce the oxidation of the termination and shall only be opened prior to use. The products shall not be stored in areas where harmful gases containing sulfur or chlorine are present

#### WARNING

- · Use PPTC beyond the maximum ratings or improper use may result in device damage and possible electrical arcing and flame.
- · PPTC are intended for protection against occasional over current or over temperature fault conditions and should not be used when repeated fault conditions or prolonged trip events are anticipated.
- · Device performance can be impacted negatively if devices are handled in a manner inconsistent with recommended electronic, thermal, and mechanical procedures for electronic components.
- · Use PPTC with a large inductance in circuit will generate a circuit voltage (L di/dt) above the rated voltage of the PPTC.
- · Avoid impact PPTC device its thermal expansion like placed under pressure or installed in limited space.
- · Contamination of the PPTC material with certain silicon based oils or some aggressive solvents can adversely impact the performance of the devices.PPTC SMD can be cleaned by standard methods.
- · Requests that customers comply with our recommended solder pad layouts and recommended reflow profile. Improper board layouts or reflow profilecould negatively impact solderability performance of our devices.

SHENZHEN JINRUI ELECTRONIC MATERIAL CO.,LTD

6 F DISTRICT NO. 3000046 BLDG Hi-Tech SCIENCE &

INDUSTRY PARK SHANGKENG COMMUNITY GUANLAN STREET BAOAN SHENZHEN

TEL: 0755-26546327 26584158 FAX: 0755-26546562

Web Site: www.jkpptc.com E-mail:customer@jkpptc.com