

# SS315 THRU SS320

# GOODWORK 3.0 AMP SURFACE MOUNT SCHOTTKY BARRIER RECTIFIER



### **FEATURES**


- \* Ideal for surface mount applications
- \* Easy pick and place
- \* Built-in strain relief
- \* Low forward voltage drop

### **MECHANICAL DATA**

- \* Case: Molded plastic
- \* Epoxy: UL 94V-0 rate flame retardant
- \* Metallurgically bonded construction
- \* Polarity: Color band denotes cathode end
- \* Mounting position: Any \* Weight: 0.063 grams

## VOLTAGE RANGE 150 to 200 Volts CURRENT

3.0 Amperes



Dimensions in inches and (millimeters)

## MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Rating 25°C ambient temperature uniess otherwies specified. Single phase half wave, 60Hz, resistive or inductive load. For capacitive load, derate current by 20%.


TYPE NUMBER	SS315	SS320	UNITS
Maximum Recurrent Peak Reverse Voltage	150	200	V
Maximum RMS Voltage	105	140	V
Maximum DC Blocking Voltage	150	200	V
Maximum Average Forward Rectified Current			
at TL=100°C	3.0		А
Peak Forward Surge Current, 8.3 ms single half sine-wave			
superimposed on rated load (JEDEC method)	80		А
Maximum Instantaneous Forward Voltage at 3.0A	0.92		V
Maximum DC Reverse Current Ta=25°C	(	).02	mA
at Rated DC Blocking Voltage Ta=100°C	2		mA
Typical Junction Capacitance (Note1)	250		PF
Typical Thermal Resistance RθJL (Note 2)	10		°C/W
Operating Temperature Range T <sub>J</sub>	-65 —+150		°C
Storage Temperature Range Tsrg	-65 —+150		°C

#### NOTES:

- 1. Measured at 1MHz and applied reverse voltage of 4.0V D.C.
- 2. Thermal Resistance Junction to Lead Vertical PC Board Mounting 0.5"(12.7mm) Lead Length.

#### RATING AND CHARACTERISTIC CURVES (SS315 THRU SS320)

#### FIG.1-TYPICAL FORWARD CURRENT DERATING CURVE



## FIG.3-MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT




FIG.4-TYPICAL JUNCTION CAPACITANCE




FIG.2-TYPICAL FORWARD




FIG.5 - TYPICAL REVERSE

