

## HV9967B

## **Integrated LED Driver with Average-Mode Current Control**

#### **Features**

- · 3% Accurate LED Current
- 60V, 0.8Ω Integrated MOSFET
- · Low Sensitivity to External Component Variation
- · Single-Resistor LED Current Setting
- · Fixed Off-Time Control
- · PWM Dimming Input
- · Output Short-Circuit Protection with Skip Mode
- · Overtemperature Protection

## **Applications**

- · DC/DC or AC/DC LED Drivers
- · RGB Backlighting Drivers for Flat Panel Displays
- · General Purpose Constant-Current Source
- · Signage and Decorative LED Lighting
- · Chargers


#### **General Description**

The HV9967B is an Average-mode current control LED driver IC operating in a Constant Off-time mode.


The IC features an integrated 60V,  $0.8\Omega$  MOSFET that can be used as a stand-alone buck converter switch or connected as a source driver for driving an external high-voltage Depletion-mode MOSFET. The HV9967B is powered through its switching output when the integrated switch is off. Therefore, the same external MOSFET can be used as a high-voltage linear regulator for powering the IC.

The LED current is programmed with one external resistor. The Average-mode current control method does not produce a peak-to-average error. This greatly improves the current accuracy as well as the line and load regulations of the LED current without any need for loop compensation or direct sensing of the LED current at a high-voltage potential. The auto-zero circuit cancels the effects of the input offset voltage and of the propagation delay of the current sense comparator.


#### Package Types



## **Functional Block Diagram**



## **Typical Application Circuit**



## 1.0 ELECTRICAL CHARACTERISTICS

## **Absolute Maximum Ratings †**

SW to GND	–0.5V to +65V
V <sub>DD</sub> to GND	0.3V to 6V
Other I/O to GND	
I <sub>RT</sub>	2 mA
Junction Temperature Range, T <sub>J</sub>	
Storage Temperature Range, T <sub>S</sub>	
Continuous Power Dissipation (T <sub>A</sub> = +25°C):	
8-lead MSOP	350 mW
8-lead DFN	1.6W

**† Notice:** Stresses above those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only, and functional operation of the device at those or any other conditions above those indicated in the operational sections of this specification is not intended. Exposure to maximum rating conditions for extended periods may affect device reliability.

### **ELECTRICAL CHARACTERISTICS**

<b>Electrical Specifications</b> : $T_A = 25$ °C, $V_{SW} = 10V/10$ mA, $V_{DD} = 5V$ unless otherwise specified.										
Parameter	Sym.	Min.	Тур.	Max.	Unit	Conditions				
INPUT	•									
Input DC Supply Voltage Range	V <sub>SWDC</sub>	8	_	60	V	DC input voltage (Note 1)				
Shutdown Mode Supply Current	I <sub>INSD</sub>	_	0.5	1	mA	Pin PWMD connected to GND				
INTERNAL REGULATOR										
Internally Regulated Voltage	$V_{DD}$	4.7	5	5.2	V	$V_{PWMD} = V_{DD}, R_T = 100 \text{ k}\Omega$				
V <sub>DD</sub> Undervoltage Lockout Upper Threshold	V <sub>UVLOR</sub>	4.1	4.35	4.7	V	V <sub>DD</sub> rising, as needed to ensure I <sub>C(MIN)</sub> (Note 1)				
V <sub>DD</sub> Undervoltage Lockout Hysteresis	ΔV <sub>UVLO</sub>	_	150	_	mV	V <sub>DD</sub> falling				
PMW DIMMING		•								
PWMD Input Low Voltage	V <sub>EN(LO)</sub>	_	_	8.0	V	(Note 1)				
PWMD Input High Voltage	V <sub>EN(HI)</sub>	2	_	_	V	(Note 1)				
PWMD Pull-Down Resistance	R <sub>EN</sub>	50	100	150	kΩ	V <sub>PWMD</sub> = 5V				
CURRENT CONTROL										
RSENSE Current Threshold Voltage	V <sub>CS(TH)</sub>	243	250	257	mV					
Threshold Voltage Temperature Coefficient	dV <sub>CS</sub> /dT	_	0.1	_	mV/°C					
Current Sense Blanking Interval	T <sub>BLANK</sub>	140	_	290	ns	(Note 1)				
Minimum On-Time	T <sub>ON(MIN)</sub>	_	_	950	ns	V <sub>RSENSE</sub> = V <sub>CS(TH)</sub> + 50 mV (Note 1)				
Maximum Steady-State Duty Cycle	D <sub>MAX</sub>	80	_	_	%	Reduction in output LED current may occur beyond this duty cycle. (Note 1)				
SHORT-CIRCUIT PROTECTION										
Hiccup Threshold Voltage at RSENSE	V <sub>CS(SHORT)</sub>	355	400	440	mV	(Note 1)				
Current Limit Delay RSENSE to SW-OFF	T <sub>DELAY</sub>			150	ns	V <sub>RSENSE</sub> = V <sub>CS(SHORT)</sub> + 50 mV				

**Note 1:** Denotes specifications which apply over the full operating ambient temperature range of  $-40^{\circ}\text{C} < \text{T}_{\text{A}} < +125^{\circ}\text{C}$ 

2: For design guidance only

## **ELECTRICAL CHARACTERISTICS (CONTINUED)**

<b>Electrical Specifications</b> : $T_A = 25$ °C, $V_{SW} = 10V/10$ mA, $V_{DD} = 5V$ unless otherwise specified.									
Parameter	Sym.	Min.	Тур.	Max.	Unit	Conditions			
Short-Circuit Hiccup Time	T <sub>HICCUP</sub>	_	800		μs				
Minimum On-Time (Short-Circuit)	T <sub>ON(MIN),SC</sub>	_	_	400	ns	V <sub>RSENSE</sub> = V <sub>CS(SHORT)</sub> + 50 mV			
T <sub>OFF</sub> TIMER	•								
		28	40	48		$R_T = 100 \text{ k}\Omega \text{ (Note 1)}$			
Off Time	T <sub>OFF</sub>	7	10	12	μs	$R_T = 100 \text{ k}\Omega \text{ (Note 1)}$			
		0.7	1	1.2		$R_T = 10 \text{ k}\Omega \text{ (Note 1)}$			
SW OUTPUT	•								
On Resistance	R <sub>ON</sub>	_	0.8	_	Ω	V <sub>DD</sub> = 5V			
Continuous Current	I <sub>C</sub>	0.75	_	_	А	V <sub>DD</sub> = 4.75V, V <sub>RSENSE</sub> = 370 mV, V <sub>SW</sub> = 10V ( <b>Note 1</b> )			
OVERTEMPERATURE PROTECTION	ON					•			
Thermal Shutdown Temperature	T <sub>SD</sub>	125	145	_	°C	Note 2			
Thermal Shutdown Hysteresis	$\Delta T_{SD}$	_	20	_	°C	Note 2			

**Note 1:** Denotes specifications which apply over the full operating ambient temperature range of  $-40^{\circ}\text{C} < \text{T}_{\text{A}} < +125^{\circ}\text{C}$ 

2: For design guidance only

## **TEMPERATURE SPECIFICATIONS**

Parameter	Sym.	Min.	Тур.	Max.	Unit	Conditions			
TEMPERATURE RANGE									
Operating Ambient Temperature	T <sub>A</sub>	-40	_	+125	°C				
Maximum Junction Temperature	T <sub>J(ABSMAX)</sub>	_	_	+150	°C				
Storage Temperature	Ts	-65	_	+150	°C				
PACKAGE THERMAL RESISTANCE									
8-lead MSOP	$\theta_{JA}$	_	216	_	°C/W				
8-lead DFN	$\theta_{JA}$	_	60	_	°C/W				

## HV9967B

## 2.0 PIN DESCRIPTION

Table 2-1 shows the pin description details of HV9967B. Refer to **Package Types** for the location of pins.

TABLE 2-1: PIN FUNCTION TABLE

Pin Number	Pin Name	Description
1	SW	Drain of 60V 0.8Ω NDMOS switch and input of H/V regulator
2	RSENSE	Source of NDMOS switch and current sense input. Connect a resistor between RSENSE and GND to program the output current and short-circuit protection tripping current.
3	PGND	Power ground. Must be wired to AGND on PCB.
4	PWMD	PWM dimming input. This TTL input enables switching of SW when in High state.
5	NC	No connection
6	RT	Resistor connected between RT and VDD. This programs the off time of SW.
7	AGND	Analog ground (0V)
8	VDD	Power supply for all internal circuits. Bypass with a low ESR capacitor to PGND (>0.5 µF). Connect gate of external Depletion-mode NFET for high-voltage operation.

#### 3.0 APPLICATION INFORMATION

## 3.1 General Description

The HV9967B employs a control scheme that achieves fast and extremely accurate control of the average current in the buck inductor by sensing only the switch current. No compensation of the current control loop is required. The LED current response to PWMD input is similar to that of the peak-current control ICs, such as the HV9910B. The inductor current ripple amplitude does not affect this control scheme significantly. Therefore, the LED current is independent of the variation in inductance, switching frequency and output voltage. Constant off-time control of the buck converter is used for stability and to reduce input voltage regulation of the LED current.

#### 3.2 Off Timer

The timing resistor connected to RT pin determines the off time of the gate driver and SW. The timing resistor must be wired across RT pin and VDD pin. Refer to Equation 3-1 for the computation of the SW off time.

#### **EQUATION 3-1:**

$$T_{OFF}$$
=  $R_T \times 100 pF$  Within the range of 10 kΩ ≤ R<sub>T</sub> ≤ 400 kΩ

# 3.3 Average Current Control Feedback and Output Short-Circuit Protection

The constant-current control feedback derives the average-current signal from the source current of the switching MOSFET. This current is detected with a sense resistor at the RSENSE pin. The feedback operates in a fast Open-loop mode. No compensation is required. Output current is programmed as seen in Equation 3-2:

#### **EQUATION 3-2:**

$$I_{LED} = \frac{0.25 \, V}{R_{CS}}$$

The above equation is only valid for continuous conduction of the output inductor. It is a good practice to design the inductor such that the peak-to-peak switching inductor ripple current in it is 30% to 40% of its average full DC current load. Hence, the recommended inductance can be computed as specified in Equation 3-3:

#### **EQUATION 3-3:**

$$L_O = \frac{V_{O(MAX)} \times T_{OFF}}{0.4 \times I_O}$$

The duty cycle range of the current control feedback is limited to D  $\leq$  0.8. A reduction in the LED current may occur when the LED string voltage  $V_O$  is greater than 80% of the input voltage  $V_{IN}$  of the HV9967B LED driver

Reducing the output LED voltage  $V_O$  below  $V_{O(MIN)} = V_{IN} \times D_{MIN}$ , where  $D_{MIN} = 0.8 \ \mu s/(T_{OFF} + 8 \ \mu s)$ , may also result in loss of LED current regulation. This condition, however, causes an increase in the LED current and can potentially trip the short-circuit protection comparator threshold.

The short-circuit protection comparator trips when the voltage at RSENSE exceeds 0.4V. When this occurs, the SW off time  $T_{HICCUP}$  = 800  $\mu$ s is generated to prevent the staircasing of the inductor current and, potentially, its saturation due to insufficient output voltage. The typical short-circuit inductor current is shown in the waveform in Figure 3-1.




FIGURE 3-1: Short-Circuit Inductor Current.

A leading-edge blanking delay is provided at RSENSE pin to prevent false triggering of the short-circuit hiccup threshold voltage and the short-circuit protection.

#### 3.4 SW Input and Linear Regulator

The HV9967B includes an integrated 60V,  $0.8\Omega$  switching MOSFET at the SW input. The power for the IC is supplied from a built-in linear 5V regulator that is also derived from the SW input.

#### 3.5 PWM Dimming


The HV9967B features a TTL-compatible dimming input PWMD. Applying a square-wave voltage to PWMD will modulate the duty ratio of the LED current accordingly. The rising and falling edges are limited by the current slew rate in the inductor. The first switching cycle is terminated upon reaching the 250 mV level at RSENSE pin. The circuit will reach the Steady state within three to four switching cycles regardless of the switching frequency.

#### 3.6 Overtemperature Protection

The HV9967B includes overtemperature protection. Typically, when the junction temperature exceeds 145°C, switching of the SW input is disabled. The switching resumes when the temperature falls by approximately 20°C from the trip point.

### 4.0 PACKAGING INFORMATION

## 4.1 Package Marking Information




Legend: XX...X Product Code or Customer-specific information
Y Year code (last digit of calendar year)
YY Year code (last 2 digits of calendar year)
WW Week code (week of January 1 is week '01')
NNN Alphanumeric traceability code

By-free JEDEC® designator for Matte Tin (Sn)
This package is Pb-free. The Pb-free JEDEC designator (a)
can be found on the outer packaging for this package.

In the event the full Microchip part number cannot be marked on one line, it will be carried over to the next line, thus limiting the number of available characters for product code or customer-specific information. Package may or not include the corporate logo.

## 8-Lead MSOP Package Outline (MG)

3.00x3.00mm body, 1.10mm height (max), 0.65mm pitch



Note: For the most current package drawings, see the Microchip Packaging Specification at www.microchip.com/packaging.

A Pin 1 identifier must be located in the index area indicated. The Pin 1 identifier can be: a molded mark/identifier; an embedded metal marker; or a printed indicator.

Symbo	ol	Α	A1	A2	b	D	E	E1	е	L	L1	L2	θ	θ1
	MIN	0.75*	0.00	0.75	0.22	2.80*	4.65*	2.80*		0.40			<b>0</b> o	5º
Dimension (mm)	NOM	-	-	0.85	-	3.00	4.90	3.00	0.65 BSC	0.60	0.95 REF	0.25 BSC	-	-
(,	MAX	1.10	0.15	0.95	0.38	3.20*	5.15*	3.20*	D00	0.80	INCI	500	<b>8</b> º	15°


JEDEC Registration MO-187, Variation AA, Issue E, Dec. 2004.

<sup>\*</sup> This dimension is not specified in the JEDEC drawing.

Drawings are not to scale.

## 8-Lead DFN Package Outline (K7)

3.00x3.00mm body, 0.80mm height (max), 0.65mm pitch



Note: For the most current package drawings, see the Microchip Packaging Specification at www.microchip.com/packaging. Notes:

- A Pin 1 identifier must be located in the index area indicated. The Pin 1 identifier can be: a molded mark/identifier; an embedded metal marker; or a printed indicator.
- a printed inducation.

  Depending on the method of manufacturing, a maximum of 0.15mm pullback (L1) may be present. The inner tip of the lead may be either rounded or square.

Symb	ol	Α	A1	А3	b	D	D2	E	E2	е	L	L1	θ
	MIN	0.70	0.00		0.25	2.85*	1.60	2.85*	1.35		0.30	0.00*	0o
Dimension (mm)	NOM	0.75	0.02	0.20 REF	0.30	3.00	-	3.00	-	0.65 BSC	0.40	-	-
()	MAX	0.80	0.05		0.35	3.15*	2.50	3.15*	1.75	BSC	0.50	0.15	14 <sup>0</sup>

JEDEC Registration MO-229, Variation WEEC-2, Issue C, Aug. 2003.
\* This dimension is not specified in the JEDEC drawing.

Drawings not to scale.

## APPENDIX A: REVISION HISTORY

## Revision A (February 2020)

- Converted Supertex Doc# DSFP-HV9967B to Microchip DS20005734A
- Updated the package marking format
- Updated the packaging quantity of the 8-lead DFN K7 package from 3000/Reel to 3300/Reel to align it with the actual BQM
- Made minor text changes throughout the document

## PRODUCT IDENTIFICATION SYSTEM

To order or obtain information, e.g., on pricing or delivery, contact your local Microchip representative or sales office.

PART NO.	<u> </u>		- х - х	Examples:	
Device	Package Environmental Options		Environmental Media Type	a) HV9967BMG-G:	Integrated LED Driver with Average-Mode Current Control, 8-lead MSOP, 2500/Reel
Device:	HV9967B	=	Integrated LED Driver with Average-Mode Current Control	b) HV9967BK7-G:	Integrated LED Driver with Average-Mode Current Control, 8-lead WDFN, 3300/Reel
Packages:	MG	=	8-lead MSOP		
	K7	=	8-lead WDFN		
Environmental:	G	=	Lead (Pb)-free/RoHS-compliant Package		
Media Type:	(blank)	=	2500/Reel for an MG Package, 3300/Reel for a K7 Package		

#### Note the following details of the code protection feature on Microchip devices:

- · Microchip products meet the specification contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is one of the most secure families of its kind on the market today, when used in the intended manner and under normal conditions.
- There are dishonest and possibly illegal methods used to breach the code protection feature. All of these methods, to our
  knowledge, require using the Microchip products in a manner outside the operating specifications contained in Microchip's Data
  Sheets. Most likely, the person doing so is engaged in theft of intellectual property.
- Microchip is willing to work with the customer who is concerned about the integrity of their code.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of their code. Code protection does not mean that we are guaranteeing the product as "unbreakable."

Code protection is constantly evolving. We at Microchip are committed to continuously improving the code protection features of our products. Attempts to break Microchip's code protection feature may be a violation of the Digital Millennium Copyright Act. If such acts allow unauthorized access to your software or other copyrighted work, you may have a right to sue for relief under that Act.

Information contained in this publication regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION, INCLUDING BUT NOT LIMITED TO ITS CONDITION, QUALITY, PERFORMANCE, MERCHANTABILITY OR FITNESS FOR PURPOSE. Microchip disclaims all liability arising from this information and its use. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

#### **Trademarks**

The Microchip name and logo, the Microchip logo, Adaptec, AnyRate, AVR, AVR logo, AVR Freaks, BesTime, BitCloud, chipKIT, chipKIT logo, CryptoMemory, CryptoRF, dsPIC, FlashFlex, flexPWR, HELDO, IGLOO, JukeBlox, KeeLoq, Kleer, LANCheck, LinkMD, maXStylus, maXTouch, MediaLB, megaAVR, Microsemi, Microsemi logo, MOST, MOST logo, MPLAB, OptoLyzer, PackeTime, PIC, picoPower, PICSTART, PIC32 logo, PolarFire, Prochip Designer, QTouch, SAM-BA, SenGenuity, SpyNIC, SST, SST Logo, SuperFlash, Symmetricom, SyncServer, Tachyon, TempTrackr, TimeSource, tinyAVR, UNI/O, Vectron, and XMEGA are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

APT, ClockWorks, The Embedded Control Solutions Company, EtherSynch, FlashTec, Hyper Speed Control, HyperLight Load, IntelliMOS, Libero, motorBench, mTouch, Powermite 3, Precision Edge, ProASIC, ProASIC Plus, ProASIC Plus logo, Quiet-Wire, SmartFusion, SyncWorld, Temux, TimeCesium, TimeHub, TimeProvider, Vite, WinPath, and ZL are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Adjacent Key Suppression, AKS, Analog-for-the-Digital Age, Any Capacitor, AnyIn, AnyOut, BlueSky, BodyCom, CodeGuard, CryptoAuthentication, CryptoAuthentication, CryptoCompanion, CryptoController, dsPICDEM, dsPICDEM.net, Dynamic Average Matching, DAM, ECAN, EtherGREEN, In-Circuit Serial Programming, ICSP, INICnet, Inter-Chip Connectivity, JitterBlocker, KleerNet, KleerNet logo, memBrain, Mindi, MiWi, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, MultiTRAK, NetDetach, Omniscient Code Generation, PICDEM, PICDEM.net, PICkit, PICtail, PowerSmart, PureSilicon, QMatrix, REAL ICE, Ripple Blocker, SAM-ICE, Serial Quad I/O, SMART-I.S., SQI, SuperSwitcher, SuperSwitcher II, Total Endurance, TSHARC, USBCheck, VariSense, ViewSpan, WiperLock, Wireless DNA, and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

SQTP is a service mark of Microchip Technology Incorporated in the U.S.A.

The Adaptec logo, Frequency on Demand, Silicon Storage Technology, and Symmcom are registered trademarks of Microchip Technology Inc. in other countries.

GestIC is a registered trademark of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2020, Microchip Technology Incorporated, All Rights Reserved.

ISBN:978-1-5224-5677-3

For information regarding Microchip's Quality Management Systems, please visit www.microchip.com/quality.



## Worldwide Sales and Service

#### **AMERICAS**

Corporate Office 2355 West Chandler Blvd. Chandler, AZ 85224-6199

Tel: 480-792-7200 Fax: 480-792-7277 Technical Support:

http://www.microchip.com/ support

Web Address:

www.microchip.com

Atlanta Duluth, GA

Tel: 678-957-9614 Fax: 678-957-1455

**Austin, TX** Tel: 512-257-3370

**Boston** 

Westborough, MA Tel: 774-760-0087 Fax: 774-760-0088

Chicago Itasca, IL

Tel: 630-285-0071 Fax: 630-285-0075

Dallas

Addison, TX Tel: 972-818-7423 Fax: 972-818-2924

**Detroit** Novi, MI

Tel: 248-848-4000

Houston, TX Tel: 281-894-5983

Indianapolis

Noblesville, IN Tel: 317-773-8323 Fax: 317-773-5453 Tel: 317-536-2380

Los Angeles

Mission Viejo, CA Tel: 949-462-9523 Fax: 949-462-9608 Tel: 951-273-7800

**Raleigh, NC** Tel: 919-844-7510

New York, NY Tel: 631-435-6000

**San Jose, CA** Tel: 408-735-9110 Tel: 408-436-4270

**Canada - Toronto** Tel: 905-695-1980 Fax: 905-695-2078

#### ASIA/PACIFIC

Australia - Sydney Tel: 61-2-9868-6733

**China - Beijing** Tel: 86-10-8569-7000

China - Chengdu Tel: 86-28-8665-5511

China - Chongqing Tel: 86-23-8980-9588

**China - Dongguan** Tel: 86-769-8702-9880

**China - Guangzhou** Tel: 86-20-8755-8029

China - Hangzhou Tel: 86-571-8792-8115

China - Hong Kong SAR Tel: 852-2943-5100

China - Nanjing Tel: 86-25-8473-2460

China - Qingdao Tel: 86-532-8502-7355

**China - Shanghai** Tel: 86-21-3326-8000

China - Shenyang

Tel: 86-24-2334-2829 China - Shenzhen

Tel: 86-755-8864-2200

**China - Suzhou** Tel: 86-186-6233-1526

**China - Wuhan** Tel: 86-27-5980-5300

China - Xian Tel: 86-29-8833-7252

China - Xiamen
Tel: 86-592-2388138

**China - Zhuhai** Tel: 86-756-3210040

#### ASIA/PACIFIC

India - Bangalore Tel: 91-80-3090-4444

India - New Delhi Tel: 91-11-4160-8631

India - Pune Tel: 91-20-4121-0141

**Japan - Osaka** Tel: 81-6-6152-7160

**Japan - Tokyo** Tel: 81-3-6880- 3770

Korea - Daegu

Tel: 82-53-744-4301

Korea - Seoul Tel: 82-2-554-7200

Malaysia - Kuala Lumpur Tel: 60-3-7651-7906

Malaysia - Penang Tel: 60-4-227-8870

Philippines - Manila Tel: 63-2-634-9065

**Singapore** Tel: 65-6334-8870

**Taiwan - Hsin Chu** Tel: 886-3-577-8366

Taiwan - Kaohsiung Tel: 886-7-213-7830

**Taiwan - Taipei** Tel: 886-2-2508-8600

Thailand - Bangkok Tel: 66-2-694-1351

Vietnam - Ho Chi Minh Tel: 84-28-5448-2100

#### **EUROPE**

**Austria - Wels** Tel: 43-7242-2244-39

Fax: 43-7242-2244-393 **Denmark - Copenhagen**Tel: 45-4450-2828

Fax: 45-4485-2829

**Finland - Espoo** Tel: 358-9-4520-820

France - Paris
Tel: 33-1-69-53-63-20
Fax: 33-1-69-30-90-79

Germany - Garching Tel: 49-8931-9700

**Germany - Haan** Tel: 49-2129-3766400

Germany - Heilbronn Tel: 49-7131-72400

**Germany - Karlsruhe** Tel: 49-721-625370

**Germany - Munich** Tel: 49-89-627-144-0 Fax: 49-89-627-144-44

Germany - Rosenheim Tel: 49-8031-354-560

Israel - Ra'anana Tel: 972-9-744-7705

Italy - Milan Tel: 39-0331-742611 Fax: 39-0331-466781

Italy - Padova Tel: 39-049-7625286

**Netherlands - Drunen** Tel: 31-416-690399 Fax: 31-416-690340

Norway - Trondheim Tel: 47-7288-4388

**Poland - Warsaw** Tel: 48-22-3325737

Romania - Bucharest Tel: 40-21-407-87-50

**Spain - Madrid** Tel: 34-91-708-08-90 Fax: 34-91-708-08-91

**Sweden - Gothenberg** Tel: 46-31-704-60-40

Sweden - Stockholm Tel: 46-8-5090-4654

**UK - Wokingham** Tel: 44-118-921-5800 Fax: 44-118-921-5820