

DESCRIPTION

The SD24C is designed for applications requiring transient overvoltage protection capability. They are intended for use in voltage and ESD sensitive equipment such as computers, printers, business machines, communication systems, medical equipment and other applications. These devices are ideal for situations where board space is at a premium.

This series has been specifically designed to protect sensitive components which are connected to power, data and transmission lines from caused ESD(electrostatic overvoltage by discharge), CDE (Cable Discharge Events), and EFT (electrical fast transients).

ORDERING INFORMATION

♦Package: SOD-323 ♦Material: Halogen free ♦Packing: Tape & Reel

♦Quantity per reel: 3,000pcs

FEATURES

- ♦IEC61000-4-2 (ESD) ±15kV (air), ±8kV (contact)
- ♦IEC61000-4-4 (EFT) 40A (5/50ns)
- ♦Protects one I/O line (bidirectional)
- ♦Low clamping voltage
- ♦Low leakage current

MACHANICAL DATA

- ♦SOD-323 package
- ♦Flammability Rating: UL 94V-0
- ♦Packaging: Tape and Reel
- ♦ High temperature soldering guaranted:260 °C/10s
- ♦Reel size: 7 inch


APPLICATIONS

- ♦ Cell Phone Handsets and Accessories
- Microprocessor based equipment
- ♦ Personal Digital Assistants (PDA's)
- ♦Notebooks, Desktops, and Servers
- ♦Portable Instrumentation
- ♦Networking and Telecom
- ♦ Serial and Parallel Ports.
- ♦Peripherals

PACKAGE OUTLINE



PIN CONFIGURATION







ABSOLUTE	ABSOLUTE MAXIMUM RATING							
Symbol	Parameter	Value	Units					
V _{ESD}	ESD per IEC 61000-4-2 (Air) ESD per IEC 61000-4-2 (Contact)	±15 ±8	kV					
P _{PP}	Peak Pulse Power (8/20µs)	350	W					
Т _{ОРТ}	Operating Temperature	-55/+150	°C					
T _{STG}	Storage Temperature	-55/+150	°C					
TL	Lead Soldering Temperature	260 (10 sec.)	°C					

ELECTRICAL CHARACTERISTICS (Tamb=25°C)									
PART NUMBER	DEVICE MARKING	V _{RWM} (V) (max.)	V _B (V) (min.)	Ι _τ (mA)	V _C @1A (V) (max.)	۷ (۷ (max.)		Ι _R (μΑ) (max.)	C⊤ (pF) (max.)
SD24C	2H	24.0	26.7	1	43.0	52.0	(@^) 7	1	50



ELECTRICAL CHARACTERISTICS CURVE





Pulse Waveform

Non-Repetitive Peak Pulse Power vs. Pulse Time

2

1.8 1.6

1.4 1.2

1.0 0.8


0.6 0.4 0.2

0

-25

-20

-15



Power Derating Curve



-10

 $Voltage-V_{R}(v)$


-5


5


0



SOD-323 PACKAGE OUTLINE DIMENSIONS







Symbol	Dimensions In Millimeters			
Symbol	Min	Max		
A		1.00		
A1	0.000	0.100		
A2	0.800	0.900		
b	0.250	0.350		
С	0.080	0.150		
D	1.200	1.400		
E	1.600	1.800		
E1	2.500	2.700		
е	1.800	2.040		
L	0.475 REF			
L1	0.250	0.400		
θ	0°	8°		

