

规格书 SPECIFICATION SHEET

Customer name:		
BERYL SERIES:	RC TYPE: RADIAL	
DESCRIPTION:	1000uF/16V Φ8*12	
Apply date :	2022-04-13	

BERYL			CUSTOMER	
P/N:RC016M102LO8*12TH-2B1	lEt	P/N:		
PREPARED	APPROVAL	PREPARED	CHECKED	APPROVAL
董桂茹				

After approved, please sign back 1 Approval Sheet before order. If not, we will treat it as tacitly acknowledged and accepted our relative standard and technical index.

Zhao Qing Beryl Electronic Technology Co., Ltd.

TEL: (0758) 13428556686 FAX: (0758) 2862870

E-mail: master@zq-beryl.com http://www.zq-beryl.com

NO.8 DUANZHOU ROAD, ZHAOQING CITY. GUANGDONG. CHINA

Sheet NO.: 20220413 Page : 1/12



Revise record

NO.	Date	Revise reason	Revise content	Prepared
01	2022.04.13	First issue	First issue	董桂茹

Sheet NO.: 20220413 Page: 2 / 12



860

18

1, Application

This specification applies to Aluminum electrolytic capacitor (foil type) used in electronic equipment. Designed capacitor's quality meets IEC 60384.

2. Table of specification and characteristics

≤160

Series	Cap(uF) 120Hz/20°C	WV(V)	Size	(mm)	Tempera (°C)	ture	Capacitance Tolerance	Life(hours) @105(°C)
	120112,20		D	L			1 ordrumed	W105(C)
RC	1000	16	8	12	-40~+105		±20%	2000
)(MAX) v/20°C	LC(µA)(N 2min/20	· · · · · · · · · · · · · · · · · · ·	,	2)(MAX) Hz/25°C	RC (mA rms) (MAX)105°C/100KHz		Surge voltage(V)


≤0.12

Other: /

3. Product Dimensions

Type

≤16




ФD	5	6.3	8	10	13	16	18	22
P	2	2.5	3.5	5	5	7.5	7.5	10
Фd	0.5	0.5	0.5/0.6	0.6	0.6	0.8	0.8	0.8
a			(L<20)	± 1.5	(L≥2	$0) \pm 2.0$		


Sheet NO.: 20220413 Page: 3 / 12



4. Part Number



5, Construction



Material name	Composition	Supplier name
Lead	Al and (Fe+Cu+Sn)	NM、JX
Rubber	EPT / IIR	LHX、LA、TH、LM2
Case	ase Aluminum OX, YJ, HL,	
Paper	Wood / Fibrous plant materials	KE、DF
Anode foil	$Al + Al_2O_3$	HY1、HY2、HF、HY3、 LD、FQ
Cathode foil	Aluminum	GY、LY1
Electrolyte	Glycol + Water +Ammonium salt	XZB、LM1、JZ2、FS
Sleeve PET		YL、CY


Sheet NO.: 20220413 Page: 4 / 12


BERYL 绿宝石

ALUMINUM ELECTROLYTIC CAPACITORS

6. Product Marking

Marking Sample:





Marking Details:

Capacitor shall be marked the following items:

- 1) Trademark (BERYL)
- 2) working voltage(16V)
- 3) Nominal capacitance(1000uF)
- 4) Cathode marked
- 5) Series symbol & Nominal capacitance tolerance (M: -20% ~ +20%)
- 6) Sleeve material(E: PET)

Maximum operating temperature(105°C)

7) Date code (2216)

22: Manufactured year 2022

Code	19	20	21	22	23	24	25	26	
Year	2019	2020	2021	2022	2023	2024	2025	2026	

16: Manufactured week (01, 02, 03, 04......52, 53)

Sheet NO.: 20220413 Page: 5 / 12



7. Characteristics

Standard atmospheric conditions

Unless other specified, the standard range of atmospheric conditions for making measurements and tests is as follows:

Ambient temperature : 15°C to 35°C
Relative humidity : 45% to 85%
Air pressure : 86kPa to 106kPa

If there is any doubt about the results, measurement shall be made within the following conditions:

Ambient temperature : $20^{\circ}\text{C} \pm 2^{\circ}\text{C}$ Relative humidity : 60% to 70%Air pressure : 86kPa to 106kPa

Operating temperature range

The ambient temperature range at which the capacitor can be operated continuously at rated voltage is $(6.3\sim450\mathrm{WV})$ -40°C to +105°C.

Table

	ITEM	PERFORMANCE
1	Nominal capacitance (Tolerance)	Condition> Measuring Frequency: 120Hz±12Hz Measuring Voltage: Not more than 0.5Vrms +1.5~2.0V.DC Measuring Temperature: 20±2°C Criteria> Shall be within the specified capacitance tolerance.
2	Leakage current	Condition> Connecting the capacitor with a protective resistor (1kΩ±10Ω) in series for 2 minutes, and then, measure leakage current. Criteria> I: Leakage current (μA) I (μA) ≤0.01CVor 3 (μA) whichever is greater, measurement circuit refer to right drawing. C: Capacitance (μF) V: Rated DC working voltage (V)
3	Dissipation factor	<condition> Nominal capacitance, for measuring frequency, voltage and temperature. <criteria> Must be within the parameters (See page 3)</criteria></condition>

Sheet NO.: 20220413 Page: 6 / 12



	ITEM				PERI	FORMA	NCE		
4	Impedance	Condition> Measuring frequency:100kHz; Measuring temperature:20±2°C Measuring point: 2mm max. from the surface of a sealing rubber on the lead wire. Criteria> (20°C) Must be within the parameters (See page 3)							
5	Load life test	Maximourrent exceed recove <criteria> The cha Leaka Capac Dissip</criteria>	ing to IEC60384 um operating ter for Rated life + the rated worki ring time at atm aracteristic shall age current citance Change pation Factor	mperatur 48/0hour ng voltag ospheric meet the Not With	e ±2°C wiss. (The sign of the	ith DC bitum of DC he products. The resign required the spector of initial a 200% of	as voltage p c and ripple ct should be sult should i ments. cified value. value. the specifie	peak voltage tested after 1 meet the follo	ripple shall not 6 hours
6	Shelf life test	The capa temp from leaka <criteria> The chara Leakage Capacit</criteria>	Appearance There shall be no leakage of electrolyte.					ors shall be remo	
7	Maximum permissible (ripple current, temperature coefficient)	applied a Table-3 The com voltage a Frequency	imum permissibut maximum operation de la maximum oper	D.C volta D.C volta Perse volt 120 0.60	mperature age and the age.	;			

Sheet NO.: 20220413 Page: 7 / 12



Sheet NO.: 20220413

ALUMINUM ELECTROLYTIC CAPACITORS

Page : 8 / 12

	ITEM	PERFORMANCE							
8	Terminal strength	Condition> Tensile strength of terminals Fixed the capacitor, applied for seconds. Bending strength of Fixed the capacitor, applied for 2~3 seconds, and then bent it is Diameter of lead wire 0.5mm and less 0.6~0.8 mm Criteria> No noticeable changes shall be	terminals. orce to bent or 90° to it Tensile (l) 10 (the termin s original perforce N (0.51) (1.02)	al (1~4 mmosition with Bending 2	n from the hin 2~3 set force N (I	rubber) for econds. kgf)	90° with	
		Condition> STEP Testing temperate 1 20±2 2 -40 -25±3 3 20±2		Time to re	Time each thermate ach thermate each the each thermate each thermate each thermate each thermate each the each thermate each thermate each thermate each the each thermate each the ea	al equilibr	ium		
9 Temperature characteristics		4 105±2 5 20±2 Capacitance, DF, and impeda Criteria> a. At +105°C, capacitance measure be a current measure be a current measure be a current shall be well as the control of the leakage current shall be well as the control of the leakage current shall not control of the control of the leakage current shall not control of the leakage current shall be well as the leakage current shall not control of the leakage current shall be well as the leakage current shall be well as the leakage current shall be well as the leakage current shall not control of the leakage cur	asured at +2 vithin the li ed shall no ured at +20 vithin the li ot more tha tio shall no	Time to ree measured 20°C shall mit of Item t more than °C shall be mit of Item n the specific	to be within ± 17.3 10 times of within ±10 17.3 Tied value.	al equilibrates 25% of its of its speci	s original va fied value. riginal value		
10	Surge test	Capacitance Change V Dissipation Factor N	5±0.5 minu hall be left Not more th Vithin ±159 Not more th	an the spec	5°C.Proceonal humidit ified value value. ified value	dure shall by for 1-2 b	be repeated	sistor in	
		Appearance T Attention: This test simulates over voltage voltage as often applied.	There shall ge at abnor				olicable to si	uch over	



	ITEM		PERFORMA	NCE			
		<condition> Temperature cycle: According to IEC60384-4 Naccording as below:</condition>	No.4.7 methods, capacito	r shall be placed in an oven, the condition			
		To	emperature	Time			
		(1) +20°C		3 Minutes			
	Change of	(2) Rated low tempera	ture (-40°C)(-25°C)	30±2 Minutes			
11	temperature test	(3) Rated high temper	ature (+105°C)	30±2 Minutes			
		(1) to (3) =1 cycle, tot	al 5 cycle				
		Criteria> The characteristic shall mee	t the following requirem	ent.			
		Leakage current	Not more than the s				
		Dissipation Factor	Not more than the s	specified value.			
		Appearance	There shall be no le	eakage of electrolyte.			
12	Damp heat test	<condition> Humidity test: According to IEC60384-4 N be exposed for 500±8 hours 40±2°C, the characteristic c <criteria> Leakage current Capacitance Change Dissipation Factor Appearance</criteria></condition>	nan atmosphere of 90~ hange shall meet the following. Not more than the special Within ±10% of initial	295%R H .at owing requirement. ecified value. al value. of the specified value.			
13	Solderability test	Condition> The capacitor shall be tested under the following conditions: Soldering temperature : 245 ±5°C Dipping depth : 2mm Dipping speed : 25±2.5mm/s Dipping time : 3±0.5s Criteria> Soldering wetting time Less than 3s Coating quality A minimum of 95% of the surface being immersed					

Sheet NO.: 20220413 Page: 9 / 12



	ITEM	PERFORMANCE							
14	Vibration test	Condition> The following conditions shall be applied for 2 hours in each 3 mutually perpendicular directions. Vibration frequency range: 10Hz ~ 55Hz each to peak amplitude: 1.5mm Sweep rate: 10Hz ~ 55Hz ~ 10Hz in about 1 minute Mounting method: The capacitor with diameter greater than 12.5mm or longer than 25mm must be fixed in place with a bracket. Within 30°							
		Criteria> To be soldered After the test, the following items shall be tested:							
		Inner construction No intermittent contacts, open or short circuiting. No damage of tab terminals or electrodes.							
		Appearance No mechanical damage in terminal. No leakage of electrolyte or swelling of the case. The markings shall be legible.							
	Resistance	Condition> Terminals of the capacitor shall be immersed into solder bath at 260±5°Cfor10±1seconds or400±10°Cfor3 ⁻⁰ seconds to 1.5~2.0 mm from the body of capacitor. Then the capacitor shall be left under the normal temperature and normal humidity for 1~2 hours before measurement. Criteria>							
15	to solder heat	Leakage current Not more than the specified value.							
	test	Capacitance Change Within ±5% of initial value.							
		Dissipation Factor Not more than the specified value.							
		Appearance There shall be no leakage of electrolyte.							
17	Vent	Condition> The following test only apply to those products with vent products at diameter ≥∅6.3 with vent. D.C. test The capacitor is connected with its polarity reversed to a DC power source. Then a current selected from Table 2 is applied. Table 2>							
16	test	Diameter (mm) DC Current (A)							
		22.4 or less 1							
		<criteria> The vent shall operate with no dangerous conditions such as flames or dispersion of pieces of the capacitor and/or case.</criteria>							

Sheet NO.: 20220413 Page: 10 / 12




8. Packing Information


Packing Label Marked (the following items shall be marked on the label) (Inside box or bag)

(1)Clint order number (2)Client part number (3)Beryl part number (4)Capacitance (5)Voltage (6)Dimension (7)Packaging quantity (8)Capacitance tolerance (9) QC Marking (10) Lot number (11) Series

LOT Number:




1) Bulk Packing:



3) Outer box



2) Taped Packing:



4) Outer box label:

		Ltd.		
C.S.R:				B. HO HE
C.S.R P/O:				KOHS HE
C.S.R P/N:				
S.P.R P/N:				QC
SPEC:				
QTY:	PCS	TOL:	%	
L/N:		S.P.R:		

Sheet NO.: 20220413 Page: 11 / 12



9. Prohibition to Use Environment- related Substances

We are hereby to certify the followings:

Our company hereby warrants and guarantees that all or part of products, including, but not limited to, the peripherals, accessories or package, delivered to your company (including your subsidiaries and affiliated companies) directly or indirectly by our company are free from any of the substances listed below.

The latest version of <Substances Prohibited as per RoHS or <Sony-SS-00259>

	Cadmium and cadmium compounds			
Accord with	Lead and lead compounds			
heavy metal	Mercury and mercury compounds			
	Hexavalent chromium compounds			
Organic chlorin compounds	Polychlorinated biphenyls (PCB)			
	Polychlorinated naphthalenes (PCN)			
	Polychlorinated terphenyls (PCT)			
	Chlorinated paraffins (CP)			
	Other chlorinated organic compounds			
Organic	Polybrominated biphenyls (PBB)			
bromine	Polybrominated diphenylethers (PBDE)			
compounds	Other brominated organic compounds			
Tributyltin compo	ounds			
Triphenyltin compounds				
Asbestos				
Specific azo compounds				
Formaldehyde				
Polyvinyl chloride (PVC) and PVC blends				
F、Cl、Br、I				
REACH				

Sheet NO.: 20220413 Page: 12 / 12