

规格书 SPECIFICATION SHEET

Customer name:			
BERYL SERIES:	RC	TYPE:	RADIAL
DESCRIPTION:	8.2uF/400V	Φ8*12	
Apply date :	2022-04-12		

BERYL		CUSTOMER				
P/N:RC400M8R2LO8*12TH-2B	1Et	P/N:				
PREPARED CHECKED	APPROVAL	PREPARED	CHECKED	APPROVAL		
董桂茹、工程部廖梅君						

After approved, please sign back 1 Approval Sheet before order. If not, we will treat it as tacitly acknowledged and accepted our relative standard and technical index.

Zhao Qing Beryl Electronic Technology Co., Ltd.

TEL: (0758) 13428556686 FAX: (0758) 2862870

E-mail: master@zq-beryl.com http://www.zq-beryl.com

NO.8 DUANZHOU ROAD, ZHAOQING CITY. GUANGDONG. CHINA

Sheet No.: 20220412 Page : 1/12



Revise record

NO.	Date	Revise reason	Revise content	Prepared
01	2022.04.12	First issue	First issue	董桂茹

Sheet No.: 20220412 Page : 2 / 12



1, Application

This specification applies to Aluminum electrolytic capacitor (foil type) used in electronic equipment. Designed capacitor's quality meets IEC 60384.

2. Table of specification and characteristics


Series	Cap(uF)	WV(V)	Size(mm)		Size(mm)		Temperature	Capacitance	Life(hours)
	120Hz/20°C		D	L	(°C)	Tolerance	@105(°C)		
RC	8.2	400	8	12	-40~ +105	±20%	5000		

DF (%)(MAX)	LC(μA)(MAX)	ESR(Ω)(MAX)	RC (mA rms)	Surge voltage(V)
120Hz/20°C	2min/20°C	100KHz/25°C	(MAX)105°C/100KHz	
≤20	≤76	-	225	440

Other: /

3. Product Dimensions

Type




ФD	5	6.3	8	10	13	16	18	22
P	2	2.5	3.5	5	5	7.5	7.5	10
Фd	0.5	0.5	0.5/0.6	0.6	0.6	0.8	0.8	0.8
a		$(L < 20) \pm 1.5$			(L≥2	$0) \pm 2.0$		


Sheet No.: 20220412 Page : 3 / 12



4. Part Number



5. Construction



Material name	Composition	Supplier name		
Lead	Al and (Fe+Cu+Sn)	NM、JX		
Rubber	EPT / IIR	LHX、LA、TH、LM2		
Case	Aluminum	OX、YJ、HL、LY2		
Paper	Wood / Fibrous plant materials	KE、DF		
Anode foil	$Al + Al_2O_3$	HY1、HY2、HF、HY3、 LD、FQ		
Cathode foil	Aluminum	GY、LY1		
Electrolyte	Glycol + Water +Ammonium salt	XZB、LM1、JZ2、FS		
Sleeve	PET	YL, CY		


Sheet No.: 20220412 Page: 4/12


BERYL 绿宝石

ALUMINUM ELECTROLYTIC CAPACITORS

6. Product Marking

Marking Sample:





Marking Details:

Capacitor shall be marked the following items:

- 1) Trademark (BERYL)
- 2) working voltage(400V)
- 3) Nominal capacitance(8.2uF)
- 4) Cathode marked
- 5) Series symbol & Nominal capacitance tolerance (M: -20% ~ +20%)
- 6) Sleeve material(E: PET)

Maximum operating temperature(105°C)

7) Date code (2216)

22: Manufactured year 2022

Code	19	20	21	22	23	24	25	26	
Year	2019	2020	2021	2022	2023	2024	2025	2026	

16: Manufactured week (01, 02, 03, 04......52, 53)

Sheet No.: 20220412 Page: 5 / 12



7. Characteristics

Standard atmospheric conditions

Unless other specified, the standard range of atmospheric conditions for making measurements and tests is as follows:

Ambient temperature : 15°C to 35°C
Relative humidity : 45% to 85%
Air pressure : 86kPa to 106kPa

If there is any doubt about the results, measurement shall be made within the following conditions:

Ambient temperature : $20^{\circ}\text{C} \pm 2^{\circ}\text{C}$ Relative humidity : 60% to 70%Air pressure : 86kPa to 106kPa

Operating temperature range

The ambient temperature range at which the capacitor can be operated continuously at rated voltage is $(6.3\sim450\mathrm{WV})$ -40°C to +105°C.

Table

	ITEM	PERFORMANCE
1	Nominal capacitance (Tolerance)	Condition> Measuring Frequency: 120Hz±12Hz Measuring Voltage: Not more than 0.5Vrms +1.5~2.0V.DC Measuring Temperature: 20±2°C Criteria> Shall be within the specified capacitance tolerance.
2	Leakage current	$ \begin{array}{l} \textbf{} \\ \textbf{Connecting the capacitor with a protective resistor } (1k\Omega\pm10\Omega) \text{ in series for} \\ \textbf{2 minutes, and then, measure leakage current.} \\ \textbf{} \\ \textbf{I: Leakage current } (\mu A) \\ \textbf{I} (\mu A) \leqslant 0.02\text{CV} + 10(\mu A) \text{ ,} \\ \textbf{measurement circuit refer to right drawing.} \\ \textbf{C: Capacitance } (\mu F) \\ \textbf{V: Rated DC working voltage } (V) \\ \end{array} $
3	Dissipation factor	<condition> Nominal capacitance, for measuring frequency, voltage and temperature. <criteria> Must be within the parameters (See page 3)</criteria></condition>

Sheet No.: 20220412 Page : 6 / 12



	ITEM			PERI	FORMAN	CE			
4	Impedance	<pre><condition> Measuring frequency:10 Measuring point: 2mm (<criteria></criteria></condition></pre>	max. from	the sur	face of a se		r on the lead	wire.	
5	Load life test	Maximum operating ten current for Rated life +4 exceed the rated working recovering time at atmost Criteria>	According to IEC60384-4No. 4.13 methods, the capacitor is stored at a temperature of Maximum operating temperature ±2°C with DC bias voltage plus the rated ripple current for Rated life +48/0hours. (The sum of DC and ripple peak voltage shall not exceed the rated working voltage) Then the product should be tested after 16 hours recovering time at atmospheric conditions. The result should meet the following table: **Criteria** The characteristic shall meet the following requirements. Leakage current Not more than the specified value. Capacitance Change Within ±20% of initial value. Dissipation Factor Not more than 200% of the specified value.						
6	Shelf life test	temperature±2°C for1 from the test chamber leakage current <criteria></criteria>	The capacitors are then stored with no voltage applied at a temperature of Maximum operating temperature±2°C for1000+48/0 hours. Following this period, the capacitors shall be removed from the test chamber and be allowed to stabilized at room temperature for16 hours. measure leakage current **Criteria** The characteristic shall meet the following requirements. Leakage current Not more than 200%of the specified value Capacitance Change Within ±20% of initial value. Dissipation Factor Not more than 200%of the specified value.						
7	Maximum permissible (ripple current, temperature coefficient)	applied at maximum oper Table-3 The combined value of D voltage and shall not reverse an	The maximum permissible ripple current is the maximum A.C current at 100kH applied at maximum operating temperature Table-3 The combined value of D.C voltage and the peak A.C voltage shall not exceed voltage and shall not reverse voltage. Tequency Multipliers: Freq (Hz) 120 1k 10k 100k Cap. (µF) 8.2 0.42 0.70 0.90 1.00 Temperature Coefficient: Temperature (°C) 60 85 95 105						

Sheet No.: 20220412 Page: 7 / 12



	ITEM					PER	FORM <i>A</i>	NCE				
8	Terminal strength	seconds. E Fixed the c 2~3 second Diame 0.5 Criteria>	d force to the terminal in lead out direction for 30+5-0 of terminals. d force to bent the terminal (1~4 mm from the rubber) for 90° verifies for 90° to its original position within 2~3 seconds.					· 90° within				
9	Temperature characteristics	a. At +105 Dissipat The leak b. In step 5 Dissipat The leak c. At -40°(Voltage (V)	Condition> STEP Testing temperature (°C) Time 1 20±2 Time to reach thermal equilibrium 2 -40 -25±3 Time to reach thermal equilibrium 3 20±2 Time to reach thermal equilibrium 4 105±2 Time to reach thermal equilibrium 5 20±2 Time to reach thermal equilibrium Capacitance, DF, and impedance shall be measured at 120Hz.									
10	Surge test	series for 30±; 1000 times. The before measur CR: Nomina Criteria> Leakage cut Capacitance Dissipation Appearance Attention:	Condition Applied a surge voltage to the capacitor connected with a (100 ±50)/CR (kΩ) resists series for 30±5 seconds in every 5±0.5 minutes at 15~35°C. Procedure shall be repeated 1000 times. Then the capacitors shall be left under normal humidity for 1-2 hours before measurement CR : Nominal Capacitance (μF)									

Sheet No.: 20220412 Page: 8 / 12



	ITEM		PERFORMA	NCE					
		<condition> Temperature cycle: According to IEC60384-4 N according as below:</condition>	Temperature cycle: According to IEC60384-4 No.4.7 methods, capacitor shall be placed in an oven,						
		Te	mperature	Time					
		(1) +20°C		3 Minutes					
	Change of	(2) Rated low tempera	ture (-40°C)(-25°C)	30±2 Minutes					
11	temperature test	(3) Rated high tempera	nture (+105°C)	30±2 Minutes					
		(1) to $(3) = 1$ cycle, total	al 5 cycle						
		Criteria> The characteristic shall meet Leakage current	the following requirem Not more than the						
		Dissipation Factor	Not more than the	specified value.					
			Appearance	There shall be no le	eakage of electrolyte.				
12	Damp heat test	According to IEC60384-4 N be exposed for 500±8 hours	Leakage current Not more than the specified value. Capacitance Change Within ±10% of initial value. Dissipation Factor Not more than 120% of the specified value.						
13	Solderability test	Soldering temperature : 24 Dipping depth : 25 Dipping speed : 2 Dipping time : 3± <criteria></criteria>	The capacitor shall be tested under the following conditions: Soldering temperature : 245 ±5°C Dipping depth : 2mm Dipping speed : 25±2.5mm/s Dipping time : 3±0.5s **Criteria> Soldering wetting time Less than 3s A minimum of 95% of the surface being						

Sheet No.: 20220412 Page: 9 / 12



ITEM		PERFORMANCE				
14	Vibration test	Condition> The following conditions shall be applied for 2 hours in each 3 mutually perpendicular directions. Vibration frequency range: 10Hz ~ 55Hz each to peak amplitude: 1.5mm Sweep rate: 10Hz ~ 55Hz ~ 10Hz in about 1 minute Mounting method: The capacitor with diameter greater than 12.5mm or longer than 25mm must be fixed in place with a bracket. Within 30° Within 30°				
		Critaria> To be soldered				
		Criteria> 10 be soldered After the test, the following items shall be tested:				
		Inner construction No intermittent contacts, open or short circuiting. No damage of tab terminals or electrodes.				
		Appearance No mechanical damage in terminal. No leakage of electrolyte or swelling of the case. The markings shall be legible.				
	Resistance to solder heat test	Condition> Terminals of the capacitor shall be immersed into solder bath at 260±5°Cfor10±1seconds or400±10°Cfor3 ⁻⁰ seconds to 1.5~2.0 mm from the body of capacitor. Then the capacitor shall be left under the normal temperature and normal humidity for 1~2 hours before measurement. Criteria>				
15		Leakage current Not more than the specified value.				
		Capacitance Change Within ±5% of initial value.				
		Dissipation Factor Not more than the specified value.				
		Appearance There shall be no leakage of electrolyte.				
16	Vent	Condition> The following test only apply to those products with vent products at diameter ≥Ø6.3 with vent. D.C. test The capacitor is connected with its polarity reversed to a DC power source. Then a current selected from Table 2 is applied. Table 2>				
16	test	Diameter (mm) DC Current (A)				
		22.4 or less 1				
		<criteria> The vent shall operate with no dangerous conditions such as flames or dispersion of pieces of the capacitor and/or case.</criteria>				

Sheet No.: 20220412 Page: 10 / 12




8. Packing Information


Packing Label Marked (the following items shall be marked on the label) (Inside box or bag)

(1)Clint order number (2)Client part number (3)Beryl part number (4)Capacitance (5)Voltage (6)Dimension (7)Packaging quantity (8)Capacitance tolerance (9) QC Marking (10) Lot number (11) Series

LOT Number:




1) Bulk Packing:



3) Outer box



2) Taped Packing:



4) Outer box label:

		Ltd.		
C.S.R:	B HA HE			
C.S.R P/O:		ROHS HE		
C.S.R P/N:	1			
S.P.R P/N:		QC		
SPEC:				
QTY:	PCS	TOL:	%	
L/N:		S.P.R:		

Sheet No.: 20220412 Page: 11 / 12



9. Prohibition to Use Environment- related Substances

We are hereby to certify the followings:

Our company hereby warrants and guarantees that all or part of products, including, but not limited to, the peripherals, accessories or package, delivered to your company (including your subsidiaries and affiliated companies) directly or indirectly by our company are free from any of the substances listed below.

The latest version of <Substances Prohibited as per RoHS or <Sony-SS-00259>

	Cadmium and cadmium compounds					
Accord with	Lead and lead compounds					
heavy metal	Mercury and mercury compounds					
	Hexavalent chromium compounds					
	Polychlorinated biphenyls (PCB)					
Oussuis ablasis	Polychlorinated naphthalenes (PCN)					
Organic chlorin	Polychlorinated terphenyls (PCT)					
compounds	Chlorinated paraffins (CP)					
	Other chlorinated organic compounds					
Organic	Polybrominated biphenyls (PBB)					
bromine	Polybrominated diphenylethers (PBDE)					
compounds	Other brominated organic compounds					
Tributyltin compounds						
Triphenyltin compounds						
Asbestos						
Specific azo compounds						
Formaldehyde						
Polyvinyl chloride (PVC) and PVC blends						
F、Cl、Br、I						
REACH						

Sheet No.: 20220412 Page: 12 / 12