

规格书 SPECIFICATION SHEET

Customer name:			
BERYL SERIES:	RG	TYPE:	RADIAL
DESCRIPTION:	2200uF/35V	Ф13*30	
Apply date :	2022-04-13		

BERYL			CUSTOMER	R
P/N:RG035M222LO13*30TA-1	P/N:			
PREPARED	APPROVAL	PREPARED	CHECKED	APPROVAL
董桂茹工學梅君	张业维			

After approved, please sign back 1 Approval Sheet before order. If not, we will treat it as tacitly acknowledged and accepted our relative standard and technical index.

Zhao Qing Beryl Electronic Technology Co., Ltd.

TEL: (0758) 13428556686 FAX: (0758) 2862870

E-mail: master@zq-beryl.com http://www.zq-beryl.com

NO.8 DUANZHOU ROAD, ZHAOQING CITY. GUANGDONG. CHINA

Sheet NO.: 20220413 Page: 1/12



Revise record

NO.	Date	Revise reason	Revise content	Prepared
01	2022.04.13	First issue	First issue	董桂茹

Sheet NO.: 20220413 Page : 2 / 12



1, Application

This specification applies to Aluminum electrolytic capacitor (foil type) used in electronic equipment. Designed capacitor's quality meets IEC 60384.

2. Table of specification and characteristics


Series	Cap(uF) 120Hz/20°C	WV(V)	Size ((mm)	Temperature (°C)	Capacitance Tolerance	Life(hours) @105(°C)
	120112/20		D L			Toterunce	@100(3)
RG	2200	35	13	30	-40~+105	±20%	10000

DF (%)(MAX)	LC(μA)(MAX)	ESR(Ω)(MAX)	RC (mA rms)	Surge voltage(V)
120Hz/20°C	2min/20°C	100KHz/25°C	(MAX)105°C/100KHz	
≤14	≤770	≤0.065	3032	40

Other: /

3. Product Dimensions

Type




ФD	5	6.3	8	10	13	16	18	22
P	2	2.5	3.5	5	5	7.5	7.5	10
Фd	0.5	0.5	0.5/0.6	0.6	0.6	0.8	0.8	0.8
а			(L<20)	± 1.5	(L≥2	$0) \pm 2.0$		


Sheet NO.: 20220413 Page: 3 / 12



4. Part Number



5. Construction



Material name	Composition	Supplier name
Lead	Al and (Fe+Cu+Sn)	NM、JX
Rubber	EPT / IIR	LHX、LA、TH、LM2
Case	Aluminum	OX、YJ、HL、LY2
Paper	Wood / Fibrous plant materials	KE、DF
Anode foil	$Al + Al_2O_3$	HY1、HY2、HF、HY3、 LD、FQ
Cathode foil	Aluminum	GY、LY1
Electrolyte Glycol + Water +Ammonium salt		XZB、LM1、JZ2、FS
Sleeve	PET	YL, CY

Sheet NO.: 20220413 Page: 4/12

BERYL 绿宝石

ALUMINUM ELECTROLYTIC CAPACITORS

6. Product Marking

Marking Details:

Capacitor shall be marked the following items:

- 1) Trademark (BERYL)
- 2) working voltage(35V)
- 3) Nominal capacitance(2200uF)
- 4) Cathode marked
- 5) Series symbol & Nominal capacitance tolerance (M: -20% ~ +20%)
- 6) Sleeve material(E: PET)

Maximum operating temperature(105°C)

7) Date code (2216)

22: Manufactured year 2022

Code	20	21	22	23	24	25	26	27	
Year	2020	2021	2022	2023	2024	2025	2026	2027	

16: Manufactured week (01, 02, 03, 04......52, 53)

Sheet NO.: 20220413 Page: 5 / 12



7. Characteristics

Standard atmospheric conditions

Unless other specified, the standard range of atmospheric conditions for making measurements and tests is as follows:

Ambient temperature : 15°C to 35°C
Relative humidity : 45% to 85%
Air pressure : 86kPa to 106kPa

If there is any doubt about the results, measurement shall be made within the following conditions:

Ambient temperature : $20^{\circ}\text{C} \pm 2^{\circ}\text{C}$ Relative humidity : 60% to 70%Air pressure : 86kPa to 106kPa

Operating temperature range

The ambient temperature range at which the capacitor can be operated continuously at rated voltage is $(6.3\sim100 \text{WV})$ -40°C to +105°C.

Table

	ITEM	PERFORMANCE
1	Nominal capacitance (Tolerance)	<condition> Measuring Frequency: 120Hz±12Hz Measuring Voltage: Not more than 0.5Vrms +1.5~2.0V.DC Measuring Temperature: 20±2°C <criteria> Shall be within the specified capacitance tolerance.</criteria></condition>
2	Leakage current	Condition> Connecting the capacitor with a protective resistor (1kΩ±10Ω) in series for 2 minutes, and then, measure leakage current. Criteria> I: Leakage current (μA) I (μA) ≤ 0.01CVor 3 (μA) whichever is greater, measurement circuit refer to right drawing. C: Capacitance (μF) V: Rated DC working voltage (V)
3	Dissipation factor	<condition> Nominal capacitance, for measuring frequency, voltage and temperature. <criteria> Must be within the parameters (See page 3)</criteria></condition>

Sheet NO.: 20220413 Page: 6 / 12



	ITEM		PF	ERFORMAN	NCE			
4	Impedance	Condition> Measuring frequency:100kHz; Measuring temperature:20±2°C Measuring point: 2mm max. from the surface of a sealing rubber on the lead wire. Criteria> (20°C) Must be within the parameters (See page 3)						
5	Load life test	Condition> According to IEC6038 Maximum operating to current for Rated life acceed the rated work recovering time at atm Criteria> The characteristic shall Leakage current Capacitance Change Dissipation Factor Appearance	emperature ±2°C -48/0hours. (Thing voltage) The hospheric condit meet the follow Not more to Within ±25 Not more to	with DC big e sum of DC en the productions. The res	as voltage pland ripple pot should be full that should mannerts. If if it is a value. If it is a value.	us the rated ripleak voltage shested after 16 eet the follow	ople nall not hours	
6	Shelf life test	<condition> The capacitors are then temperature±2°C fo from the test chamb leakage current <criteria> The characteristic shall in Leakage current Capacitance Change Dissipation Factor Appearance</criteria></condition>	neet the following Not more the Within ±25 Not more the Not more than Not more tha	rs. Following ed to stabilize	ents. the specified value. the specified	the capacitors emperature for value.	shall be removed	
7	Maximum permissible (ripple current, temperature coefficient)	Condition> The maximum permissi applied at maximum op Table-3 The combined value of voltage and shall not reserved. Frequency Multipliers: Freq (Fap. (μF) 2200 Temperature Coefficient Temperature (°C) Factor	D.C voltage and verse voltage. Hz) 120 0.75	ure				

Sheet NO.: 20220413 Page: 7 / 12



Sheet NO.: 20220413

ALUMINUM ELECTROLYTIC CAPACITORS

Page : 8 / 12

	ITEM		PER	FORMAN	CE		
8 Terminal strength		seconds. Bending streng Fixed the capacitor, appli 2~3 seconds, and then be Diameter of lead win 0.5mm and less 0.6~0.8 mm	the deferred to the tenth of terminals. The deferred to be more to be more than the deferred to the tenth of terminals. The deferred to the tenth of the deferred to the deferred	ed force to the terminal in lead out direction for 30+5-0 in of terminals. ed force to bent the terminal (1~4 mm from the rubber) for 90 it it for 90° to its original position within 2~3 seconds.			per) for 90° within ls.
9	Temperature characteristics	1 20 2 -40 3 20 4 10 5 20 Capacitance, DF, and in <criteria> a. At +105°C, capacitance Dissipation factor shal The leakage current m b. In step 5, capacitance of Dissipation factor shal The leakage current shal</criteria>	e measured at + l be within the l easured shall no measured at +20 l be within the l all not more tha	Time to re Time to re Time to re Time to re e measured 20°C shall be imit of Item t more than 1°C shall be imit of Item n the specif t exceed the	ach thermal ach thermal ach thermal ach thermal at 120Hz. The within ±2 7.3 ach times of within ±10% 7.3 and the solution in	its specified 6 of its origin	value. al value.
10	Surge test	<condition> Applied a surge volta series for 30±5 seconds in evaluation 1000 times. Then the capacities before measurement CR: Nominal Capacitance <criteria> Leakage current Capacitance Change Dissipation Factor Appearance Attention: This test simulates over woltage as often applied.</criteria></condition>	wery 5±0.5 minutors shall be left (μF) Not more than Within ±15% Not more than There shall be	ttes at 15~35 under norm the specifi of initial van the specifi e no leakage	ed value. lue. ed value. of electroly	for 1-2 hours	peated



	ITEM		PERFORMA	NCE	
		<condition> Temperature cycle: According to IEC60384-4 No according as below:</condition>	o.4.7 methods, capacito	r shall be placed in an over	n, the condition
			nperature	Time	
		(1) +20°C		3 Minutes	
	Change of	(2) Rated low temperatu	are (- 40°C) (-25°C)	30±2 Minutes	
11	1 temperature test	(3) Rated high temperat	ure (+105°C)	30±2 Minutes	
		(1) to (3) =1 cycle, total	5 cycle		
		Criteria> The characteristic shall meet to be a characteristic shal	the following requirem Not more than the		
		Dissipation Factor		_	
		Appearance	Not more than the specified value. There shall be no leakage of electrolyte.		
12	Damp heat test	be exposed for 500±8 hours in 40±2°C, the characteristic character		owing requirement.	
		Capacitance Change	Within ±10% of initia	al value.	
		Dissipation Factor	Not more than 120%	of the specified value.	
		Appearance	There shall be no leal	kage of electrolyte.	
13	Solderability test	Dipping depth : 2m Dipping speed : 25	5 ±5°C nm ±2.5mm/s 0.5 s Less than 3s	nditions: % of the surface being	

Sheet NO.: 20220413 Page: 9 / 12



ITEM		PERFORMANCE				
14	Vibration test	Condition> The following conditions shall be applied for 2 hours in each 3 mutually perpendicular directions. Vibration frequency range: 10Hz ~ 55Hz each to peak amplitude: 1.5mm Sweep rate: 10Hz ~ 55Hz ~ 10Hz in about 1 minute Mounting method: The capacitor with diameter greater than 12.5mm or longer than 25mm must be fixed in place with a bracket. Within 30° After the test, the following items shall be tested:				
		Inner construction No intermittent contacts, open or short circuiting. No damage of tab terminals or electrodes. No mechanical damage in terminal. No leakage of electrolyte or swelling of the case. The markings shall be legible.				
	Resistance to solder heat test	Condition> Terminals of the capacitor shall be immersed into solder bath at 260±5°Cfor10±1seconds or400±10°Cfor3 -0 seconds to 1.5~2.0 mm from the body of capacitor. Then the capacitor shall be left under the normal temperature and normal humidity for 1~2 hours before measurement. Criteria>				
15		Leakage current Not more than the specified value.				
		Capacitance Change Within ±5% of initial value.				
		Dissipation Factor Not more than the specified value.				
		Appearance There shall be no leakage of electrolyte.				
16	Vent	Condition> The following test only apply to those products with vent products at diameter ≥∅6.3 with vent. D.C. test The capacitor is connected with its polarity reversed to a DC power source. Then a current selected from Table 2 is applied. Table 2>				
	test	Diameter (mm) DC Current (A) 22.4 or less 1 <criteria> The vent shall operate with no dangerous conditions such as flames or dispersion of pieces of the capacitor and/or case.</criteria>				

Sheet NO.: 20220413 Page: 10 / 12




8. Packing Information


Packing Label Marked (the following items shall be marked on the label) (Inside box or bag)

(1)Clint order number (2)Client part number (3)Beryl part number (4)Capacitance (5)Voltage (6)Dimension (7)Packaging quantity (8)Capacitance tolerance (9) QC Marking (10) Lot number (11) Series

LOT Number:




1) Bulk Packing:



3) Outer box



2) Taped Packing:



4) Outer box label:

C.S.R:			- 110 110
C.S.R P/O:	ROHS HE		
C.S.R P/N:			
S.P.R P/N:	QC		
SPEC:			
QTY: PCS	TOL:	%	
L/N:	S.P.R:		

Sheet NO.: 20220413 Page: 11 / 12



9. Prohibition to Use Environment- related Substances

We are hereby to certify the followings:

Our company hereby warrants and guarantees that all or part of products, including, but not limited to, the peripherals, accessories or package, delivered to your company (including your subsidiaries and affiliated companies) directly or indirectly by our company are free from any of the substances listed below.

The latest version of <Substances Prohibited as per RoHS or <Sony-SS-00259>

	Cadmium and cadmium compounds					
	1					
Accord with	Lead and lead compounds					
heavy metal	Mercury and mercury compounds					
	Hexavalent chromium compounds					
	Polychlorinated biphenyls (PCB)					
Oncomio ablania	Polychlorinated naphthalenes (PCN)					
Organic chlorin	Polychlorinated terphenyls (PCT)					
compounds	Chlorinated paraffins (CP)					
	Other chlorinated organic compounds					
Organic	Polybrominated biphenyls (PBB)					
bromine	Polybrominated diphenylethers (PBDE)					
compounds	Other brominated organic compounds					
Tributyltin compounds						
Triphenyltin compounds						
Asbestos						
Specific azo compounds						
Formaldehyde						
Polyvinyl chloride (PVC) and PVC blends						
F、Cl、Br、I						
REACH						

Sheet NO.: 20220413 Page: 12 / 12