


Technical Data Sheet

Infrared Remote-control Receiver Module

IRM-3636

Features

- High data rate (up to 4000 bit/sec)
- · High protection ability against EMI.
- Circular lens to improve the receive characteristic.
- Line-up for various center carrier frequencies.
- Low voltage and low power consumption.
- · High immunity against ambient light.
- Photodiode with integrated circuit.
- TTL and CMOS compatibility.
- Long reception distance.
- High sensitivity.
- Suitable min. burst length ≥ 6 or 10 pulses/burst.
- · Pb free.
- The product itself will remain within RoHS compliant version.



• The device is a miniature type infrared remote control system receiver which has been developed and designed by utilizing the most updated IC technology. The PIN diode and preamplifier are assembled on lead frame, the epoxy package is designed as an IR filter. The demodulated output signal can directly be decoded by a microprocessor.

Applications

- Light detecting portion of remote control
- AV instruments such as Audio, TV, VCR, CD, MD, etc.
- Home appliances such as Air-conditioner, Fan, etc.
- The other equipments with wireless remote control.
- CATV set top boxes
- Multi-media Equipment


PART	MATERIAL	COLOR	
Chip	Silicon		
Compound	Ероху	Black	

Everlight Electronics Co., Ltd. http:\\www.everlight.com Rev 1 Page: 1 of 9

Device No: SZDMO-036-045 Prepared date: 21-Jun-06 Prepared by: Meijuan Zhang

IRM-3636

Package Dimensions



Notes: 1.All dimensions are in millimeters.

2. Tolerances unless dimensions ±0.3mm.

Absolute Maximum Ratings (Ta=25°C)

Parameter	Symbol	Rating	Unit	Notice
Supply Voltage	Vcc	0 ~ 6	V	
Operating Temperature	Topr	-25 ~ +85	$^{\circ}\mathbb{C}$	
Storage Temperature	Tstg	-40 ~ +85	$^{\circ}\mathbb{C}$	
Soldering Temperature	Tsol	260	$^{\circ}\!\mathbb{C}$	4mm from mold body less than 10 seconds

Everlight Electronics Co., Ltd.

Device No: SZDMO-036-045

http:\\www.everlight.com Prepared date : 21-Jun-06 Rev 1

Page: 2 of 9

Prepared by : Meijuan Zhang



IRM-3636

Recommended Operating Condition

Supply Voltage Rating: Vcc 2.7V to 5.5V

Electro-Optical Characteristics (Ta=25°C, and Vcc=3.0V)

Parameter	Symbol	MIN.	TYP.	MAX.	Unit	Condition	
Consumption Current	Icc			2	mA	No signal input	
B.P.F Center Frequency	Fo		36		KHz		
Peak Wavelength	λp		940		nm		
Reception Distance	L_0	14			m		
	L_{45}	6					
Half Angle(Horizontal)	Θ_{h}		45		deg	At the ray axis *1	
Half Angle(Vertical)	Θ_{v}		45		deg		
High Level Pulse Width	T_{H}	400		800	μ s	At the ray axis	
Low Level Pulse Width	T_{L}	400		800	μ s	*2	
High Level Output Voltage	V_{H}	2.7			V		
Low Level Output Voltage	V_{L}		0.2	0.5	V		

Notes:

Everlight Electronics Co., Ltd. http://www.everlight.com Rev 1 Page: 3 of 9

Device No: SZDMO-036-045 Prepared date: 21-Jun-06 Prepared by: Meijuan Zhang

^{*1:}The ray receiving surface at a vertex and relation to the ray axis in the range of θ = 0° and θ =45°.

^{*2:}A range from 30cm to the arrival distance. Average value of 50 pulses.

IRM-3636

Test Method:

The specified electro-optical characteristics is satisfied under the following Conditions at the controllable distance.

①Measurement place

A place that is nothing of extreme light reflected in the room.

②External light

Project the light of ordinary white fluorescent lamps which are not high Frequency lamps and must be less then 10 Lux at the module surface. (Ee \leq 10Lux)

Standard transmitter


A transmitter whose output is so adjusted as to **Vo=400mVp-p** and the output Wave form shown in Fig.-1.According to the measurement method shown in Fig.-2 the standard transmitter is specified.

However , the infrared photodiode to be used for the transmitter should be $\lambda p=940$ nm, $\Delta\lambda=50$ nm. Also, photodiode is used of PD438B(Vr=5V). (Standard light / Light source temperature 2856°K).

Measuring system

According to the measuring system shown in Fig.-3

Block Diagram:




Everlight Electronics Co., Ltd. http:\\www.everlight.com Rev 1 Page: 4 of 9

Device No: SZDMO-036-045 Prepared date: 21-Jun-06 Prepared by: Meijuan Zhang

IRM-3636

Application Circuit:



RC Filter should be connected closely between Vcc pin and GND pin.

Fig.-1 Transmitter Wave Form

D.U.T output Pulse





Fig.-2 Measuring Method

Fig.-3 Measuring System



Everlight Electronics Co., Ltd. http://www.everlight.com Rev 1 Page: 5 of 9

Device No: SZDMO-036-045 Prepared date: 21-Jun-06 Prepared by: Meijuan Zhang

IRM-3636

Typical Electro-Optical Characteristics Curves

Fig.-4 Relative Spectral Sensitivity vs.

Wavelength

100 \lesssim 90 Relative Responsitibity 80 70 60 50 40 30 20 10 0 700 800 900 1000 1100 600 Wavelength (nm)

Fig.-5 Relative Transmission Distance vs.






Fig.-6 Output Pulse Length vs. Arrival Distance Fig.-7 Arrival Distance vs. Supply Voltage





Everlight Electronics Co., Ltd. Device No: SZDMO-036-045

http:\\www.everlight.com Prepared date : 21-Jun-06 Rev 1

Page: 6 of 9


Prepared by : Meijuan Zhang


IRM-3636

Typical Electro-Optical Characteristics Curves

Fig.-8 Relative Transmission Distance vs. Center Carrier Frequency

Fig.-9 Arrival Distance vs. Ambient Temperature





Everlight Electronics Co., Ltd. http://www.everlight.com Rev 1 Page: 7 of 9

Device No: SZDMO-036-045 Prepared date: 21-Jun-06 Prepared by: Meijuan Zhang



IRM-3636

Reliability Test Item And Condition

The reliability of products shall be satisfied with items listed below.

Confidence level: 90%

LTPD: 10%

Test Items	Test Conditions	Failure Judgement Criteria	Samples(n) Defective(c)
Temperature cycle	1 cycle -40° C \longrightarrow $+100^{\circ}$ C $(15\text{min})(5\text{min})(15\text{min})$ 300 cycle test		n=22,c=0
High temperature test	Temp: +100°C Vcc:6V 1000hrs	$egin{array}{ccc} L_0 &\leq & Lx0.8 \ L_{45} &\leq & Lx0.8 \end{array}$	n=22,c=0
Low temperature storage	Temp: -40°C 1000hrs	L: Lower	n=22,c=0
High temperature High humidity	Ta: 85°C,RH:85% 1000hrs	specification limit	n=22,c=0
Solder heat	Temp: 260±5°C 10sec 4mm From the bottom of the package.		n=22,c=0

Everlight Electronics Co., Ltd. http:\\www.everlight.com Rev 1 Page: 8 of 9

Device No: SZDMO-036-045 Prepared date: 21-Jun-06 Prepared by: Meijuan Zhang




IRM-3636

Packing Quantity Specification

- 1. 1500PCS/1Box
- 2. 10Boxes/1Carton

Label Form Specification



CPN: Customer's Production Number

P/N : Production Number QTY: Packing Quantity

CAT: Ranks

HUE: Peak Wavelength

REF: Reference

LOT No: Lot Number

MADE IN TAIWAN: Production Place

Notes

- 1. Above specification may be changed without notice. EVERLIGHT will reserve authority on material change for above specification.
- 2. When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
- 3. These specification sheets include materials protected under copyright of EVERLIGHT corporation. Please don't reproduce or cause anyone to reproduce them without EVERLIGHT's consent.

EVERLIGHT ELECTRONICS CO., LTD.

Office: No 25, Lane 76, Sec 3, Chung Yang Rd, Tucheng, Taipei 236, Taiwan, R.O.C Tel: 886-2-2267-2000, 2267-9936

Fax: 886-2267-6244, 2267-6189, 2267-6306

http:\\www.everlight.com

Everlight Electronics Co., Ltd. http:\\www.everlight.com Rev 1 Page: 9 of 9

Device No: SZDMO-036-045 Prepared date: 21-Jun-06 Prepared by: Meijuan Zhang