

600nA 14.5KHZ CMOS Rail-to-Rail IO Opamp with RF Filter

Features

- Single-Supply Operation from +1.4V ~ +5.5V
- Rail-to-Rail Input / Output
- Gain-Bandwidth Product: 14.5KHz (Typ)
- Low Input Bias Current: 1pA (Typ)
- Low Offset Voltage: 3mV (Max)
- Quiescent Current: 600nA per Amplifier (Typ)
- Chip Select with HGV6043NH(active High) and HGV6043NL(active Low)
- **General Description**

- Operating Temperature: -40°C ~ +125°C
- Embedded RF Anti-EMI Filter
- Small Package:

HGV6041 Available in SOT23-5 and SC70-5 Packages HGV6042 Available in SOP-8 and MSOP-8 Packages HGV6043NH Available in SOT23-6 and SC70-6 Packages HGV6043NL Available in SOT23-6 and SC70-6 Packages


The HGV604X family has a high gain-bandwidth product of 14.5KHz, a slew rate of 6V/ms, and a quiescent current of 600nA/amplifier at 5V. The HGV604X family is designed to provide optimal performance in low voltage and low noise systems. They provide rail-to-rail output swing into heavy loads. The input common mode voltage range includes ground, and the maximum input offset voltage is 3mV for HGV604X family. They are specified over the extended industrial temperature range (-40°C to +125°C). The operating range is from 1.4V to 5.5V. The HGV6041 single is available in Green SC70-5 and SOT23-5 packages. The HGV6042 Dual is available in Green SOP-8 and MSOP-8 packages. The HGV6043 single is available in Green SC70-6 and SOT23-6 packages.

Applications

- ASIC Input or Output Amplifier
- Sensor Interface
- Medical Communication
- Smoke Detectors

Pin Configuration

- Audio Output
- Piezoelectric Transducer Amplifier
- Medical Instrumentation
- Portable Systems







ORDERING INFORMATION

DEVICE	Package Type	MARKING	Packing	Packing Qty	
HGV6041M5/TR	SOT23-5	6041	REEL	3000pcs/reel	
HGV6041M7/TR	SC70-5	6041	REEL	3000pcs/reel	
HGV6042M/TR	SOP8L	HGV6042	REEL	2500pcs/reel	
HGV6042MM/TR	MSOP8L	HGV6042	REEL	3000pcs/reel	
HGV6043NHM6/TR	SOT23-6	043H	REEL	3000pcs/reel	
HGV6043NHM7/TR	SC70-6	043H	REEL	3000pcs/reel	
HGV6043NLM6/TR	SOT23-6	043L	REEL	3000pcs/reel	
HGV6043NLM7/TR	SC70-6	043L	REEL	3000pcs/reel	

Absolute Maximum Ratings

Condition	Min	Мах		
Power Supply Voltage (V _{DD} to Vss)	-0.5V	+7.5V		
Analog Input Voltage (IN+ or IN-)	Vss-0.5V	V _{DD} +0.5V		
PDB Input Voltage	Vss-0.5V	+7V		
Operating Temperature Range	-40°C	+125°C		
Junction Temperature	+160°C			
Storage Temperature Range	-55°C	+150°C		
Lead Temperature (soldering, 10sec)	+260°C			
Package Thermal Resistance (T _A =+25℃)				
SOP-8, θ _{JA}	125°C/W			
MSOP-8, θ _{JA}	216°C/W			
SOT23-5, θ _{JA}	190°C/W			
SOT23-6, θ _{JA}	190°C/W			
SC70-5, θ _{JA}	333°C/W			
SC70-6, θ _{JA}	333°C/W			
ESD Susceptibility				
НВМ	6KV			
MM	300V			

Note: Stress greater than those listed under Absolute Maximum Ratings may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any other conditions outside those indicated in the operational sections of this specification are not implied. Exposure to absolute maximum rating conditions for extended periods may affect reliability.



Electrical Characteristics


(At Vs = +5V, RL = $1M\Omega$ connected to Vs/2, and Vout = Vs/2, unless otherwise noted.)


DADAMETED	SYMBOL	CONDITIONS	HGV6041/6042/6043			
PARAMETER			ТҮР	MIN	МАХ	UNITS
INPUT CHARACTERISTICS						•
Input Offset Voltage	Vos	$V_{CM} = V_S/2$	0.4		3	mV
Input Bias Current	I _B		1			pА
Input Offset Current	los		1			pА
Common-Mode Voltage Range	V _{CM}	V _S = 5.5V	-0.1 to +5.6			V
Common-Mode Rejection Ratio	CMRR	$V_{\rm S}$ = 5V, $V_{\rm CM}$ = -0.1V to 2.5V	78	66		dB
		$V_{\rm S}$ = 5V, $V_{\rm CM}$ = -0.1V to 5.1V	84	67		
Open-Loop Voltage Gain	A _{OL}	$Vs=1.4V, R_L = 50k\Omega, V_O = Vs-0.1V$	86	75		dB
		Vs=5V, R_L = 50k Ω , V_O = Vs-0.1V	93	84		
Input Offset Voltage Drift	$\Delta V_{OS} / \Delta_T$		2.5			µV/°C
OUTPUT CHARACTERISTICS						
Output Voltage Swing from Rail	V _{он}	Vs=1.4V, R _L = 50kΩ	1.395	1.390		V
	V _{OL}		4.5		10	mV
	V _{OH}	Vs=5V, R _L = 50kΩ	4.997	4.990		V
	V _{OL}		3.5		10	mV
Output Current	I _{SOURCE}	R_L = 10 Ω to V _S /2	20			- mA
	I _{SINK}		20			
POWER SUPPLY						•
Operating Voltage Range			1.4			V
			5.5			V
Power Supply Rejection Ratio	PSRR	$V_{\rm S}$ = +1.4V to +5.5V, $V_{\rm CM}$ = +0.5V	80	77		dB
Quiescent Current / Amplifier	Ι _Q		600			nA
Shutdown Current / Amplifier	I _{Q_off}	HGV6043NH / HGV6043NL	54			nA
DYNAMIC PERFORMANCE (CL	= 100pF)				•	
Gain-Bandwidth Product	GBP		14.5			KHz
Slew Rate	SR	G = +1, 2V Output Step	6			V/ms
	•	•			•	•



Typical Performance characteristics

At T_A =+25°C, V_S =+5V, and R_L =100K Ω connected to V_S /2, unless otherwise noted.







Large Signal Non-Inverting Pulse Response

Time(10ms/div)

Time(10ms/div) Small Signal Inverting Pulse Response



Small Signal Non-Inverting Pulse Response




Time(10ms/div)



Typical Performance characteristics

At T_A =+25°C, V_S =+5V, and R_L =100K Ω connected to V_S /2, unless otherwise noted.





Application Note

Size

HGV604X family series op amps are unity-gain stable and suitable for a wide range of general-purpose applications. The small footprints of the HGV604X family packages save space on printed circuit boards and enable the design of smaller electronic products.

Power Supply Bypassing and Board Layout

HGV604X family series operates from a single 1.4V to 5.5V supply or dual $\pm 0.7V$ to $\pm 2.75V$ supplies. For best performance, a 0.1µF ceramic capacitor should be placed close to the V_{DD} pin in single supply operation. For dual supply operation, both V_{DD} and V_{SS} supplies should be bypassed to ground with separate 0.1µF ceramic capacitors.

Low Supply Current

The low supply current (typical 600nA per channel) of HGV604X family will help to maximize battery life. They are ideal for battery powered systems.

Operating Voltage

HGV604X family operates under wide input supply voltage (1.4V to 5.5V). In addition, all temperature specifications apply from -40 °C to +125 °C. Most behavior remains unchanged throughout the full operating voltage range. These guarantees ensure operation throughout the single Li-lon battery lifetime.

Rail-to-Rail Input

The input common-mode range of HGV604X family extends 100mV beyond the supply rails (V_{SS} -0.1V to V_{DD} +0.1V). This is achieved by using complementary input stage. For normal operation, inputs should be limited to this range.

Rail-to-Rail Output

Rail-to-Rail output swing provides maximum possible dynamic range at the output. This is particularly important when operating in low supply voltages. The output voltage of HGV604X family can typically swing to less than 50mV from supply rail in light resistive loads (> $50k\Omega$).

Capacitive Load Tolerance

The HGV604X family is optimized for bandwidth and speed, not for driving capacitive loads. Output capacitance will create a pole in the amplifier's feedback path, leading to excessive peaking and potential oscillation. If dealing with load capacitance is a requirement of the application, the two strategies to consider are (1) using a small resistor in series with the amplifier's output and the load capacitance and (2) reducing the bandwidth of the amplifier's feedback loop by increasing the overall noise gain. Figure 2. shows a unity gain follower using the series resistor strategy. The resistor isolates the output from the capacitance and, more importantly, creates a zero in the feedback path that compensates for the pole created by the output capacitance.




Figure 2. Indirectly Driving a Capacitive Load Using Isolation Resistor



The bigger the R_{ISO} resistor value, the more stable V_{OUT} will be. However, if there is a resistive load R_L in parallel with the capacitive load, a voltage divider (proportional to R_{ISO}/R_L) is formed, this will result in a gain error.

The circuit in Figure 3 is an improvement to the one in Figure 2. R_F provides the DC accuracy by feed-forward the V_{IN} to R_L . C_F and R_{ISO} serve to counteract the loss of phase margin by feeding the high frequency component of the output signal back to the amplifier's inverting input, thereby preserving the phase margin in the overall feedback loop. Capacitive drive can be increased by increasing the value of C_F . This in turn will slow down the pulse response.




Figure 3. Indirectly Driving a Capacitive Load with DC Accuracy



Typical Application Circuits

Differential amplifier

The differential amplifier allows the subtraction of two input voltages or cancellation of a signal common the two inputs. It is useful as a computational amplifier in making a differential to single-end conversion or in rejecting a common mode signal. Figure 4. shown the differential amplifier using HGV604X family.




Figure 4. Differential Amplifier

$$V_{\text{OUT}} = \left(\frac{R_1 + R_2}{R_3 + R_4}\right) \frac{R_4}{R_1} V_{\text{IN}} - \frac{R_2}{R_1} V_{\text{IP}} + \left(\frac{R_1 + R_2}{R_3 + R_4}\right) \frac{R_3}{R_1} V_{\text{REF}}$$

If the resistor ratios are equal (i.e. $R_1=R_3$ and $R_2=R_4$), then

$$V_{\rm OUT} = \frac{R_2}{R_1} (V_{\rm IP} - V_{\rm IN}) + V_{\rm REF}$$

Low Pass Active Filter

The low pass active filter is shown in Figure 5. The DC gain is defined by $-R_2/R_1$. The filter has a -20dB/decade roll-off after its corner frequency $f_c=1/(2\pi R_3 C_1)$.




Figure 5. Low Pass Active Filter



Instrumentation Amplifier

The triple HGV604X family can be used to build a three-op-amp instrumentation amplifier as shown in Figure 6. The amplifier in Figure 6 is a high input impedance differential amplifier with gain of R2/R1. The two differential voltage followers assure the high input impedance of the amplifier.





Figure 6. Instrument Amplifier



HGV6041/42/43


Package Information





HGV6041/42/43


Package Information





HGV6041/42/43

Package Information





Important statement:

Huaguan Semiconductor Co,Ltd. reserves the right to change the products and services provided without notice. Customers should obtain the latest relevant information before ordering, and verify the timeliness and accuracy of this information.

Customers are responsible for complying with safety standards and taking safety measures when using our products for system design and machine manufacturing to avoid potential risks that may result in personal injury or property damage.

Our products are not licensed for applications in life support, military, aerospace, etc., so we do not bear the consequences of the application of these products in these fields.

Our documentation is only permitted to be copied without any tampering with the content, so we do not accept any responsibility or liability for the altered documents.