

# **DATASHEET**

# SMD • B 19-226/R6GHC-A04/2T



#### **Features**

- Package in 8mm tape on 7" diameter reel.
- Compatible with automatic placement equipment.
- Compatible with infrared and vapor phase reflow solder process.
- Mono-color type.
- Pb-free.
- The product itself will remain within RoHS compliant version.
- Compliance with EU REACH
- Compliance Halogen Free .(Br <900 ppm ,Cl <900 ppm , Br+Cl < 1500 ppm).

### **Description**

- The 19-226 SMD LED is much smaller than lead frame type components, thus enable smaller board ize, higher packing density, reduced storage space and finally smaller equipment to be obtained.
- Besides, lightweight makes them ideal for miniature applications. etc.

### **Applications**

- Backlighting in dashboard and switch.
- Telecommunication: indicator and backlighting in telephone and fax.
- Flat backlight for LCD, switch and symbol.
- General use.



### **Device Selection Guide**

Chip Type	Chip Materials	Emitted Color	Resin Color
R6	AlGaInP	Brilliant Red	Water Clear
GH	InGaN	Brilliant Green	Water Clear

### Absolute Maximum Ratings (Ta=25°C)

Parameter	Symbol	Rating	Unit
Reverse Voltage	$V_R$	5	V
Forward Current	lF	R6:25 GH:25	mA
Peak Forward Current (Duty 1/10 @1KHz)	lfp	R6:60 GH:100	mA
Power Dissipation	Pd	R6:60 GH:95	mW
Electrostatic Discharge	ESD <sub>HBM</sub>	R6: 2000 GH: 150	V
Operating Temperature	T <sub>opr</sub>	-40 ~ +85	$^{\circ}\!\mathbb{C}$
Storage Temperature	Tstg	-40 ~ +90	$^{\circ}\! \mathbb{C}$
Soldering Temperature T <sub>sol</sub>			ng : 260 ℃ for 10 sec. g : 350 ℃ for 3 sec.

### **Electro-Optical Characteristics (Ta=25℃)**

Parameter	Symbol	Min.	Тур.	Max.	Unit	Condition
Luminous Intensity	lv	R6: 180 GH: 225		450 450	mcd	I <sub>F</sub> =20mA
Viewing Angle	<b>2θ</b> <sub>1/2</sub>		120		deg	I <sub>F</sub> =20mA
Peak Wavelength	λр	R6 : GH :	632 518		nm	I <sub>F</sub> =20mA
Dominant Wavelength	λd	R6: 621.5 GH: 520		633.5 535	nm	I <sub>F</sub> =20mA
Spectrum Radiation Bandwidth	Δλ	R6 : GH :	20 35		nm	I <sub>F</sub> =20mA
Forward Voltage	V <sub>F</sub>	R6: 1.7 GH: 2.8		2.5 3.6	V	I <sub>F</sub> =20mA
Reverse Current	I <sub>R</sub>	R6 : GH :		10 50	μΑ	V <sub>R</sub> =5V

### Note:

<sup>1.</sup>Tolerance of Luminous Intensity: ±11%

<sup>2.</sup>Tolerance of Dominant Wavelength ±1nm

<sup>3.</sup>Tolerance of Forward Voltage:±0.1V

<sup>4.</sup>Reverse Voltage(VR) Condition is applied to IR test only The device is not designed for reverse operation



### **Bin Range of Luminous Intensity**

**R6** 

	Bin Code	Min.	Max.	Unit	Condition
	S1	180	225		I <sub>F</sub> =20mA
	S2	225	285	- mad	
	T1	285	360	mcd	
	T2	360	450		
GH					
	Bin Code	Min.	Max.	Unit	Condition
	S2	225	285		I <sub>F</sub> =20mA
	T1	285	360	mcd	
-	T2	360	450		

## **Bin Range of Dominant Wavelength**

**R6** 

Bin Code	Min.	Max.	Unit	Condition
E5	621.5	625.5		
E6	625.5	629.5	nm	I <sub>F</sub> =20mA
E7	629.5	633.5		

GH

Bin Code	Min.	Max.	Unit	Condition
X	520	525		
Υ	525	530	nm	I <sub>F</sub> =20mA
Z	530	535		


### Note:


<sup>1.</sup> Tolerance of Luminous Intensity: ±11%


<sup>2.</sup> Tolerance of Dominant Wavelength: ±1nm





# Typical Electro-Optical Characteristics Curves R6


















# **EVERLIGHT**


### GH

















### **Package Outline Dimensions**




Suggested pad dimension is just for reference only. Please modify the pad dimension based on individual need.

Note: Tolerances unless mentioned ±0.1mm. Unit = mm




# **Moisture Resistant Packing Materials Label Explanation**




- · CPN: Customer's Product Number
- P/N: Product NumberQTY: Packing Quantity
- · CAT: Luminous Intensity Rank
- HUE: Chromaticity Coordinates & Dom. Wavelength Rank
- · REF: Forward Voltage Rank
- · LOT No: Lot Number

### **Reel Dimensions**




Note: The tolerances unless mentioned is  $\pm 0.1$ mm, Unit = mm

## Carrier Tape Dimensions: Loaded quantity 2000 PCS per reel



**Note:** The tolerances unless mentioned is  $\pm 0.1$ mm, Unit = mm

# **Moisture Resistant Packaging**





### **Precautions For Use**

#### 1. Over-current-proof


Customer must apply resistors for protection, otherwise slight voltage shift will cause big current change ( Burn out will happen ).

- 2. Storage
- 2.1 Do not open moisture proof bag before the products are ready to use.
- 2.2 After opening the package: The LEDs should be kept at 30℃ or less and 60%RH or less.
- 2.3 The LEDs should be used within 168 hours (7days) after opening the package.

If unused LEDs remain, it should be stored in moisture proof packages.

2.4 If the moisture absorbent material (silica gel) has faded away or the LEDs have exceeded the storage time, baking treatment should be performed using the following conditions. Baking treatment:  $60\pm5^{\circ}$ C for 24 hours.

- 3. Soldering Condition
- 3.1 Pb-free solder temperature profile




- 3.2 Reflow soldering should not be done more than two times.
- 3.3 When soldering, do not put stress on the LEDs during heating.
- 3.4 After soldering, do not warp the circuit board.
- 4. Soldering Iron

Each terminal is to go to the tip of soldering iron temperature less than 350°C for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.

### 5.Repairing

Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.





### **Application Restrictions**

High reliability applications such as military/aerospace, automotive safety/security systems, and medical equipment may require different product. If you have any concerns, please contact Everlight before using this product in your application. This specification guarantees the quality and performance of the product as an individual component. Do not use this product beyond the specification described in this document.





### **DISCLAIMER**

- 1. EVERLIGHT reserves the right(s) on the adjustment of product material mix for the specification.
- 2. The product meets EVERLIGHT published specification for a period of twelve (12) months from date of shipment.
- 3. The graphs shown in this datasheet are representing typical data only and do not show guaranteed values.
- 4. When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from the use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
- 5. These specification sheets include materials protected under copyright of EVERLIGHT. Reproduction in any form is prohibited without obtaining EVERLIGHT's prior consent.
- 6. This product is not intended to be used for military, aircraft, automotive, medical, life sustaining or life saving applications or any other application which can result in human injury or death. Please contact authorized Everlight sales agent for special application request.

