
US1A-DM THRU US1M-DM

SURFACE MOUNT ULTRAFAST RECOVERY RECTIFIER

Reverse Voltage – 50 to 1000 V Forward Current – 1 A

Features

- For surface mount applications
- Low profile package
- Built-in strain relief
- · Easy pick and place
- Ultrafast recovery times for high efficiency
- Plastic package has Underwriters Laboratories Flammability Classification 94V-0



Dimensions in inches and (millimeters)

Mechanical Data

- Case: SMA (DO-214AC) molded plastic
- Terminals: Solder plated, solderable per MIL-STD-750, method 2026 guaranteed
- · Polarity: Color band denotes cathode end

Maximum Ratings and Electrical Characteristics


Ratings at 25 $^{\circ}$ C ambient temperature unless otherwise specified. Single phase, half wave, 60 Hz, resistive or inductive load. For capacitive load, derate current by 20%.


Parameter	Symbols	US1A	US1B	US1D	US1G	US1J	US1K	US1M	Units
Maximum Repetitive Peak Reverse Voltage	V _{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS Voltage	V _{RMS}	35	70	140	280	420	560	700	V
Maximum DC Blocking Voltage	V _{DC}	50	100	200	400	600	800	1000	V
Maximum Average Forward Rectified Current at T_L = 100 °C	I _{F(AV)}				1				А
Peak Forward Surge Current 8.3 ms Single Half Sine-wave Superimposed on Rated Load (JEDEC Method)	I _{FSM}				30				A
Maximum Forward Voltage at 1 A	V _F		1		1.4		1.7		V
Maximum DC Reverse Current $T_A = 25^{\circ}C$ at Rated DC Blocking Voltage $T_A = 100^{\circ}C$	I _R	5 50						μΑ	
Typical Junction Capacitance at 4 V, 1 MHz	CJ	17							pF
Maximum Reverse Recovery Time at $I_F = 0.5 \text{ A}$, $I_R = 1 \text{ A}$, $I_{rr} = 0.25 \text{ A}$	t _{rr}		5	0			75		ns
Typical Thermal Resistance ¹⁾	R _{0JA}	50							°C/W
Operating and Storage Temperature Range	T _J ,T _{Stg}	- 55 to + 150							°C

¹⁾ Mounted on P.C.B. with 0.2 X 0.2" (5 X 5 mm) copper pad areas.



US1A-DM THRU US1M-DM












FIG. 5-TYPICAL JUNCTION CAPACITANCE





NUMBER OF CYCLES AT 60 Hz

FIG. 4-TYPICAL REVERSE CHARACTERISTICS





FIG. 6-TYPICAL TRANSIENT THERMAL IMPEDANCE



t,PULSE DURATION,sec.

