



3D VIEW

Specifications:
 规格:
 Current rating:5A AC/DC
 额定电流: 5A AC/DC
 Voltage rating:250V AC
 额定电压: 250V AC
 Withstanding voltage:500V AC/MIN
 耐受电压: ≥500V AC/分钟
 Temperature range:-25℃~+105℃
 温度范围: -55℃~+105℃
 Insulation resistance:1000MΩMIN
 绝缘电阻: ≥1000MΩ
 Contact resistance:30mΩMAN
 接触电阻:≤30mΩ
 Material And FINISHED:
 材料和成本:
 INSULATOR:PBT+30% GF UL 94V-0
 绝缘体: pbt+30% gf ul 94-0
 SHELL:STEEL, NI FINISHED
 外壳: 钢、镍加工
 CONTACT MATERIAL:BRASS SELEVITE GOLD FINISHED
 触点材料: 黄铜SELEVITE

X03 XX W X X X X
 ① ② ③ ④ ⑤ ⑥ ⑦

- ① Series NO.
- ② Row No.Pin No.XX-09:15;25;37
- ③ Welding Board Angle :W-male
- ④ T: Tradutional C: Car-pin
- ⑤ Planting Category: 1:1U 2:2U 3:3U 4:5U 5:15U 6:30U 7 : AuSn
- ⑥ B:BLACK W:White BL:Blue Y:Yellow G:Green R:Red
- ⑦ 1:TYPE-1; 2:TYPE-2; 3:TYPE-3; 4:TYPE-4; 5:TYPE-5; 6:TYPE-6

NO OF CONTACT	A	B	C
09	30. 81	24. 99	16. 92
15	39. 14	33. 32	25. 25
25	53. 04	47. 04	38. 96
37	69. 32	63. 50	55. 42

锁合方式	TYPE-1: 锁合	TYPE-6: 直铆锁	TYPE-3: 叉锁	TYPE-2: 锁合锁螺丝
图式				

REVISIONS					UNSPECIFIED TOLERANCES	DSND	DATE	SCALE: N/A	MODEL TYPE:
ΔX					units: mm	DWN	DATE	VIEW:	PART NO.:
ΔX					tolerance: X.X ±0.2mm	CHKD	DATE	UNIT: mm/in	DWG NO.:
ΔX					X.XX ±0.1mm	APPD	DATE	SIZE: A4	X03XXWXXXX
MARK	DESCRIPTION	DATE	REVISED	APPROVED	X.XXX ±0.05mm	KKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT
									1.0g
									SHEET
									1/1
									REVISION
									A0