Technical Data Sheet

Top View LEDs

67-21/B7C-BS2U1K/2T

Features

- P-LCC-2 package.
- White package.
- Optical indicator.
- Colorless clear window.
- Wide viewing angle.
- Suitable for vapor-phase reflow.
- Computable with automatic placement equipment.
- Available on tape and reel (8mm Tape).
- Pb-free
- The product itself will remain within RoHS compliant version

Descriptions

• The 67-21 series is available in soft orange, green, blue and yellow. Due to the package design, the LED has wide viewing angle and optimized light coupling by inter reflector. This feature makes TOP LED ideal for light pipe application. The low current requirement makes this device ideal for portable equipment or any other application where power is at a premium.

Applications

- Automotive: backlighting in dashboard and switch.
- Telecommunication: indicator and backlighting in telephone and fax.
- Flat backlight for LCD, switch and symbol.
- Light pipe application.
- General use.

Device Selection Guide

Chip	E:44 - J C-l	Desir Calan	
Material	Emitted Color	Resin Color	
InGaN	Blue	Water Clear	

Everlight Electronics Co., Ltd. http://www.everlight.com Rev. 3 Page: 1 of 11




Technical Data Sheet

Top View LEDs

67-21/B7C-BS2U1K/2T

Package Dimensions



Note: The tolerances unless mentioned is ± 0.1 mm; Unit = mm

Everlight Electronics Co., Ltd. http://www.everlight.com Rev. 3 Page: 2 of 11

Device No.: DSE-0007593 Prepared date: 23-Feb.-2017 Prepared by: Irene Lin

T 2 D 1 D 4 02/17 (10017 11)(会長 4 1/丁子及行)

Technical Data Sheet

Top View LEDs

67-21/B7C-BS2U1K/2T

Absolute Maximum Ratings (Ta=25°C)

Parameter	Symbol	Rating	Unit
Reverse Voltage	V_R	5	V
Forward Current	$ m I_F$	30	mA
Peak Forward Current (Duty 1/10 @1KHz)	I_{FP}	100	mA
Power Dissipation	Pd	110	mW
Electrostatic Discharge (HBM)	ESD	1000	V
Operating Temperature	Topr	-40 ~ +85	$^{\circ}\!\mathbb{C}$
Storage Temperature	Tstg	-40 ~ +90	$^{\circ}\mathbb{C}$
Soldering Temperature	Tsol	Reflow Soldering : 260 °C for 10 sec. Hand Soldering : 350 °C for 3 sec.	

Electro-Optical Characteristics (Ta=25°C)

Parameter	Symbol	Min.	Тур.	Max.	Unit	Condition
Luminous Intensity	Iv	225		565	mcd	I _F =20mA
Viewing Angle	201/2		120		deg	I _F =20mA
Peak Wavelength	$\lambda_{ m P}$		468		nm	I _F =20mA
Dominant Wavelength	$\lambda_{ m d}$	464.5		473.5	nm	I _F =20mA
Spectrum Radiation Bandwidth	Δλ		25		nm	I _F =20mA
Forward Voltage	V_{F}	2.70		3.30	V	I _F =20mA
Reverse Current	I_R			50	μΑ	V _R =5V

Notes:

1. Tolerance of Luminous Intensity : $\pm 11\%$

2. Tolerance of Dominant Wavelength : $\pm 1 \text{nm}$

3.Tolerance of Forward Voltage: ±0.1V

Everlight Electronics Co., Ltd. http://www.everlight.com Rev. 3 Page: 3 of 11

Device No.: DSE-0007593 Prepared date: 23-Feb.-2017 Prepared by: Irene Lin

Technical Data Sheet

Top View LEDs

67-21/B7C-BS2U1K/2T

Bin Range of Luminous Intensity

Bin Code	Min.	Max.	Unit	Condition
S2	225	285		I _F =20mA
T1	285	360		
T2	360	450	mcd	
U1	450	565		

Bin Range of Dominant Wavelength

Group	Bin Code	Min.	Max.	Unit	Condition
В	A9	464.5	467.5	nm	
	A10	467.5	470.5		I _F =20mA
	A11	470.5	473.5		

Bin Range of Forward Voltage

Group	Bin Code	Min.	Max.	Unit	Condition
	10	2.70	2.90		
K	11	2.90	3.10	V	I _F =20mA
	12	3.10	3.30		

Notes:

1.Tolerance of Luminous Intensity: ±11%

2.Tolerance of Dominant Wavelength: ±1nm

3.Tolerance of Forward Voltage: ±0.1V

Everlight Electronics Co., Ltd. http://www.everlight.com Rev. 3 Page: 4 of 11


Device No.: DSE-0007593 Prepared date: 23-Feb.-2017 Prepared by: Irene Lin


Technical Data Sheet


Top View LEDs


67-21/B7C-BS2U1K/2T


Typical Electro-Optical Characteristics














Everlight Electronics Co., Ltd. http://www.everlight.com Rev. 3 Page: 5 of 11


Technical Data Sheet


Top View LEDs

67-21/B7C-BS2U1K/2T

Label Explanation

CAT: Luminous Intensity Rank HUE: Dom. Wavelength Rank REF: Forward Voltage Rank





Note: The tolerances unless mentioned is ± 0.1 mm; Unit = mm

Everlight Electronics Co., Ltd. http://www.everlight.com Rev. 3 Page: 6 of 11


Device No.: DSE-0007593 Prepared date: 23-Feb.-2017 Prepared by: Irene Lin

Technical Data Sheet

Top View LEDs

67-21/B7C-BS2U1K/2T


Carrier Tape Dimensions: Loaded Quantity 2000 pcs Per Reel.



Note:

- 1.Tolerance unless mentioned is ±0.1mm; Unit = mm
- 2. Minimum packing amount is 250/500/1000/2000 pcs per reel.

Moisture Resistant Packaging



Everlight Electronics Co., Ltd. http://www.everlight.com Rev. 3 Page: 7 of 11

Technical Data Sheet

Top View LEDs

67-21/B7C-BS2U1K/2T

Reliability Test Items and Conditions

The reliability of products shall be satisfied with items listed below.

Confidence level: 90%

LTPD: 10%

No.	Items	Test Condition	Test Hours/Cycles	Sample Size	Ac/Re
1	Reflow Soldering	Temp. : 260° C ±5 $^{\circ}$ C Min. 10sec.	6 Min.	22 PCS.	0/1
2	Temperature Cycle	$H: +100^{\circ}\mathbb{C}$ 15min $\int 5 \text{ min}$ $L: -40^{\circ}\mathbb{C}$ 15min	300 Cycles	22 PCS.	0/1
3	Thermal Shock	H: +100°C 5min ∫ 10 sec L: -10°C 5min	300 Cycles	22 PCS.	0/1
4	High Temperature Storage	Temp. : 100°C	1000 Hrs.	22 PCS.	0/1
5	Low Temperature Storage	Temp. : -40°C	1000 Hrs.	22 PCS.	0/1
6	DC Operating Life	$I_F = 20 \text{ mA}$	1000 Hrs.	22 PCS.	0/1
7	High Temperature / High Humidity	85°C / 85%RH	1000 Hrs.	22 PCS.	0/1

Everlight Electronics Co., Ltd. http://www.everlight.com Rev. 3 Page: 8 of 11

Device No.: DSE-0007593 Prepared date: 23-Feb.-2017 Prepared by: Irene Lin

Technical Data Sheet

Top View LEDs

67-21/B7C-BS2U1K/2T


Precautions for Use

1. Over-current-proof

Customer must apply resistors for protection, otherwise slight voltage shift will cause big current change (Burn out will happen).

- 2. Storage
 - 2.1 Do not open moisture proof bag before the products are ready to use.
 - 2.2 Before opening the package: The LEDs should be kept at 30°C or less and 90%RH or less.
 - 2.3 After opening the package: The LED's floor life are 168 hours under 30℃ or less and 60% RH or less.If unused LEDs remain, it should be stored in moisture proof packages.
 - 2.4 If the moisture absorbent material (silica gel) has faded away or the LEDs have exceeded the storage time, baking treatment should be performed using the following conditions.

 Baking treatment: 60±5°C for 24 hours.
- 3. Soldering Condition
 - 3.1 Pb-free solder temperature profile



- 3.2 Reflow soldering should not be done more than two times.
- 3.3 When soldering, do not put stress on the LEDs during heating.
- 3.4 After soldering, do not warp the circuit board.

Everlight Electronics Co., Ltd. http://www.everlight.com Rev. 3 Page: 9 of 11

Device No.: DSE-0007593 Prepared date: 23-Feb.-2017 Prepared by: Irene Lin

Technical Data Sheet

Top View LEDs


67-21/B7C-BS2U1K/2T

4. Soldering Iron

Each terminal is to go to the tip of soldering iron temperature less than 350°C for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.

5. Repairing

Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.



Everlight Electronics Co., Ltd. http://www.everlight.com Rev. 3 Page: 10 of 11

Technical Data Sheet

Top View LEDs

67-21/B7C-BS2U1K/2T

DISCLAIMER

- 1. EVERLIGHT reserves the right(s) on the adjustment of product material mix for the specification.
- 2. The product meets EVERLIGHT published specification for a period of twelve (12) months from date of shipment.
- 3. The graphs shown in this datasheet are representing typical data only and do not show guaranteed values.
- 4. When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from the use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
- 5. These specification sheets include materials protected under copyright of EVERLIGHT. Reproduction in any form is prohibited without obtaining EVERLIGHT's prior consent.
- 6. This product is not intended to be used for military, aircraft, automotive, medical, life sustaining or life saving applications or any other application which can result in human injury or death. Please contact authorized Everlight sales agent for special application request.

Everlight Electronics Co., Ltd. http://www.everlight.com Rev. 3 Page: 11 of 11

Device No.: DSE-0007593 Prepared date: 23-Feb.-2017 Prepared by: Irene Lin