

SK3080RB

Band8, RF-Rx Balance SAW Filter
Revision 0: August 2016

MSL 3 Device



- Electrical Characteristics
 - Package Dimensions
 - Testing Environment
 - Frequency Characteristics
-

□ Electrical Characteristics

Maximum Ratings


Parameters Description	Unit	Minimum	Typical	Maximum
Operating Temperature Range	°C	-30	-	+85
Storage Temperature Range	°C	-40	-	+85
Maximum DC Voltage	V	-	-	-
Maximum Input Power	dBm	-	-	10
Source Impedance (unbalance) ⁽¹⁾	□	-	50	-
Load Impedance (balance) ⁽¹⁾	□	-	100	-
Package type & size	C14			
Length x Width	mm ²	-	1.1 x 0.9	-
Height	mm	-	-	0.55

Electrical Specification

Parameters Description	Unit	Minimum	Typical @+25°C	Maximum
Center Frequency (Fo)	MHz	-	942.5	-
Insertion Loss within 925.0 ~ 960.0 MHz	dB	-	1.9	3.0
Insertion Loss within 927.4~ 957.6 MHz	dB	-	2.0	2.6
Amplitude Ripple within 925.0 ~ 960.0 MHz	dB _{p-p}	-	0.8	1.8
VSWR within 925.0 ~ 960.0 MHz	-	-	1.8	2.1
Amplitude balance within 925.0 ~ 960.0 MHz	dB	-1.2	-0.3/+0.4	+1.2
Phase balance within 925.0 ~ 960.0 MHz	deg	-10	-1.5/+3.4	+10
Attenuation:				
DC ~ 880.0 MHz	dB	50	65	-
880.0 ~ 915.0 MHz	dB	45	56	-
882.4 ~ 912.6 MHz	dB	50	56	-
980.0 ~ 1025.0 MHz	dB	23	32	-
1025.0 ~ 2880.0 MHz	dB	35	56	-
2880.0 ~ 6000.0 MHz	dB	30	44	-

Notes : (1) No Matching Network .


□ Package Dimensions



Marking Descriptions	
(X)	Series Number
X	Date Code(Year+Month)

Pin Description	
B, E	Ground
A	Input
C,D	Balanced Output


□ Testing Environment





Source Impedance: 50 Ω
Load Impedance: 100

□ Frequency Characteristics



Frequency Response



VSWR



Smith Chart



Amplitude balance



Phase balance

