

# **DATASHEET**

# LAMP 334-15UTC/S400-X10



#### **Features**

- Popular T-1 round package
- High luminous power
- Typical chromaticity coordinates x=0.29, y=0.28 according to CIE1931
- Bulk, available taped on reel.
- The product itself will remain within RoHS compliant version
- Compliance with EU REACH
- •Compliance Halogen Free .(Br <900 ppm ,Cl <900 ppm , Br+Cl < 1500 ppm)

# **Description**

- The series is designed for application required high luminous intensity.
- The phosphor filled in the reflector converts the blue emission of InGaN chip to ideal white.

# **Applications**

- Message panels
- Optical Indicators
- Backlighting
- Marker Lights



# **Device Selection Guide**

Chip Materials	Emitted Color	Resin Color	
InGaN	White	Water Clear	

# Absolute Maximum Ratings (Ta=25℃)

Parameter	Symbol	Rating	Unit	
Continuous Forward Current	I <sub>F</sub>	30	mA	
Peak Forward Current (Duty 1/10 @ 1KHZ)	I <sub>FP</sub>	100	mA	
Reverse Voltage	$V_R$	5	V	
Power Dissipation	$P_d$	110	mW	
Operating Temperature	Topr	-40 ~ +85	$^{\circ}\!\mathbb{C}$	
Storage Temperature	Tstg	-40 ~ +100	${\mathbb C}$	
Electrostatic Discharge	ESD	150	V	
Soldering Temperature	Tsol	260 °C for 5 sec.		

# Electro-Optical Characteristics (Ta=25°C)

Parameter	Symbol	Min.	Тур.	Max.	Unit	Condition
Forward Voltage	$V_{F}$	2.8		4.0	V	I <sub>F</sub> =20mA
Reverse Current	I <sub>R</sub>			50	μA	V <sub>R</sub> =5V
Luminous Intensity	I <sub>V</sub>	11250		28500	mcd	I <sub>F</sub> =20mA
Viewing Angle	201/2		20		deg	I <sub>F</sub> =20mA
Chromaticity Coordinates	Х		0.29			I <sub>F</sub> =20mA
	У		0.28			1 <sub>F</sub> -20111A



# **Bin Range of Luminous Intensity**

Bin Code	Min.	Max.	Unit	Condition
V	11250	14250	mcd	I <sub>F</sub> =20mA
W	14250	18000		
X	18000	22500		
Υ	22500	28500		

Note:


Tolerance of Luminous Intensity: ±10%

# **Forward Voltage Combination**

Bin Code	Min.	Max.	Unit	Condition	
0	2.8	3.0		I <sub>F</sub> =20mA	
1	3.0	3.2	V		
2	3.2	3.4			
3	3.4	3.6			
4	3.6	3.8			
5	3.8	4.0			
Note: Measurement Uncertainty of Forward Voltage: ±0.1V					




# **CIE Chromaticity Diagram**





Note:

Measurement uncertainty of the color coordinates: ±0.01

**Typical Electro-Optical Characteristics Curves** 










# **Package Dimension**



Note: Note:

1.All dimensions are in millimeters, and tolerance is 0.25mm except being specified.


2.Lead spacing is measured where the lead emerges from the package.

3. Protruded resin under flange is 1.5mm Max. LED.



# **Moisture Resistant Packing Materials**

## **Label Explanation**




- · CPN: Customer's Production Number
- P/N : Production NumberQTY: Packing Quantity
- · CAT: Ranks of Luminous Intensity and Forward Voltage
- HUE: Color RankREF: ReferenceLOT No: Lot Number

## **Packing Specification**


Anti-electrostatic bag



Inner Carton



Outside Carton



- Packing Quantity
- 1. Min200~500 PCS/1 Bag, 5 Bags/1 Box
- 2. 10 Box/1 Carton



#### **Notes**

## Lead Forming

- During lead formation, the leads should be bent at a point at least 3mm from the base of the epoxy bulb.
- Lead forming should be done before soldering.
- Avoid stressing the LED package during leads forming. The stress to the base may damage the LED's characteristics or it may break the LEDs.
- Cut the LED leadframes at room temperature. Cutting the leadframes at high temperatures may cause failure of the LEDs.
- When mounting the LEDs onto a PCB, the PCB holes must be aligned exactly with the lead position of the LED. If the LEDs are mounted with stress at the leads, it causes deterioration of the epoxy resin and this will degrade the LEDs.

## 2. Storage


- The LEDs should be stored at 30°C or less and 70%RH or less after being shipped from Everlight and the storage life limits are 3 months. If the LEDs are stored for 3 months or more, they can be stored for a year in a sealed container with a nitrogen atmosphere and moisture absorbent material.
- Please avoid rapid transitions in ambient temperature, especially, in high humidity environments where condensation can occur.

#### 3. Soldering

Careful attention should be paid during soldering. When soldering, leave more then 3mm from solder joint to epoxy bulb, and soldering beyond the base of the tie bar is recommended.

#### Recommended soldering conditions:

Hand Soldering		DIP Soldering		
Temp. at tip of iron	300°C Max. (30W Max.)	Preheat temp.	100°C Max. (60 sec Max.)	
Soldering time	3 sec Max.	Bath temp. & time	260 Max., 5 sec Max	
Distance	3mm Min.(From solder joint to epoxy bulb)	Distance	3mm Min. (From solder joint to epoxy bulb)	






- Avoiding applying any stress to the lead frame while the LEDs are at high temperature particularly when soldering.
- Dip and hand soldering should not be done more than one time
- After soldering the LEDs, the epoxy bulb should be protected from mechanical shock or vibration until the LEDs return to room temperature.
- A rapid-rate process is not recommended for cooling the LEDs down from the peak temperature.
- Although the recommended soldering conditions are specified in the above table, dip or handsoldering at the lowest possible temperature is desirable for the LEDs.
- Wave soldering parameter must be set and maintain according to recommended temperature and dwell time in the solder wave.

## 4. Cleaning

- When necessary, cleaning should occur only with isopropyl alcohol at room temperature for a duration of no more than one minute. Dry at room temperature before use.
- Do not clean the LEDs by the ultrasonic. When it is absolutely necessary, the influence of ultrasonic cleaning on the LEDs depends on factors such as ultrasonic power and the assembled condition. Ultrasonic cleaning shall be pre-qualified to ensure this will not cause damage to the LED

#### 5. Circuit Protection

- Below the zener reference voltage Vz, all the current flows through LED and as the voltage rises to Vz, the zener diode "breakdown." If the voltage tries to rise above Vz current flows through the zener branch to keep the voltage at exactly Vz.
- When the LED is connected using serial circuit, if either piece of LED is no light up but current can't flow through causing others to light down. In new design, the LED is parallel with zener diode. if either piece of LED is no light up but current can flow through causing others to light up.



#### 6. Heat Management

Heat management of LEDs must be taken into consideration during the design stage of LED application. The current should be de-rated appropriately by referring to the de-rating curve found in each product



specification.

■ The temperature surrounding the LED in the application should be controlled. Please refer to the data sheet de-rating curve.

#### 7. ESD (Electrostatic Discharge)

■ The products are sensitive to static electricity or surge voltage. ESD can damage a die and its reliability. When handling the products, the following measures against electrostatic discharge are strongly recommended:

Eliminating the charge

Grounded wrist strap, ESD footwear, clothes, and floors

Grounded workstation equipment and tools

ESD table/shelf mat made of conductive materials

- Proper grounding is required for all devices, equipment, and machinery used in product assembly.
   Surge protection should be considered when designing of commercial products.
- If tools or equipment contain insulating materials such as glass or plastic,

the following measures against electrostatic discharge are strongly recommended:

Dissipating static charge with conductive materials

Preventing charge generation with moisture

Neutralizing the charge with ionizers

#### 8. Other

- Above specification may be changed without notice. EVERLIGHT will reserve authority on material change for above specification.
- When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.

These specification sheets include materials protected under copyright of EVERLIGHT corporation. Please don't reproduce or cause anyone to reproduce them without EVERLIGHT's consent

#### **DISCLAIMER**

- 1. EVERLIGHT reserves the right(s) on the adjustment of product material mix for the specification.
- 2. The product meets EVERLIGHT published specification for a period of twelve (12) months from date of shipment.
- 3. The graphs shown in this datasheet are representing typical data only and do not show guaranteed values.
- 4. When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from the use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
- These specification sheets include materials protected under copyright of EVERLIGHT. Reproduction in any form is prohibited without obtaining EVERLIGHT's prior consent.



6. This product is not intended to be used for military, aircraft, automotive, medical, life sustaining or life saving applications or any other application which can result in human injury or death. Please contact authorized Everlight sales agent for special application request.

