

100V N-CHANNEL MOSFET

Features

- Advanced Trench MOS Technology
- Low Gate Charge
- Low R_{DS(ON)}
- 100% EAS Guaranteed
- Green Device Available


Applications


- Power Management in Desktop Computer or DC/DC Converters.
- Isolated DC/DC Converters in Telecom and Industrial.


Product Summary



V_{DS}	100	V
R _{DS(on),Typ} @ Vgs=10V	5.9	$m\Omega$
I_{D}	68	Α







Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V _{DS}	Drain-Source Voltage	100	V
V _G S	Gate-Source Voltage	±20	V
I _D @T _C =25°C	Continuous Drain Current ^{1,6}	68	А
I _D @T _C =70°C	Continuous Drain Current ^{1,6} 48		А
I _{DM}	Pulsed Drain Current ²	140	А
EAS	Single Pulse Avalanche Energy ³ 61		mJ
IAS	Avalanche Current 35		А
P _D @T _C =25°C	Total Power Dissipation ⁴ 108		W
T _{STG}	Storage Temperature Range	-55 to 150	°C
TJ	Operating Junction Temperature Range	-55 to 150	℃

Thermal Data

Symbol	Parameter		Max.	Unit
ReJA	Thermal Resistance Junction-Ambient ¹(t≦10s)		25	°C/W
Кеја	Thermal Resistance Junction-Ambient ¹		55	°C/W
ReJC	Thermal Resistance Junction-Case ¹		1.15	°C/W

100V N-CHANNEL MOSFET

Electrical Characteristics (T_J=25 °C, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit	
BV _{DSS}	Drain-Source Breakdown Voltage V _{GS} =0V , I _D =250uA		100			V	
Dagger	Static Drain-Source On-Resistance ² V _{GS} =10V , I _D =13.5A			5.9	8	mΩ	
Rds(on)	Static Drain-Source On-Resistance ²	V _{GS} =4.5V , I _D =11.5A		7.6	10.5	1112.2	
V _{GS(th)}	Gate Threshold Voltage	V _{GS} =V _{DS} , I _D =250uA	1.2		2.3	V	
I _{DSS}	Drain Source Leekage Current	V _{DS} =80V , V _{GS} =0V , T _J =25°C			1		
IDSS	Drain-Source Leakage Current	V _{DS} =80V , V _{GS} =0V , T _J =55°C			5	uA	
Igss	Gate-Source Leakage Current	$V_{GS}=\pm20V$, $V_{DS}=0V$			±100	nA	
gfs	Forward Transconductance	V _{DS} =5V , I _D =20A		85		S	
Qg	Total Gate Charge (10V)			45			
Qg	Total Gate Charge (4.5V)	\/po_50\/ \/oo_10\/ \p_12.54		19.3		nC	
Qgs	Gate-Source Charge	VDS=50V , VGS=10V , ID=13.5A		9.5		iiC	
Qgd	Gate-Drain Charge			4.8			
Td(on)	Turn-On Delay Time			10			
Tr	Rise Time	VDD=50V , VGS=10V , RG=3 Ω ,		6.5		no	
Td(off)	Turn-Off Delay Time	ID=13.5A		45		ns	
Tf	Fall Time			7.5			
Ciss	Input Capacitance			3320			
Coss	Output Capacitance	vitance VDS=50V , VGS=0V , f=1MHz		605		pF	
Crss	Reverse Transfer Capacitance			20			

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit
Is	Continuous Source Current ^{1,5,6}	V _G =V _D =0V , Force Current			48	Α
V_{SD}	Diode Forward Voltage ²	V _{GS} =0V , I _S =1A , T _J =25°C			1.1	V
t _{rr}	Reverse Recovery Time IF=13.5A , di/dt=100A/µs ,			33		nS
Qrr	Reverse Recovery Charge	T _J =25°C		150		nC

Note

- 1. The data tested by surface mounted on a 1 inch² FR-4 board with 2OZ copper.
- 2.The data tested by pulsed , pulse width \leq 300us , duty cycle \leq 2%
- 3. The EAS data shows Max. rating . The test condition is V_{DD} =25V, V_{GS} =10V, L=0.3mH, I_{AS} =35A
- 4. The power dissipation is limited by 150°C junction temperature
- 5. The data is theoretically the same as I_D and I_{DM} , in real applications, should be limited by total power dissipation.
- 6. The maximum current rating is package limited.



Typical Characteristics




Fig.1 Typical Output Characteristics




Fig.3 Source-Drain Forward Characteristics




Fig.5 Normalized V_{GS(th)} vs. T_J




Fig.2 On-Resistance vs. G-S Voltage




Fig.4 Gate-Charge Characteristics





Fig.6 Normalized R_{DSON} vs. T_J








Fig.7 Capacitance

Fig.8 Safe Operating Area




Fig.9 Normalized Maximum Transient Thermal Impedance




Fig.10 Switching Time Waveform




Fig.11 Unclamped Inductive Switching Waveform




Ordering and Marking Information


Ordering Device No.	Marking	Package	Packing	Quantity
ASDM100R066NQ-R	100R066N	DFN5x6-8	Tape&Reel	4000/Reel


PACKAGE	MARKING
DFN5x6-8	AS Date Code Lot Number 100R066N □□□□□ Date Code



DFN5x6-8 PACKAGE IN FORMATION







Sumbal	Dimensions I	n Millimeters	Dimension	s In Inches
Symbol	Min.	Max.	Min.	Max.
Α	0.900	1.000	0.035	0.039
A3	0.254	REF.	0.010	REF.
D	4.944	5.096	0.195	0.201
E	5.974	6.126	0.235	0.241
D1	3.910	4.110	0.154	0.162
E1	3.375	3.575	0.133	0.141
D2	4.824	4.976	0.190	0.196
E2	5.674	5.826	0.223	0.229
k	1.190	1.390	0.047	0.055
b	0.350	0.450	0.014	0.018
е	1.270	TYP.	0.050TYP.	
L	0.559	0.711	0.022	0.028
L1	0.424	0.576	0.017	0.023
Н	0.574	0.726	0.023	0.029
θ	10°	12°	10°	12°



ASDM100R066NQ

100V N-CHANNEL MOSFET

IMPORTANT NOTICE

Xi'an Ascend Semiconductor incorporated MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Xi'an Ascend Semiconductor Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Xi'an Ascend Semiconductor Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Xi'an Ascend Semiconductor Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume.

all risks of such use and will agree to hold Ascendsemi Incorporated and all the companies whose products are represented on Xi'an Ascend Semiconductor Incorporated website, harmless against all damages.

Xi'an Ascend Semiconductor Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Xi'an Ascend Semiconductor Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Xi'an Ascend Semiconductor Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

www.ascendsemi.com