

DATASHEET

SMD-Full Color Top View LEDs 67-23-RSHGRBYC-M050505-ET1-CS



Features

- P-LCC-4 package.
- White package.
- Optical indicator.
- Colorless clear window.
- Ideal for backlight and light pipe application.
- Inter reflector.
- · Wide viewing angle.
- Suitable for vapor-phase reflow.
- Computable with automatic placement equipment.
- Available on tape and reel (12mm Tape).
- Ph-free
- The product itself will remain within RoHS compliant version.
- Compliance with EU REACH.
- Compliance Halogen Free .(Br<900ppm,Cl<900ppm,Br+Cl<1500ppm)
- Precondition: Bases on JEDEC J-STD 020D Level 3

Applications

- Switches, symbol, mobile phone, digital camera and illuminated advertising.
- Display for indoor and outdoor application.
- Ideal for coupling into light guides.
- · Substitution of traditional light.
- · Amusement equipment.
- · General applications.
- · Optical indicator.



Device Selection Guide

Chip Code	Chip Materials	Emitted Color	Resin Color
RSH	AlGaInP	Brilliant Red	Water Clear
GR	InGaN	Brilliant Green	Water Clear
ВҮ	InGaN	Brilliant Blue	Water Clear

Absolute Maximum Ratings (Ta=25°C)

Parameter	Symbol	Code	Rating	Unit
D Vallana		RSH	10	
Reverse Voltage	V_{R}	GR / BY	5	V
		RSH	50	
Forward Current	l _F	GR	30	mA
		BY	30	
Peak Forward Current (Duty 1/10 @1KHz)	I _{FP}		100	mA
		RSH	115	
Power Dissipation	Pd	GR	93	mW
		BY	93	
Junction Temperature	Tj		115	$^{\circ}\!\mathbb{C}$
Operating Temperature	T_{opr}		-40 ~ +85	$^{\circ}\!\mathbb{C}$
Storage Temperature	Tstg		-40 ~ +90	$^{\circ}\!\mathbb{C}$
ESD	ECD	RSH	2000	V
ESD	ESD	GR / BY	1000	V
Soldering Temperature	T _{sol}	Reflow Soldering : 260 $^{\circ}$ C for 10 sec. Hand Soldering : 350 $^{\circ}$ C for 3 sec.		



Electro-Optical Characteristics (Ta=25℃)

Parameter	Symbol	Code	Min.	Тур.	Max.	Unit	Condition	
		RSH	140		355	mcd		
	lv.	GR	355		900		R:I _F =5mA G:I _F =5mA B:I _F =5mA	
Luminous Intensity	lv -	BY	71		180			
	•	Mix	560		1800	•		
Viewing Angle	2θ _{1/2}			120		deg	R:I _F =5mA G:I _F =5mA B:I _F =5mA	
		RSH		632			R:I _F =5mA	
Peak Wavelength	λр	GR		518		nm	$G:I_F=5mA$	
		BY		468			B:I _F =5mA	
		RSH	617.5		629.5	- nm -	R:I _F =5mA G:I _F =5mA B:I _F =5mA	
Dominant Wavelength	λd	GR	520.0		535.0			
		BY	464.5		476.5			
		RSH		18		nm	R:I _F =5mA G:I _F =5mA B:I _F =5mA	
Spectrum Radiation Bandwidth	Δλ	GR		29				
		BY		20			D.IF-SIIIA	
		RSH	1.50		2.30	_	R:I₅=5mA	
Forward Voltage	V _F	GR	2.40		3.10	V	G:I _F =5mA B:I _F =5mA	
		BY	2.40		3.10		B.IF=SIIIA	
White point coordinate	X			0.25			R:I _F =5mA — G:I _F =5mA	
	У			0.26			B:I _F =5mA	
Reverse Current		RSH			10	μA	V _R =10V V _R =5V	
	I _R	GR			10	μA		
		ВҮ			10	μA	V _R =5V	

Notes

- 1. Tolerance of Luminous Intensity: ±11%
- 2. Tolerance of Dominant Wavelength: ±1nm
- 3. Tolerance of Chromaticity Coordinates: ±0.01
- 4. Tolerance of Forward Voltage: ±0.1V



Bin Range of Luminous Intensity

Chip	Bin Code	Min.	Max.	Unit	Condition
5011	R2	140	180		R:I _F =5mA G:I _F =5mA B:I _F =5mA
	S1	180	224		
RSH	S2	224	280		
	T1	280	355		
	T2	355	450		
GR	U1	450	560	mcd	
GK	U2	560	710		
	V1	710	900		
	Q1	71	90		
BY	Q2	90	112		
	R1	112	140		
	R2	140	180		
	U2	560	710		
Mix	V1	710	900		
	V2	900	1120		
	AA	1120	1400		
	AB	1400	1800		

Note:

Tolerance of Luminous Intensity: ±11%

Bin Range of Dominant Wavelength


Chip	Bin Code	Min.	Max.	Unit	Condition
	E4	617.5	621.5	621.5 625.5 629.5 525.0 530.0 535.0 467.5 470.5 473.5	
RSH	E5	621.5	625.5		
	E6	625.5	629.5		
	Χ	520.0	525.0		
GR	Υ	525.0	530.0		$R:I_F=5mA$ $G:I_F=5mA$
_	Z	530.0	535.0		$B:I_F=5mA$
	A9	464.5	467.5		
BY	A10	467.5	470.5		
ВΥ	A11	470.5	473.5		
- -	A12	473.5	476.5		

Note:

Tolerance of Dominant Wavelength: ±1nm



Bin Code of Chromaticity Coordinates R/G/B=5/5/5mA





Bin Code of Chromaticity Coordinates

Bin Code	CIE_x	CIE_y	Bin Code	CIE_x	CIE_y
	0.219	0.231		0.239	0.231
	0.219	0.251	S2	0.239	0.251
S1	0.239	0.251	52	0.259	0.251
	0.239	0.231		0.259	0.231
	0.259	0.231		0.219	0.251
S3	0.259	0.251	84	0.219	0.271
53	0.279	0.251	- S4 -	0.239	0.271
	0.279	0.231		0.239	0.251
	0.239	0.251	- S6	0.259	0.251
S5	0.239	0.271		0.259	0.271
33	0.259	0.271		0.279	0.271
	0.259	0.251		0.279	0.251
	0.219	0.271	S8	0.239	0.271
S7	0.219	0.291		0.239	0.291
31	0.239	0.291		0.259	0.291
	0.239	0.271		0.259	0.271
S 9	0.259	0.271			
	0.259	0.291			
	0.279	0.291			
		-	⊣		

Note:

Tolerance of Chromaticity Coordinates: ±0.01.


0.279

0.271




Typical Electro-Optical Characteristics Curves

Typical Curve of Spectral Distribution




Note: $V(\lambda)$ =Standard eye response curve

Diagram Characteristics of Radiation




Typical Electro-Optical Characteristics Curves (RSH)


Forward Current vs. Forward Voltage (Ta=25°C)




Relative Luminous Intensity vs. Forward Current ($Ta=25^{\circ}C$)



Dominant Wavelength vs. Forward Current (Ta=25°C)




Max. Permissible Forwarded Current (Ta=25℃)




Typical Electro-Optical Characteristics Curves (GR)


Forward Current vs. Forward Voltage (Ta=25°C)




Relative Luminous Intensity vs. Forward Current ($Ta=25^{\circ}C$)



Dominant Wavelength vs. Forward Current (Ta=25℃)




Max. Permissible Forwarded Current(Ta=25℃)




Typical Electro-Optical Characteristics Curves (BY)


Forward Current vs. Forward Voltage (Ta=25℃)




Relative Luminous Intensity vs. Forward Current ($Ta=25^{\circ}C$)



Dominant Wavelength vs. Forward Current (Ta=25°C)




Max. Permissible Forwarded Current(Ta=25℃)





Package Dimension




Note: Tolerances unless mentioned ±0.1mm. Unit = mm




Moisture Resistant Packing Materials

Label Explanation




- · CPN: Customer's Product Number
- P/N: Product Number
- QTY: Packing Quantity
- · CAT: Luminous Intensity Rank
- · HUE: Dom. Wavelength Rank
- · REF: Forward Voltage Rank
- · LOT No: Lot Number

Reel Dimensions






Carrier Tape Dimensions: Loaded Quantity 800 pcs Per Reel



Note:

Tolerances unless mentioned ±0.1mm. Unit = mm

Moisture Resistant Packing Process




Note: Tolerances unless mentioned ±0.1mm. Unit = mm



Precautions for Use

1. Over-current-proof

1.1 Customer must apply resistors for protection, otherwise slight voltage shift will cause big current change (Burn out will happen).



2. Storage

- 2.1 Moisture proof bag should only be opened immediately prior to usage.
- 2.2 Environment should be less than 30℃ and 60% RH when moisture proof bag is opened.
- 2.3 After opening the package MSL Conditions stated on page 1 of this spec should not be exceeded.
- 2.4 If the moisture sensitivity card indicates higher than acceptable moisture, the component should be baked at min. 60deg +/-5deg for 24 hours.

3. Soldering Condition


- 3.1 Pb-free solder temperature profile
- 3.2 Reflow soldering should not be done more than two times.
- 3.3 When soldering, do not put stress on the LEDs during heating.
- 3.4 After soldering, do not warp the circuit board.

4. Soldering Iron

Each terminal is to go to the tip of soldering iron temperature less than 350° C for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.

5. Repairing

Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.





Application Restrictions

High reliability applications such as military/aerospace, automotive safety/security systems, and medical equipment may require different product. If you have any concerns, please contact Everlight before using this product in your application. This specification guarantees the quality and performance of the product as an individual component. Do not use this product beyond the specification described in this document.

DISCLAIMER

- 1. EVERLIGHT reserves the right(s) on the adjustment of product material mix for the specification.
- 2. The product meets EVERLIGHT published specification for a period of twelve (12) months from date of shipment.
- 3. The graphs shown in this datasheet are representing typical data only and do not show guaranteed values.
- 4. When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from the use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
- 5. These specification sheets include materials protected under copyright of EVERLIGHT. Reproduction in any form is prohibited without obtaining EVERLIGHT's prior consent.
- 6. This product is not intended to be used for military, aircraft, automotive, medical, life sustaining or life saving applications or any other application which can result in human injury or death. Please contact authorized Everlight sales agent for special application request.