


JIANGSU CHANGJING ELECTRONICS TECHNOLOGY CO., LTD.

AD-CJ3400 Plastic-Encapsulated MOSFET

AD-CJ3400 N-Channel MOSFET

V _{(BR)DSS}	R _{DS(on), max}	lο
30V	35mΩ @ 10V	
	40mΩ @ 4.5V	5.8A
	52mΩ @ 2.5V	



FEATURES


- High dense cell design for extremely low R_{DS(ON)}
- Exceptional on-state resistance and maximum DC current capability
- AEC-Q101 qualified

APPLICATIONS


- Load/power switching
- Interfacing switching

MARKING





 $\overline{R}0$ = Device code



AD-CJ3400 www.jscj-elec.com

MAXIMUM RATINGS (T_j = 25°C unless otherwise specified)


Parameter	Symbol	Value	Unit
Drain-source voltage	V _{DS}	30	V
Gate-source voltage	V _G s	±12	V
Continuous drain current	I _D	5.8	Α
Pulsed drain current	I _{DM} ¹⁾	30	Α
Power dissipation	P _D	350	mW
Thermal resistance from junction to ambient	R _{θJA}	357	°C/W
Operating junction and storage temperature range	T _j , T _{stg}	-55 ~ 150	°C


ELECTRICAL CHARACTERISTICS (Tj = 25°C unless otherwise specified)


Parameter	Symbol	Test condition	Min	Тур	Max	Unit
Static characteristics						
Drain-source breakdown voltage	V _{(BR)DSS}	$V_{GS} = 0V, I_{D} = 250\mu A$	30	-	-	V
Zoro goto voltago drain current	1	$V_{DS} = 24V$, $V_{GS} = 0V$, $T_j = 25$ °C	-	-	1	μΑ
Zero gate voltage drain current	IDSS	$V_{DS} = 24V$, $V_{GS} = 0V$, $T_j = 125$ °C			1	mA
Gate-source leakage current	Igss	V _{GS} = ±12V, V _{DS} = 0V	-	-	±100	nA
Gate threshold voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _D = 250μA	0.7	0.9	1.4	V
Forward transconductance	g _{fs} ²⁾	V _{DS} = 5V, I _D = 5A	8	-	-	S
		V _{GS} = 10V, I _D = 5.8A	-	25	35	
Drain-source on-state resistance	R _{DS(on)} ²⁾	V _{GS} = 4.5V, I _D = 5A	-	27	40	mΩ
		V _{GS} = 2.5V, I _D = 4A		33	52	
Dynamic characteristics 3)	•		U.			I.
Total gate charge	Qg		-	9.5	-	
Gate-source charge	Q _{gs}	$V_{DS} = 10V, V_{GS} = 6V, I_{D} = 5A$	-	1.5	-	nC
Gate-drain charge	Q_{gd}		-	3	-	
Gate resistance	Rg	V _{DS} = 0V, V _{GS} = 0V, f = 1MHz	-	3.6	-	Ω
Input capacitance	C _{iss}		-	820	1050	
Output capacitance	Coss	$V_{DS} = 15V, V_{GS} = 0V, f = 1MHz$	-	99	-	pF
Reverse transfer capacitance	C _{rss}		-	77	-	
Switching parameters 3)	•		•	•		
Turn-on delay time	t _{d(on)}		-	3.3	5	
Turn-off delay time	t _{d(off)}	V_{GS} = 10V, R_{GEN} = 3 Ω , V_{DS} =	-	4.8	7	
Rise time	t _r	15V, R_L = 2.7Ω	-	26	40	ns
Fall time	t _f		-	4	6	
Diode characteristics	•		•	•		
Drain-source diode forward voltage	V _{SD} ²⁾	I _S = 1A, V _{GS} = 0V	-	-	1	V
Continuous drain-source diode					F 0	^
forward current	ls		-	_	5.8	Α
Pulsed drain-source diode	I _{SM} 1)		_	_	30	А
forward current						, ,


¹⁾ Repetitive rating: Pulse width limited by maximum junction temperature.
2) Pulse test: Pulse width ≤ 300µs, duty cycle ≤ 2%.
3) Guaranteed by design, not subject to production.


TYPICAL CHARACTERISTICS

















SOT-23 PACKAGE OUTLINE DIMENSIONS








Symbol	Dimensions	In Millimeters	Dimensions In Inches		
Зупівої	Min	Max	Min	Max	
Α	0.900	1.150	0.035	0.045	
A1	0.000	0.100	0.000	0.004	
A2	0.900	1.050	0.035	0.041	
b	0.300	0.500	0.012	0.020	
С	0.080	0.150	0.003	0.006	
D	2.800	3.000	0.110	0.118	
E	1.200	1.400	0.047	0.055	
E1	2.250	2.550	0.089	0.100	
е	0.950	TYP	0.037	7 TYP	
e1	1.800	2.000	0.071	0.079	
L	0.550	REF	0.022	REF	
L1	0.300	0.500	0.012	0.020	
θ	0°	8°	0°	8°	

SOT-23 SUGGESTED PAD LAYOUT




Note:

- 1. Controlling dimension in millimeters.
- 2. General tolerance: ±0.05mm.
- 3. The pad layout is for reference purpose only.

SOT-23 TAPE AND REEL

SOT-23 Embossed Carrier Tape





Packaging Description:

SOT-23 parts are shipped in tape. The carrier tape is made from a dissipative (carbon filled) polycarbonate resin. The cover tape is a multilayer film (Heat Activated Adhesive in nature) primarily composed of polyester film, adhesive layer, sealant, and anti-static sprayed agent. These reeled parts in standard option are shipped with 3,000 units per 7" or 17.8cm diameter reel. The reels are clear in color and is made of polystyrene plastic (anti-static coated).

	Dimensions are in millimeter									
Pkg type A B C d E F P0 P P1 W								W		
SOT-23	3.15	2.77	1.22	Ø1.50	1.75	3.50	4.00	4.00	2.00	8.00

SOT-23 Tape Leader and Trailer





Dimensions are in millimeter								
Reel Option D D1 D2 G H I W1 W2								
7"Dia	Ø178.00	54.40	13.00	R78.00	R25.60	R6.50	9.50	12.30

REEL	Reel Size	Box	Box Size(mm)	Carton	Carton Size(mm)	G.W.(kg)
3000 pcs	7 inch	30,000 pcs	203×203×195	120,000 pcs	438×438×220	

PUBLISHED BY

JIANGSU CHANGJING ELECTRONICS TECHNOLOGY CO., LTD.

13th Floor, C Block, Tengfei Building, Yan Chuang Yuan, Nanjing Jiangbei New Area, China

LEGAL DISCLAIMER

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples, hints or typical values stated herein and/or any information regarding the application of the device, JSCJ hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of JSCJ in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

INFORMATION

For further information on technology, delivery terms and conditions as well as prices, please contact your nearest JSCJ office (www.jscj-elec.com).

WARNINGS

Due to technical requirements, products may contain dangerous substances. For information on the types in question, please contact your nearest JSCJ office.

Except as otherwise explicitly approved by JSCJ in a written document signed by authorized representatives of JSCJ, JSCJ's products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.