

#### N-Channel Enhancement-Mode Vertical DMOS FET

#### **Features**

- · Free from Secondary Breakdown
- · Low Power Drive Requirement
- · Ease of Paralleling
- Low C<sub>ISS</sub> and Fast Switching Speeds
- · Excellent Thermal Stability
- · Integral Source-Drain Diode
- · High Input Impedance and High Gain

#### **Applications**

- Logic-Level Interfaces (Ideal for TTL and CMOS)
- · Solid-State Relays
- · Battery-Operated Systems
- · Photovoltaic Drives
- · Analog Switches
- · General Purpose Line Drivers
- · Telecommunication Switches

#### **General Description**

The TN2124 low-threshold Enhancement-mode (normally-off) transistor uses a vertical Diffusion Metal-Oxide Semiconductor (DMOS) structure and a well-proven silicon gate manufacturing process. This combination produces a device with the power handling capabilities of bipolar transistors and the high input impedance and positive temperature coefficient inherent in Metal-Oxide Semiconductor (MOS) devices. Characteristic of all MOS structures, this device is free from thermal runaway and thermally induced secondary breakdown.

Microchip's vertical DMOS Field-Effect Transistors (FETs) are ideally suited to a wide range of switching and amplifying applications where very low threshold voltage, high breakdown voltage, high input impedance, low input capacitance and fast switching speeds are desired.

#### Package Type



See Table 3-1 for pin information.

#### 1.0 ELECTRICAL CHARACTERISTICS

#### **Absolute Maximum Ratings†**

Drain-to-Source Voltage	BV <sub>DSS</sub>
Drain-to-Gate Voltage	200
Gate-to-Source Voltage	200
Operating Ambient Temperature, T <sub>A</sub>	
Storage Temperature, T <sub>S</sub>	

**† Notice:** Stresses above those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress rating only, and functional operation of the device at those or any other conditions above those indicated in the operational sections of this specification is not intended. Exposure to maximum rating conditions for extended periods may affect device reliability.

#### DC ELECTRICAL CHARACTERISTICS

**Electrical Specifications:**  $T_A = 25^{\circ}$ C unless otherwise specified. All DC parameters are 100% tested at 25°C unless otherwise stated. Pulse test: 300 µs pulse, 2% duty cycle

Parameter	Sym.	Min.	Тур.	Max.	Unit	Conditions
Drain-to-Source Breakdown Voltage	BV <sub>DSS</sub>	240	_	_	V	$V_{GS}$ = 0V, $I_D$ = 1 mA
Gate Threshold Voltage	V <sub>GS(th)</sub>	0.8		2	<b>V</b>	$V_{GS} = V_{DS}$ , $I_D = 1 \text{ mA}$
Change in V <sub>GS(th)</sub> with Temperature	$\Delta V_{GS(th)}$			-5.5	mV/°C	$V_{GS} = V_{DS}$ , $I_D = 1 \text{ mA}$ (Note 1)
Gate Body Leakage Current	I <sub>GSS</sub>	_	0.1	100	nA	$V_{GS} = \pm 20V, V_{DS} = 0V$
	I <sub>DSS</sub>			1	μΑ	V <sub>GS</sub> = 0V, V <sub>DS</sub> = Maximum rating
Zero-Gate Voltage Drain Current				100	μΑ	$V_{DS}$ = 0.8 Maximum rating, $V_{GS}$ = 0V, $T_A$ = 125°C (Note 1)
On-State Drain Current	I <sub>D(ON)</sub>	140		_	mA	$V_{GS} = 4.5V, V_{DS} = 25V$
Static Drain-to-Source On-State Resistance	D	_	ı	30	Ω	$V_{GS} = 3V, I_{D} = 25 \text{ mA}$
Static Drain-to-Source On-State Nesistance	R <sub>DS(ON)</sub>			15	Ω	$V_{GS}$ = 4.5V, $I_{D}$ = 120 mA
Change in R <sub>DS(ON)</sub> with Temperature	ΔR <sub>DS(ON)</sub>		0.7	1	%/°C	V <sub>GS</sub> = 4.5V, I <sub>D</sub> = 120 mA ( <b>Note 1</b> )

Note 1: Specification is obtained by characterization and is not 100% tested.

#### **AC ELECTRICAL CHARACTERISTICS**

**Electrical Specifications:** T<sub>A</sub> = 25°C unless otherwise specified. Specification is obtained by characterization and is not 100% tested.

Parameter	Sym.	Min.	Тур.	Max.	Unit	Conditions
Forward Transconductance	G <sub>FS</sub>	100	170	_	mmho	V <sub>DS</sub> = 25V, I <sub>D</sub> = 120 mA
Input Capacitance	C <sub>ISS</sub>	_	38	50	pF	0,4,14
Common Source Output Capacitance	Coss	_	9	15	pF	V <sub>GS</sub> = 0V, V <sub>DS</sub> = 25V, If = 1 MHz
Reverse Transfer Capacitance	C <sub>RSS</sub>	_	3	5	pF	1 - 1 WI 12
Turn-On Delay Time	t <sub>d(ON)</sub>	_	4	7	ns	
Rise Time	t <sub>r</sub>	_	2	5	ns	V <sub>DD</sub> = 25V, I <sub>D</sub> = 140 mA,
Turn-Off Delay Time	t <sub>d(OFF)</sub>	_	7	10	ns	$R_{GEN} = 25\Omega$
Fall Time	t <sub>f</sub>	_	9	12	ns	
DIODE PARAMETER						
Diode Forward Voltage Drop	V <sub>SD</sub>	_	_	1.8	V	V <sub>GS</sub> = 0V, I <sub>SD</sub> = 120 mA ( <b>Note 1</b> )
Reverse Recovery Time	t <sub>rr</sub>	_	400	_	ns	V <sub>GS</sub> = 0V, I <sub>SD</sub> = 120 mA

**Note 1:** Unless otherwise stated, all DC parameters are 100% tested at +25°C. Pulse test: 300 μs pulse, 2% duty cycle

#### **TEMPERATURE SPECIFICATIONS**

Electrical Characteristics: Unless otherwise specified, for all specifications $T_A = T_J = +25$ °C.										
Parameter	Sym.	Min.	Тур.	Max.	Unit	Conditions				
TEMPERATURE RANGE										
Operating Ambient Temperature	T <sub>A</sub>	-55	_	+150	°C					
Storage Temperature	T <sub>S</sub>	-55	_	+150	°C					
PACKAGE THERMAL RESISTANCE										
3-lead SOT-23	$\theta_{\sf JA}$	_	203	_	°C/W					

#### THERMAL CHARACTERISTICS

Package	I <sub>D</sub> (Note 1) (Continuous) (mA)	I <sub>D</sub> (Pulsed) (mA)	Power Dissipation at T <sub>A</sub> = 25°C (W)	I <sub>DR</sub> (Note 1) (mA)	I <sub>DRM</sub> (mA)
3-lead SOT-23	134	250	0.36	134	250

Note 1:  $I_D$  (continuous) is limited by maximum  $T_J$ .

#### 2.0 TYPICAL PERFORMANCE CURVES

**Note:** The graphs and tables provided following this note are a statistical summary based on a limited number of samples and are provided for informational purposes only. The performance characteristics listed herein are not tested or guaranteed. In some graphs or tables, the data presented may be outside the specified operating range (e.g. outside specified power supply range) and therefore outside the warranted range.




FIGURE 2-1: Output Characteristics.





FIGURE 2-2: Transconductance vs. Drain



**FIGURE 2-3:** Maximum Rated Safe Operating Area.






FIGURE 2-4: Saturation Characteristics.



**FIGURE 2-5:** Power Dissipation vs. Temperature.



**FIGURE 2-6:** Thermal Response Characteristics.




FIGURE 2-7: Temperature.

 $BV_{DSS}$  Variation with




FIGURE 2-8:

Transfer Characteristics.




FIGURE 2-9: Capa Drain-to-Source Voltage.




FIGURE 2-10:

On-resistance vs. Drain




FIGURE 2-11: Temperature.

 $V_{(th)}$  and  $R_{DS}$  Variation with




FIGURE 2-12: Characteristics.

Gate Drive Dynamic

### **TN2124**

#### 3.0 PIN DESCRIPTION

The details on the pins of TN2124 are listed on Table 3-1. Refer to **Package Type** for the location of pins.

TABLE 3-1: PIN FUNCTION TABLE

Pin Number	Pin Name	Description						
1	Gate	Gate						
2	Source	Source						
3	Drain	Drain						

#### 4.0 FUNCTIONAL DESCRIPTION

Figure 4-1 illustrates the switching waveforms and test circuit for TN2124.





FIGURE 4-1: Switching Waveforms and Test Circuit.

TABLE 4-1: PRODUCT SUMMARY

BV <sub>DSS</sub> /BV <sub>DGS</sub> (V)	R <sub>DS(ON)</sub> (Maximum) (Ω)	V <sub>GS(th)</sub> (Maximum) (V)
240	15	2

#### 5.0 PACKAGING INFORMATION

#### 5.1 Package Marking Information




Legend: XX...X Product Code or Customer-specific information
Year code (last digit of calendar year)
YY Year code (last 2 digits of calendar year)
WW Week code (week of January 1 is week '01')
NNN Alphanumeric traceability code

By-free JEDEC® designator for Matte Tin (Sn)
This package is Pb-free. The Pb-free JEDEC designator (e3)
can be found on the outer packaging for this package.

**Note**: In the event the full Microchip part number cannot be marked on one line, it will be carried over to the next line, thus limiting the number of available characters for product code or customer-specific information. Package may or not include the corporate logo.

# 3-Lead TO-236AB (SOT-23) Package Outline (K1/T) 2.90x1.30mm body, 1.12mm height (max), 1.90mm pitch



Note: For the most current package drawings, see the Microchip Packaging Specification at www.microchip.com/packaging.

Symb	ol	Α	A1	A2	b	D	E	E1	е	e1	L	L1	θ
D	MIN	0.89	0.01	0.88	0.30	2.80	2.10	1.20	0.05	4.00	0.20 <sup>†</sup>	0.54	0°
Dimension (mm)	NOM	-	-	0.95	-	2.90	-	1.30	0.95 BSC	1.90 BSC	0.50	0.54 REF	-
()	MAX	1.12	0.10	1.02	0.50	3.04	2.64	1.40	500	500	0.60	111	8°

JEDEC Registration TO-236, Variation AB, Issue H, Jan. 1999. † This dimension differs from the JEDEC drawing.

Drawings not to scale.

## **TN2124**

NOTES:

#### APPENDIX A: REVISION HISTORY

#### Revision A (April 2018)

- Converted Supertex Doc# DSFP-TN2124 to Microchip DS20005698A
- Added some sections to comply with the standard Microchip format
- · Changed the package marking format
- Made minor text changes throughout the document

#### PRODUCT IDENTIFICATION SYSTEM

To order or obtain information, e.g., on pricing or delivery, contact your local Microchip representative or sales office.

PART NO.	<u> </u>		- <u>X</u> -		<u>X</u>	Example:	
Device	Packa Optic		 Environmental	Media	Type	a) TN2124K1-G:	N-Channel Enhancement-Mode Vertical DMOS FET, 3-lead SOT-23, 3000/Reel
Device:	TN2124	=	N-Channel Enhancemen DMOS FET	t-Mode Ve	ertical		
Package:	K1	=	3-lead SOT-23				
Environmental:	G	=	Lead (Pb)-free/RoHS-co	mpliant Pa	ickage		
Media Type:	(blank)	=	3000/Reel for a K1 Pack	age			

#### Note the following details of the code protection feature on Microchip devices:

- Microchip products meet the specification contained in their particular Microchip Data Sheet.
- Microchip believes that its family of products is one of the most secure families of its kind on the market today, when used in the intended manner and under normal conditions.
- There are dishonest and possibly illegal methods used to breach the code protection feature. All of these methods, to our knowledge, require using the Microchip products in a manner outside the operating specifications contained in Microchip's Data Sheets. Most likely, the person doing so is engaged in theft of intellectual property.
- Microchip is willing to work with the customer who is concerned about the integrity of their code.
- Neither Microchip nor any other semiconductor manufacturer can guarantee the security of their code. Code protection does not mean that we are guaranteeing the product as "unbreakable."

Code protection is constantly evolving. We at Microchip are committed to continuously improving the code protection features of our products. Attempts to break Microchip's code protection feature may be a violation of the Digital Millennium Copyright Act. If such acts allow unauthorized access to your software or other copyrighted work, you may have a right to sue for relief under that Act.

Information contained in this publication regarding device applications and the like is provided only for your convenience and may be superseded by updates. It is your responsibility to ensure that your application meets with your specifications. MICROCHIP MAKES NO REPRESENTATIONS OR WARRANTIES OF ANY KIND WHETHER EXPRESS OR IMPLIED, WRITTEN OR ORAL, STATUTORY OR OTHERWISE, RELATED TO THE INFORMATION, INCLUDING BUT NOT LIMITED TO ITS CONDITION, QUALITY, PERFORMANCE, MERCHANTABILITY OR FITNESS FOR PURPOSE. Microchip disclaims all liability arising from this information and its use. Use of Microchip devices in life support and/or safety applications is entirely at the buyer's risk, and the buyer agrees to defend, indemnify and hold harmless Microchip from any and all damages, claims, suits, or expenses resulting from such use. No licenses are conveyed, implicitly or otherwise, under any Microchip intellectual property rights unless otherwise stated.

Microchip received ISO/TS-16949:2009 certification for its worldwide headquarters, design and wafer fabrication facilities in Chandler and Tempe, Arizona; Gresham, Oregon and design centers in California and India. The Company's quality system processes and procedures are for its PIC® MCUs and dsPIC® DSCs, KEELOQ® code hopping devices, Serial EEPROMs, microperipherals, nonvolatile memory and analog products. In addition, Microchip's quality system for the design and manufacture of development systems is ISO 9001:2000 certified.

# QUALITY MANAGEMENT SYSTEM CERTIFIED BY DNV = ISO/TS 16949=

#### **Trademarks**

The Microchip name and logo, the Microchip logo, AnyRate, AVR, AVR logo, AVR Freaks, BeaconThings, BitCloud, CryptoMemory, CryptoRF, dsPIC, FlashFlex, flexPWR, Heldo, JukeBlox, KEELOQ, KEELOQ logo, Kleer, LANCheck, LINK MD, maXStylus, maXTouch, MediaLB, megaAVR, MOST, MOST logo, MPLAB, OptoLyzer, PIC, picoPower, PICSTART, PIC32 logo, Prochip Designer, QTouch, RightTouch, SAM-BA, SpyNIC, SST, SST Logo, SuperFlash, tinyAVR, UNI/O, and XMEGA are registered trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

ClockWorks, The Embedded Control Solutions Company, EtherSynch, Hyper Speed Control, HyperLight Load, IntelliMOS, mTouch, Precision Edge, and Quiet-Wire are registered trademarks of Microchip Technology Incorporated in the U.S.A.

Adjacent Key Suppression, AKS, Analog-for-the-Digital Age, Any Capacitor, Anyln, AnyOut, BodyCom, chipKIT, chipKIT logo, CodeGuard, CryptoAuthentication, CryptoCompanion, CryptoController, dsPICDEM, dsPICDEM.net, Dynamic Average Matching, DAM, ECAN, EtherGREEN, In-Circuit Serial Programming, ICSP, Inter-Chip Connectivity, JitterBlocker, KleerNet, KleerNet logo, Mindi, MiWi, motorBench, MPASM, MPF, MPLAB Certified logo, MPLIB, MPLINK, MultiTRAK, NetDetach, Omniscient Code Generation, PICDEM, PICDEM.net, PICkit, PICtail, PureSilicon, QMatrix, RightTouch logo, REAL ICE, Ripple Blocker, SAM-ICE, Serial Quad I/O, SMART-I.S., SQI, SuperSwitcher, SuperSwitcher II, Total Endurance, TSHARC, USBCheck, VariSense, ViewSpan, WiperLock, Wireless DNA, and ZENA are trademarks of Microchip Technology Incorporated in the U.S.A. and other countries.

 $\ensuremath{\mathsf{SQTP}}$  is a service mark of Microchip Technology Incorporated in the U.S.A.

Silicon Storage Technology is a registered trademark of Microchip Technology Inc. in other countries.

GestIC is a registered trademark of Microchip Technology Germany II GmbH & Co. KG, a subsidiary of Microchip Technology Inc., in other countries.

All other trademarks mentioned herein are property of their respective companies.

© 2018, Microchip Technology Incorporated, All Rights Reserved. ISBN: 978-1-5224-2937-1



#### **Worldwide Sales and Service**

#### **AMERICAS**

Corporate Office 2355 West Chandler Blvd. Chandler, AZ 85224-6199 Tel: 480-792-7200

Tel: 480-792-7200 Fax: 480-792-7277 Technical Support:

http://www.microchip.com/ support

Web Address:

www.microchip.com

Atlanta
Duluth, GA
Tel: 678-957-96

Tel: 678-957-9614 Fax: 678-957-1455

**Austin, TX** Tel: 512-257-3370

Boston

Westborough, MA Tel: 774-760-0087 Fax: 774-760-0088

Chicago Itasca, IL

Tel: 630-285-0071 Fax: 630-285-0075

**Dallas** Addison, TX

Tel: 972-818-7423 Fax: 972-818-2924

**Detroit** Novi, MI

Tel: 248-848-4000

Houston, TX

Tel: 281-894-5983 Indianapolis

Noblesville, IN Tel: 317-773-8323 Fax: 317-773-5453 Tel: 317-536-2380

Los Angeles

Mission Viejo, CA Tel: 949-462-9523 Fax: 949-462-9608 Tel: 951-273-7800

**Raleigh, NC** Tel: 919-844-7510

New York, NY Tel: 631-435-6000

**San Jose, CA** Tel: 408-735-9110 Tel: 408-436-4270

**Canada - Toronto** Tel: 905-695-1980 Fax: 905-695-2078

#### ASIA/PACIFIC

Australia - Sydney Tel: 61-2-9868-6733

**China - Beijing** Tel: 86-10-8569-7000

China - Chengdu Tel: 86-28-8665-5511

China - Chongqing Tel: 86-23-8980-9588

**China - Dongguan** Tel: 86-769-8702-9880

**China - Guangzhou** Tel: 86-20-8755-8029

China - Hangzhou Tel: 86-571-8792-8115

China - Hong Kong SAR Tel: 852-2943-5100

**China - Nanjing** Tel: 86-25-8473-2460

China - Qingdao Tel: 86-532-8502-7355

China - Shanghai Tel: 86-21-3326-8000

China - Shenyang Tel: 86-24-2334-2829

**China - Shenzhen** Tel: 86-755-8864-2200

China - Suzhou Tel: 86-186-6233-1526

China - Wuhan

Tel: 86-27-5980-5300 **China - Xian** Tel: 86-29-8833-7252

China - Xiamen
Tel: 86-592-2388138

**China - Zhuhai** Tel: 86-756-3210040

#### ASIA/PACIFIC

India - Bangalore Tel: 91-80-3090-4444

India - New Delhi Tel: 91-11-4160-8631

India - Pune Tel: 91-20-4121-0141

Japan - Osaka

Tel: 81-6-6152-7160

Japan - Tokyo

Tel: 81-3-6880- 3770

**Korea - Daegu** Tel: 82-53-744-4301

Korea - Seoul Tel: 82-2-554-7200

Malaysia - Kuala Lumpur Tel: 60-3-7651-7906

Malaysia - Penang Tel: 60-4-227-8870

Philippines - Manila Tel: 63-2-634-9065

**Singapore** Tel: 65-6334-8870

**Taiwan - Hsin Chu** Tel: 886-3-577-8366

Taiwan - Kaohsiung Tel: 886-7-213-7830

**Taiwan - Taipei** Tel: 886-2-2508-8600

Thailand - Bangkok Tel: 66-2-694-1351

**Vietnam - Ho Chi Minh** Tel: 84-28-5448-2100

#### **EUROPE**

**Austria - Wels** Tel: 43-7242-2244-39 Fax: 43-7242-2244-393

**Denmark - Copenhagen** Tel: 45-4450-2828 Fax: 45-4485-2829

Finland - Espoo Tel: 358-9-4520-820

France - Paris
Tel: 33-1-69-53-63-20
Fax: 33-1-69-30-90-79

Germany - Garching Tel: 49-8931-9700

**Germany - Haan** Tel: 49-2129-3766400

Germany - Heilbronn Tel: 49-7131-67-3636

Germany - Karlsruhe Tel: 49-721-625370

**Germany - Munich** Tel: 49-89-627-144-0 Fax: 49-89-627-144-44

Germany - Rosenheim Tel: 49-8031-354-560

Israel - Ra'anana Tel: 972-9-744-7705

Italy - Milan Tel: 39-0331-742611 Fax: 39-0331-466781

Italy - Padova Tel: 39-049-7625286

**Netherlands - Drunen** Tel: 31-416-690399 Fax: 31-416-690340

Norway - Trondheim Tel: 47-7289-7561

**Poland - Warsaw** Tel: 48-22-3325737

Romania - Bucharest Tel: 40-21-407-87-50

**Spain - Madrid** Tel: 34-91-708-08-90 Fax: 34-91-708-08-91

**Sweden - Gothenberg** Tel: 46-31-704-60-40

Sweden - Stockholm Tel: 46-8-5090-4654

**UK - Wokingham** Tel: 44-118-921-5800 Fax: 44-118-921-5820