

表面贴装保险丝

DOC.No.:

INDIVIDUAL SPECIFICATION SHEET

Product Name: 表面贴装保险丝

Part Number: TA10

Revision: C







Dongguan TLC Electronic Technology Co., LTD

No.18,5th GaoLi Road,TangXia Town,DongGuan,GuangDong,P.R China 523710

TEL: 86-0769-3892 0511 FAX: 86-0769-8793 2077

Http: www.tlcet.com.cn

Rev.	Effective Date	Changed Contents
Α	2021-2-25	New Release
В	2021-6-10	Update Spedfications
С	2021-11-16	变更包装数量

The individual specification sheet are the property of Dongguan TLC electronic technology Co.,Ltd and shall not be copied or used as commercial purposes without permission.

PREPARED BY	APPROVED BY
杨峰	A Mag



1.产品特性及应用范围 / Description, Features and Applications

本产品适用于各类电子设备电路初、次级电路板的过流保护,广泛应用于绿色照明、消费电子、电源供应、网络通信、医疗仪器及工业控制器等领域。

Descriptions:

TLC TA series slow-blow square Surface Mount fuses are ceramic tube/end cap constructions, RoHS compliant, Halogen Free and lead(Pb) exempts of the requirements of RoHS Directive(2002/95/EC), with U.S. (UL/CSA) safety agency approvals. Provide board level primary and secondary circuit protection in a wide variety of applications. With excellent inrush current withstanding capability, excellent reliability for thermal and mechanic shock, also have a high reliability and stable solder ability, end caps are available in gold/silver/nickel plated.

Features:

Time-Lag (Slow-Blow) Small size(6.1mm*2.5mm)

Wide range of current rating available Wide operating temperature range

Low temperature de-rating RoHS compliant

Tape and Reel for automatic placement Conflict free metals

Applications:

LED lighting	Notebook PC	Battery devices	LCD/PDP devices
LCD backlight inverter	Portable Devices	Power supply	Networking devices
PC server	Cooling fan system	Storage system	Telecom system
Wireless base station	White goods	Game console	Office equipment
Digital camera	Industrial equipment	Medical equipment	Automotive devices

2.安规认证标准及编号 / Standards and Agency Approvals

2.1 执行标准: 遵循 UL 248-14。 Standards: In accordance with UL 248-14.

2.2 认证范围 Certification:

安规标准 Agency	认证范围 Ampere Range	证书编号 Agency File Number
(UL)	50mA ~ 15A	E467707(JDYX2)
راك)	50mA ~ 15A	E467707(JDYX8)



2.3 目录编号 Catalogue No., ● 已认证 Approved / ○ 认证中 Pending

目录编号 Catalog No.	额定电流 Ampere Rating	额定电压 Voltage Rating	分断能力 Breaking Capacity	冷阻值 Nominal Cold				冷阻值 Nominal Cold				熔化热能 I ² TMelting Integral(A2.S)	TMelting	观认证 Approvals	
No.	Rating	Rating	Capacity	Resistance (Ohms)	mogran(A2.0)										
TA10	10A	125Vac	200A@125VAC	0.007	284.025	•	•								


- *: These catalog no. cold resistance and I2t value are pending due to fuse elements shall be customized;
- ➤ DC Cold Resistance are measured at <10% of rated current in ambient temperature of 25°C;
- > Typical Pre-arching I2t are calculated at 10*In Current or 8ms;

3.产品标示 / Product Marking

保险丝上需有下列标示 / The fuses shall have the following markings 示例 Example:

注:对于标示的大小和位置没有规定 / Note: Size and position of the markings shall not be provided.

4.结构及尺寸 / Dimensions and Structure



5.材料明细 / Material Details

编 号 NO.	零 件 名 称 Part Name	材 质 Material
1)	端帽 End caps	黄铜镀金 Au Plated Brass Cap
2	主体 Body	陶瓷管 Non-Transparent Square Ceramic Tube
3	熔丝 Fuse element	合金 Cu-Ag Alloy wire



6.产品特性 / Product Characteristics

编号 NO.	项目 Item	内容 Content	参考标准 Reference standards	
1	产品标识 Product Marking	Brand, Ampere Rating	TLC marking standards	
2	工作温度 Operating Temperature	-55°C to 125°C	IEC60068-2-1/2	
3	可焊性 Solderability	T=240°C±5°C , t=3sec±0.5sec, Coverage≥95%	MIL-STD-202, Method 208	
4	耐焊接热 Resistance to Soldering Heat	10 sec at 260°C	MIL-STD-202, Method 210, Test condition B	
5	绝缘阻抗 Insulation Resistance (after Opening)	10,000 ohms minimum	MIL-STD-202, Method 302, Test Condition A	
6	热冲击 Thermal Shock			
7	机械冲击 100G's peak for 6 milliseconds, Mechanical Shock 3cycles		MIL-STD-202, Method 213, Test I	
8	振动试验 Vibration	0.03"amplitude, 10-55 Hz in 1 min. 2hrs each XYZ=6hrs	MIL-STD-202, Method 201	
9	耐湿性 Moisture Resistance	10 cycles	MIL-STD-202, Method 106	
10	盐雾试验 Salt Spray	5% salt solution, 48hrs	MIL-STD-202, Method 101, Test Condition B	

7.电气特性 / Electrical Characteristics

7.1 实验条件: Test Condition

所有测试环境温度为 25±5℃。

All electrical test is to be conducted with the ambient air at a temperature of 25±5℃.

7.2 分断能力 Interrupting Rating:


保险丝承受分断能力: 200A@125Vac. Breaking Capacity: 200A@125Vac.



7.3 熔断时限 / Operating Characteristics

额定电流的%	熔断时间		
% of Ampere Rating(In)	Blowing Time		
100% * In	大于 4 小时(4 hours Min)		
200% * In	小于 120 秒 (120 sec Max)		
1000% * In	大于 10 毫秒 (10ms Min)		

7.4 平均时间电流曲线图 / Average Time Current Curves






8.环境特性 / Environmental Characteristic

若操作环境温度超出 **25±5**℃范围,在选用保险丝规格时,需考虑操作环境温度对保险丝的影响,请参照如下:温度-电流曲线图。

When choosing the fuse's specification, if the operating environmental temperature beyond the scope from 20~30°C, engineer should consider the environmental temperature's affection to fuses.

Please refer: Temperature Rerating Curve:




9.建议焊接参数 / Recommended Soldering Parameters

A.波峰/回流焊参数 / Wave /Reflow Soldering Parameters:

锡膏工艺 / Solder paste process.

锡炉温度 / Solder Pot Temperature: 260°C Max; 焊接时间 / Solder Dwell Time: 5 seconds max

R	eflow Condition	Pb-Free assembly		
Average r	amp-up rate (Ts(max)to Tp)	5°C /second max.		
	Temperature Min (Ts(min))	150°C		
Preheat	Temperature Max	200°C		
	Time (Min to Max) (ts)	60-120 seconds		
Reflow	Temperature (TL)	220°C		
Reliow	Time Max (tL)	60 seconds		
Peak Tem	perature(Tp)	260°C max		
Ramp-dov	vn Rate	5°C/second max		
Time 25°C	to peak Temperature (Tp)	8 minutes max		



B.手工焊参数 / Hand-Solder Parameters:


烙铁温度 / Solder Iron Temperature: 300±5℃

焊接时间 / Heating Time: 1~2 s Max



10.包装 / Packaging

1500 个每卷/ 1,500 pcs in 7 inches dia. reel, 12mm wide tape, EIA Standard 481



Item	Α	В	В		D		E	W1	W2
Spec.(mm)	178±0.10	60±0.50	13±0.20		21±0.20		2.2±0.20	12.5±0.20	14.5±0.20
Item A0		B0			D0 D1		E	F	
Spec.(mm)	Spec.(mm) 2.70±0.10		6.40±0.10 1.50+0.10		1.	50+0.25	1.75±0.10	5.50±0.10	
Item	K0	P0		ŀ	P1		P2	W	t
Spec.(mm) 2.70±0.10		4.00±0	.10	4.00	±0.10	2.0	00±0.10	12.00±0.15	0.25±0.05

11.其他 / Others

11.1 如果在使用中有超出本规格书的要求,须经双方协商确认。

In the event that an impropriety is found beyond this specification, it shall be fixed by mutual agreement between the parties.

11.2 如果本规格书有不适当的情况,须通过双方协商并由本公司修改。

In the event that an impropriety is found in this specification, TLC. shall amend it by mutual agreement between the parties.