



MBR2040CT~MBR20200CT

20 AMPERES SCHOTTKY BARRIER RECTIFIERS

VOLTAGE 40 to 200 Volts

CURRENT 20 Amperes


FEATURES

- Plastic package has Underwriters Laboratory Flammability Classification 94V-0. Flame Retardant Epoxy Molding Compound.
- Metal silicon junction, majority carrier conduction
- Low power loss, high efficiency.
- High current capability
- For use in low voltage, high frequency inverters free wheeling, and polarity protection applications.
- Lead free in comply with EU RoHS

MECHANICAL DATA

- Case: TO-220AB molded plastic
- Terminals: Solder plated, solderable per MIL-STD-750, Method 2026
- Polarity: As marked.
- Mounting Position: Any

TO-220AB



MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified. Single phase, half wave, 60 Hz, resistive or inductive load.

For capacitive load, derate current by 20%

PARAMETER	SYMBOL	MBR 2040CT	MBR 2045CT	MBR 2050CT	MBR 2060CT	MBR 2080CT	MBR 2090CT	MBR 20100CT	MBR 20120CT	MBR 20150CT	MBR 20200CT	UNITS
Maximum Recurrent Peak Reverse Voltage	V_{RRM}	40	45	50	60	80	90	100	120	150	200	V
Maximum RMS Voltage	V_{RMS}	28	31.5	35	42	56	63	70	84	105	140	V
Maximum DC Blocking Voltage	V_{DC}	40	45	50	60	80	90	100	120	150	200	V
Maximum Average Forward Current (See fig.1)	$I_{F(AV)}$	20										A
Peak Forward Surge Current :8.3ms single half sine- wave superimposed on rated load(JEDEC th d)	I_{FSM}	150A										A
Maximum Forward Voltage at 10A, per leg	V_F	0.7		0.8		0.85			0.92			V
Maximum DC Reverse Current $T_J=25^\circ\text{C}$ at Rated DC Blocking Voltage $T_J=125^\circ\text{C}$	I_R	0.05 10										mA
Typical Thermal Resistance	$R_{\theta JC}$	2										$^\circ\text{C} / \text{W}$
Operating Junction and Storage Temperature Range	T_J, T_{STG}	-50 to +150									-55 to +175	$^\circ\text{C}$



RATING AND CHARACTERISTIC CURVES

