## **FR101 THRU FR107**

## **FAST RECOVERY RECTIFIERS**

Reverse Voltage - 50 to 1000 V Forward Current - 1 A


#### I OI Wald Cullett - 17

#### **Features**

- High current capability
- High reliability
- Low leakage

### **Mechanical Data**

- Case: Molded plastic, DO-41
- Epoxy: UL 94V-0 rate flame retardant
- Lead: Axial leads, solderable per MIL-STD-202, Method 208 guaranteed
- Polarity: Color band denotes cathode end
- Mounting Position: Any



Dimensions in inches and (millimeters)

## **Maximum Ratings and Electrical Characteristics**

Ratings at 25 °C ambient temperature unless otherwise specified. Single phase, half-wave, 60 Hz, resistive or inductive load, for capacitive load, derate current by 20%.

| Parameter   | Symbols            | FR101         | FR102 | FR103 | FR104 | FR105 | FR106 | FR107 | Units |
|---|--------------------|---------------|-------|-------|-------|-------|-------|-------|-------|
| Maximum Recurrent Peak Reverse Voltage  | $V_{RRM}$          | 50            | 100   | 200   | 400   | 600   | 800   | 1000  | V     |
| Maximum RMS Voltage   | V <sub>RMS</sub>   | 35            | 70    | 140   | 280   | 420   | 560   | 700   | V     |
| Maximum DC Blocking Voltage   | $V_{DC}$           | 50            | 100   | 200   | 400   | 600   | 800   | 1000  | V     |
| Maximum Average Forward Rectified Current 0.375" (9.5 mm) Lead Length at $T_A = 55$ °C                  | I <sub>F(AV)</sub> | 1             |       |       |       |       |       |       | А     |
| Peak Forward Surge Current 8.3 ms Single Half<br>Sine-Wave Superimposed on Rated Load (JEDEC<br>Method) | I <sub>FSM</sub>   | 30            |       |       |       |       |       |       | А     |
| Maximum Forward Voltage at 1 A  | V <sub>F</sub>     | 1.3           |       |       |       |       |       | V     |       |
| Maximum Reverse Current $T_A = 25$ °C at Rated DC Blocking Voltage $T_A = 100$ °C                       | I <sub>R</sub>     | 5<br>500      |       |       |       |       |       |       | μΑ    |
| Typical Junction Capacitance 1)   | CJ                 | 15            |       |       |       |       |       |       | pF    |
| Typical Thermal Resistance 2)   | $R_{\theta JA}$    | 50            |       |       |       |       |       |       | °C/W  |
| Maximum Reverse Recovery Time 3)  | t <sub>rr</sub>    |               | 15    | 50    |       | 250   | 50    | 00    | nS    |
| Operating and Storage temperature range   | $T_j$ , $T_{stg}$  | - 55 to + 150 |       |       |       |       |       | °C    |       |


<sup>1)</sup> Measured at 1 MHz and applied reverse voltage of 4 V D.C.



<sup>&</sup>lt;sup>2)</sup> Thermal resistance from junction to ambient 0.375"(9.5 mm) lead length P.C.B mounted.

<sup>&</sup>lt;sup>3)</sup> Reverse recovery test conditions:  $I_F = 0.5 \text{ A}$ ,  $I_R = 1 \text{ A}$ ,  $I_{rr} = 0.25 \text{ A}$ .

# **FR101 THRU FR107**






FIG.3- TYPICAL FORWARD CHARACTERISTICS




FIG.4- TYPICAL JUNCTION CAPACITANCE




FIG.5- REVERSE RECOVERY TIME CHARACTERISTIC AND TEST CIRCUIT DIAGRAM

