

# KBL6005 THRU KBL610

## **BRIDGE RECTIFIERS**

#### **FEATURES**

- · UL Recognized File # E469616
- · Reliable low cost construction utilizing molded plastic technique
- · Ideal for printed circuit board
- · Low forward voltage drop
- · Low reverse leakage current
- · High surge current capability
- · Glass passivated chip junctions


#### **MECHANICAL DATA**

Case: Molded plastic, KBL

Epoxy: UL 94V-O rate flame retardant

Terminals: Leads solderable per MIL-STD-202,

method 208 guaranteed Mounting position: Any Weight: 0.2ounce, 5.6gram



Dimensions in inches and (millimeters)

### Maximum Ratings and Electrical Characteristics

Ratings at 25 ambient temperature unless otherwise specified.

Single phase, half wave,  $60H_Z$ , resistive or inductive load.

For capacitive load, derate current by 20%.

	Symbols	KBL6005	KBL601	KBL602	KBL604	KBL606	KBL608	KBL610	Units
Maximum Recurrent Peak Reverse Voltage	$V_{RRM}$	50	100	200	400	600	800	1000	Volts
Maximum RMS Voltage	V <sub>RMS</sub>	35	70	140	280	420	560	700	Volts
Maximum DC Blocking Voltage	V <sub>DC</sub>	50	100	200	400	600	800	1000	Volts
Maximum Average Forward Rectified Current .5"(12.7mm) Lead Length at T <sub>A</sub> =50	I <sub>(AV)</sub>	6.0							Amp
Peak Forward Surge Current,									
8.3ms single half-sine-wave	I <sub>FSM</sub> 120							Amp	
superimposed on rated load (JEDEC method)									
Maximum Forward Voltage at 6.0A DC and 25	$V_{\mathrm{F}}$	1.1							Volts
Maximum Reverse Current at T <sub>A</sub> =25		10.0							uAmp
at Rated DC Blocking Voltage T <sub>A</sub> =100	$I_R$	500							
Typical Junction Capacitance (Note 1)	$C_{J}$	40							pF
Typical Thermal Resistance (Note 2)	$R_{\theta JA}$	19							/W
Typical Thermal Resistance (Note 3)	$R_{\theta JL}$	2.4							/W
Operating and Storage Temperature Range	T <sub>J</sub> , Tstg			-	-55 to +150	0			

#### **NOTES:**


- 1- Measured at 1 MHz and applied reverse voltage of 4.0 VDC.
- 2- Thermal resistance from junction to ambient with units mounted on 3.0 x 3.0 x 0.11" thick (7.5 x 7.5 x 0.3cm) Al. plate
- 3- Thermal resistance from junction to lead with units mounted on P.C.B. at 0.375" (9.5mm) lead length and 0.5 x 0.5" (12 x 12mm) copper pads







# BRIDGE RECTIFIERS


### Characteristic Curves (T<sub>A</sub>=25 <sup>°</sup>C unless otherwise noted)







#### FIG.3-TYPICAL FORWARD **CHARACTERISTICS**



#### FIG.4-TYPICAL REVERSE **CHARACTERISTICS**

