


# RL201 THRU RL207 SILICON RECTIFIERS

### FEATURES

- Plastic package has Underwriters Laboratory Flammability Classification 94V-O ctilizing Flame Retardant Epoxy Molding Compound.
- $\cdot$  2.0 ampere operation at  $T_A\!\!=\!\!75$   $\,$  with no
- thermal runaway.
- · Exceeds environmental standards of MIL-S-19500/228

#### MECHANICAL DATA

Case: Molded plastic, DO-15 Epoxy: UL 94V-O rate flame retardant Lead: Axial leads, solderable per MIL-STD-202, method 208 guaranteed Polarity: Color band denotes cathode end Mounting position: Any Weight: 0.015ounce, 0.4gram



Dimensions in inches and (millimeters)

D®

东钜兴电子科技有限公司

## Maximum Ratings and Electrical Characteristics

Ratings at 25 ambient temperature unless otherwise specified. Single phase, half wave,  $60H_Z$ , resistive or inductive load. For capacitive load, derate current by 20%.

	Symbols	RL201	RL202	RL203	RL204	RL205	RL206	RL207	Units
Maximum Recurrent Peak Reverse Voltage	V <sub>RRM</sub>	50	100	200	400	600	800	1000	Volts
Maximum RMS Voltage	V <sub>RMS</sub>	35	70	140	280	420	560	700	Volts
Maximum DC Blocking Voltage	V <sub>DC</sub>	50	100	200	400	600	800	1000	Volts
Maximum Average Forward Rectified Current	т	2.0							Amp
.375"(9.5mm) Lead Length at T <sub>A</sub> =75	I <sub>(AV)</sub>								
Peak Forward Surge Current,									
8.3ms single half-sine-wave	I <sub>FSM</sub>	I <sub>FSM</sub> 60							Атр
superimposed on rated load (JEDEC method)									
Maximum Forward Voltage	V <sub>F</sub>	1.1							Volts
at 2.0A DC and 25	۷F								
Maximum Reverse Current at T <sub>A</sub> =25	Т	5.0 500							uAmp
at Rated DC Blocking Voltage T <sub>A</sub> =100	I <sub>R</sub>								
Typical Junction Capacitance (Note 1)	CJ	20							pF
Typical Thermal Resistance (Note 2)	$R_{\theta JA}$	40							/W
Operating Junction Temperature Range	T <sub>J</sub>	-55 to +125							
Storage Temperature Range	Tstg	-55 to +125							


#### NOTES:


1- Measured at 1 MHz and applied reverse voltage of 4.0 VDC.

2- Thermal Resistance Junction to Ambient and form junction to lead at 0.375"(9.5mm) lead length P.C.B. Mounted.



## **RATINGS AND CHARACTERISTIC CURVES**





G