








GENERAL TOLERANCE										USED ON
10 MAX	30 MAX	50 MAX	70 MAX	100 MAX	120 MAX	250 MAX	250 OVR	ANGLE	ECCENT	
±0.15	±0.20	±0.30	±0.40	±0.50	±0.75	±0.90	±1.4	±0.5°	0.1	










- NOTES
1. MATERIAL : SEE TABLE
  2. GENERAL TOLERANCE : SEE TABLE
  3. APPLICABLE HEADER : 104212-6411
  4. APPLICABLE TERMINAL :

TERMINAL SERIES	PART NO	CRIMPING RANGE	
		SO	WIRE
025	98658-1211	0.30-0.50	AVSS
	98658-1213	0.22-0.50	CHFUS
060	98195-1211	0.30-0.50	AVSS
	98195-1212	0.50-0.85	AVSS

NO	DESCRIPTION	MATERIAL	QUANTITY
2	TPA	PBT (YELLOW)	1
1	025 060 HYB FEMALE 20P	PBT (BLACK)	1

<b>REVISED</b> EC NO: KTR2018-0010 DRWN: JWK1M02 2017/09/13 CHKD: APPR: JHJANG 2017/09/14	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE	SCALE	DESIGN UNITS	<b>025 060 HYB FEMALE CONNECTOR ASSY 20P</b>   SD-104213-003	THIRD ANGLE PROJECTION																										
	$F_A=0$ $F_G=0$ $F_P=0$	<table border="1"> <thead> <tr> <th></th> <th>mm</th> <th>INCH</th> </tr> </thead> <tbody> <tr> <td>4 PLACES</td> <td>± ---</td> <td>± ---</td> </tr> <tr> <td>3 PLACES</td> <td>± ---</td> <td>± ---</td> </tr> <tr> <td>2 PLACES</td> <td>± ---</td> <td>± ---</td> </tr> <tr> <td>1 PLACE</td> <td>± ---</td> <td>± ---</td> </tr> <tr> <td>0 PLACE</td> <td>± ---</td> <td>± ---</td> </tr> </tbody> </table>		mm	INCH			4 PLACES	± ---	± ---	3 PLACES	± ---	± ---	2 PLACES	± ---	± ---	1 PLACE	± ---	± ---	0 PLACE	± ---	± ---	<table border="1"> <thead> <tr> <th>mm ONLY</th> <th>DATE</th> </tr> </thead> <tbody> <tr> <td>DRAWN BY: JWK1M02</td> <td>2015/05/14</td> </tr> <tr> <td>CHECKED BY: BCY00N</td> <td>DATE</td> </tr> <tr> <td>APPROVED BY: JYCHOI</td> <td>2015/05/15</td> </tr> </tbody> </table>	mm ONLY	DATE	DRAWN BY: JWK1M02	2015/05/14	CHECKED BY: BCY00N	DATE	APPROVED BY: JYCHOI	2015/05/15	2:1	METRIC
		mm	INCH																														
4 PLACES	± ---	± ---																															
3 PLACES	± ---	± ---																															
2 PLACES	± ---	± ---																															
1 PLACE	± ---	± ---																															
0 PLACE	± ---	± ---																															
mm ONLY	DATE																																
DRAWN BY: JWK1M02	2015/05/14																																
CHECKED BY: BCY00N	DATE																																
APPROVED BY: JYCHOI	2015/05/15																																
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	SEE TABLE	MATERIAL NO. DOCUMENT NO. SHEET NO. THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	TITLE 1 OF 1																														

GENERAL TOLERANCE										USED ON
10 MAX	30 MAX	50 MAX	70 MAX	100 MAX	120 MAX	250 MAX	250 OVR	ANGLE	ECCENT	
±0.15	±0.20	±0.30	±0.40	±0.50	±0.75	±0.90	±1.4	±0.5°	0.1	



- NOTES
1. MATERIAL : SEE TABLE
  2. GENERAL TOLERANCE : SEE TABLE
  3. APPLICABLE HEADER : 104212-6411
  4. APPLICABLE TERMINAL :

TERMINAL SERIES	PART NO	CRIMPING RANGE	
		SO	WIRE
025	98658-1211	0.30-0.50	AVSS
	98658-1213	0.22-0.50	CHFUS
060	98195-1211	0.30-0.50	AVSS
	98195-1212	0.50-0.85	AVSS

NO	DESCRIPTION	MATERIAL	QUANTITY
2	TPA	PBT (YELLOW)	1
1	025 060 HYB FEMALE 20P	PBT (BLACK)	1

△ B	1042132011	104213-2011
	MATERIAL NO.	ORDER NO.

REVISED  
EC NO: KTR2018-0010  
DRWN: JWK1M02 2017/09/13  
CHKD:  
APPR: JHJANG 2017/09/14

QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)	
	mm	INCH
$F_A=0$	4 PLACES ± --- ± ---	
$F_G=0$	3 PLACES ± --- ± ---	
$F_P=0$	2 PLACES ± --- ± ---	
	1 PLACE ± --- ± ---	
	0 PLACE ± --- ± ---	
	ANGULAR ± --- °	

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

DIMENSION STYLE		SCALE
MM ONLY		2:1
DRAWN BY	DATE	TITLE
JWK1M02	2015/05/14	025 060 HYB FEMALE CONNECTOR ASSY 20P
CHECKED BY	DATE	
BCYOON		
APPROVED BY	DATE	
JYCHOI	2015/05/15	
MATERIAL NO.	DOCUMENT NO.	
SEE TABLE	SD-104213-003	

DESIGN UNITS: METRIC

THIRD ANGLE PROJECTION

**molex**

SD-104213-003

SHEET NO. 1 OF 1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION