

# Superfast Recovery Rectitiers

#### **FEATURES**

- · Glass Passivated chip junction
- · High surge capability
- · Low forward voltage, high current capability
- · Hermetically sealed
- · Superfast recovery times
- · Exceeds environmental standards of MIL-S-19500/228
- · Low leakage.

#### **MECHANICAL DATA**

Case: Molded plastic, DO-201AD Epoxy: UL 94V-O rate flame retardant

Lead: Axial leads, solderable per MIL-STD-202,


method 208 guaranteed

Polarity: Color band denotes cathode end

For capacitive load, derate current by 20%.

Mounting position: Any Weight: 0.04ounce, 1.1gram

#### DO-201AD(DO-27)



Dimensions in inches and (millimeters)

### Maximum Ratings and Electrical Characteristics

Ratings at 25 ambient temperature unless otherwise specified. Single phase, half wave, 60Hz, resistive or inductive load.

Parameter	Symbol	SFA06	Units
Maximum Recurrent Peak Reverse Voltage	$V_{ m RRM}$	400	V
Maximum RMS Voltage	$V_{ m RMS}$	280	V
Maximum DC blocking Voltage	$V_{ m DC}$	400	V
Maximum Average Forward Rectified Current at $T_C = 100$ °C	$I_{\mathrm{F(AV)}}$	10.0	A
Peak Forward Surge Current 8.3ms single half sine-wave superimposed on rated load (JEDEC method)	$I_{ m FSM}$	120	A
Maximum Reverse Recovery Time (Note 1)	$t_{\rm rr}$	35	nS
Typical Junction Capacitance (Note 2)	C <sub>J</sub>	50	pF
Operation Junction Temperature and Storage Temperature	$T_{ m J},T_{ m STG}$	-55 to +175	°C

#### **ELECTRICAL CHARACTERISTICS** (T<sub>C</sub>=25°C unless otherwise noted)

Parameter		Symbol	Тур	Max	Units
Maximum Forward Voltage	at 10.0A DC	$V_{ m F}$	1.10	1.25	V
Maximum DC Reverse Current	@T <sub>A</sub> =25°C	7		10	4
at rated DC blocking voltage	$@T_A = 100^{\circ}C$	$I_{ m R}$		100.0	μΑ

#### THERMAL CHARACTERISTICS (T<sub>C</sub>=25°C unless otherwise noted)

		,	
Parameter	Symbol	SFA06	Units
Typical Thermal Resistance (Note 3)	$R_{(JC)}$	6.5	°C/W

#### Note:

- 1. Test Conditions: I<sub>F</sub>=0.5A, I<sub>R</sub>=1.0A, I<sub>RR</sub>=0.25A
- 2. Measured at 1.0 MHz and applied reverse voltage of 4.0Vdc
- 3. Thermal Resistance From Junction to Case





# Superfast Recovery Rectitiers

## Characteristic Curves ( $T_A$ =25 $^{\circ}$ C unless otherwise noted)

FIG.1-TYPICAL FORWARD CURRENT DERATING CURVE




FIG.2-TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS




FIG.3-MAXIMUN NON-REPETITIVE FORWARD SURGE CURRENT





FIG.4-TYPICAL REVERSE



# FIG.5-TEST CIRCUIT DIAGRAM AND REVERSE RECOVERY TIME CHARACTERSITIC

