

This document was generated on 10/25/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 47018-2000

Status: Active

Overview: Serial ATA Host Receptacles

Description: 1.27mm Pitch Serial ATA Host Receptacle, Mating Height 4.30mm, Gold (Au) Flash,

Light Tin Solder Area, Surface Mount, Right Angle, Top Mount Type, 22 Circuits, Lead-

Free

Documents:

<u>3D Model</u> <u>Product Specification PS-67492-001 (PDF)</u>
<u>Drawing (PDF)</u> <u>RoHS Certificate of Compliance (PDF)</u>



CSA LR19980 UL E29179

General

Product Family PCB Receptacles

Series <u>47018</u>

Application Board-to-Board, Signal Comments Top Mount Type

Overview <u>Serial ATA Host Receptacles</u>

Product Name Serial ATA UPC 822350127677

Physical

22 Circuits (Loaded) Circuits (maximum) 22 Color - Resin Black Durability (mating cycles max) 500 Flammability 94V-0 **Glow-Wire Compliant** No Keying to Mating Part Yes Lock to Mating Part None Material - Metal Copper Alloy

Material - Plating Mating
Material - Plating Termination
Net Weight
Number of Rows
Gold
Tin
1.839/g


Orientation Right Angle 1.60mm PC Tail Length **PCB** Locator Yes **PCB** Retention Yes Packaging Type Tray Pitch - Mating Interface 1.27mm Pitch - Termination Interface 1.27mm Plating min - Termination 2.032µm Polarized to Mating Part Yes Polarized to PCB Yes Surface Mount Compatible (SMC) N/A

Temperature Range - Operating -35°C to +85°C Termination Interface: Style Surface Mount

Electrical

Current - Maximum per Contact 1.5A Voltage - Maximum 15V DC

Solder Process Data



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Low-Halogen



Need more information on product environmental compliance?

Email <u>productcompliance@molex.com</u>
For a multiple part number RoHS Certificate of Compliance, click here

Please visit the <u>Contact Us</u> section for any non-product compliance questions.

Search Parts in this Series

<u>47018</u>Series

Mates With 877030001

Duration at Max. Process Temperature (seconds)

Lead-free Process Capability Reflow Capable (SMT only)

Max. Cycles at Max. Process Temperature 1
Process Temperature max. C 255

Material Info

Reference - Drawing Numbers
Electrical Model Document

Electrical Model Document EE-47018-002
Product Specification PS-67492-001
Sales Drawing SD-47018-001

This document was generated on 10/25/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION