

Unidirectional TVS Diodes

DESCRIPTION

The HSDxx Series is designed for applications transient requiring overvoltage protection capability. They are intended for use in voltage and ESD sensitive equipment such as computers, printers. business machines. communication systems, medical equipment and other applications. These devices are ideal for situations where board space is at a premium.

This series has been specifically designed to protect sensitive components which are connected to power, data and transmission lines from overvoltage caused by ESD(electrostatic discharge), CDE (Cable Discharge Events), and EFT (electrical fast transients).

ORDERING INFORMATION

Device: HSDxxPackage: SOD-323Material: Halogen freePacking: Tape & Reel

♦ Quantity per reel: 3,000pcs

FEATURES

- ♦IEC61000-4-2 (ESD) ±30kV (air), ±30kV (contact) ♦IEC61000-4-4 (EFT) 40A (5/50ηs)
- ♦350 Watts Peak Pulse Power per (tp=8/20µs)
- ♦Protects one I/O line (unidirectional)
- ♦Low clamping voltage
- ♦Working voltages : 3.3V to 36V
- ♦Low leakage current

MACHANICAL DATA

- ♦SOD-323 package
- ♦Flammability Rating: UL 94V-0
- ♦Packaging: Tape and Reel
- ♦ High temperature soldering guaranted: 260°C/10s
- ♦Reel size: 7 inch
- ♦MSL 1
- ♦ Weight: 4.6 mg

APPLICATIONS

- ♦ Cell Phone Handsets and Accessories
- ♦ Microprocessor based equipment
- ♦ Personal Digital Assistants (PDA's)
- ♦ Notebooks, Desktops, and Servers
- ♦ Portable Instrumentation
- ♦ Networking and Telecom
- ♦ Serial and Parallel Ports
- ♦ Peripherals

PIN CONFIGURATION



PACKAGE OUTLINE






Unidirectional TVS Diodes

ABSOLUTE MAXIMUM RATING (Tamb=25°C)							
Symbol	Parameter	Value	Units				
V _{ESD}	ESD per IEC 61000-4-2 (Air) ESD per IEC 61000-4-2 (Contact)	±30 ±30	kV				
P_PP	Peak Pulse Power (8/20µs)	350	W				
T _{OPT}	Operating Temperature	-55/+150	°C				
T _{STG}	Storage Temperature	-55/+150	°C				
TL	Lead Soldering Temperature	260 (10 sec.)	°C				

ELECTRICAL CHARACTERISTICS (Tamb=25°C)									
PART NUMBER	DEVICE MARKING	V _{RWM} (V) (max.)	V _B (V) (min.)	I _T (mA)	V _C @1A (V) (max.)	V _C ((V (max.)	② I _{PP} ') (A)	l _R (μA) (max.)	C _J (pF) (max.)
HSD03	03W	3.3	4	1	6.5	14	20	40	450
HSD05	05W	5	6	1	9.8	18	17	10	300
HSD12	12W	12	13.3	1	19	32	11	1	130
HSD15	15W	15	16.7	1	24	38	10	1	120
HSD18	18W	18	20.0	1	29	45	9	1	100
HSD20	20W	20	22.3	1	35	50	8	1	90
HSD24	24W	24	26.7	1	43	52	7	1	80
HSD36	36W	36	40	1	60	75	5	1	60




Unidirectional TVS Diodes







Unidirectional TVS Diodes


SOD-323 PACKAGE OUTLINE DIMENSIONS







Symbol	Dimensions In Millimeters				
Symbol	Min	Max			
Α		1.00			
A1	0.000	0.100			
A2	0.800	0.900			
b	0.250	0.350			
С	0.080	0.150			
D	1.200	1.400			
Е	1.600	1.800			
E1	2.500	2.700			
е	1.800	2.040			
L	0.475 REF				
L1	0.250	0.400			
θ	0°	8°			



Recommended Pad outline