





MBR2040CT thru MBR20200CT 20.0Amp Schottky Barrier Rectifiers

Features

- Construction utilizes void-free molded plastic technique
- Low reverse leakage
- High forward surge current capability
- High temperature soldering guaranteed
250 °C/10 seconds at terminals
- Component in accordance to
RoHS 2011/65/EU



- 1-Cathode 1
- 2-Anode
- 3-Cathode 2
- 4-Tab Anode



RoHS
COMPLIANT

Mechanical Date

- **Case:**TO-220AB
Molding compound meets
UL 94 V-0 flammability rating
- **Terminals:** Solder plated, solderable per
MIL-STD-750, Method 2026
- **Polarity :** Polarity symbol marking on body
- **Mounting Position:** Any

Maximum Ratings & Thermal Characteristics (T_A = 25 °C unless otherwise specified)

Parameter	Symbol	MBR 2040CT	MBR 2045CT	MBR 2060CT	MBR 20100CT	MBR 20150CT	MBR 20200CT	Unit
Maximum repetitive peak reverse voltage	V _{RRM}	40	45	60	100	150	200	V
Maximum RMS voltage	V _{RMS}	28	31.5	42	70	105	140	V
Maximum DC blocking voltage	V _{DC}	40	45	60	100	150	200	V
Maximum average forward rectified current at T _C =125°C	I _{F(AV)}	20						A
Peak forward surge current, 8.3ms single half sine-wave superimposed on rated load	I _{FSM}	150						A
Thermal resistance from junction to case	R _{θJC}	1.3						°C/W
Junction temperature	T _J	-55 to +150						°C
Storage temperature range	T _{STG}	-55 to +150						°C

Electrical Characteristics (T_A = 25 °C unless otherwise noted)

Parameter	Symbol	MBR 2040CT	MBR 2045CT	MBR 2060CT	MBR 20100CT	MBR 20150CT	MBR 20200CT	Unit
Maximum instantaneous forward voltage per diode at 10.0A	V _F	0.55		0.70	0.85	0.95		V
Maximum DC reverse current at rated DC blocking voltage	T _A =25°C	0.5			0.05			mA
	T _A =125°C	50			10			



Characteristic Curves (T_A=25 °C unless otherwise noted)

FIG. 1- DERATING CURVE OUTPUT RECTIFIED CURRENT




FIG. 2-MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT PERLEG




FIG. 3-TYPICAL FORWARD VOLTAGE CHARACTERISTICS






FIG. 4-TYPICAL REVERSE LEAKAGE CHARACTERISTICS





Package Outline

TO-220AB



Dimensions in inches and (millimeters)

- TRR is registered trademark of Zhejiang TRR Microelectronics Inc. Zhejiang TRR Microelectronics Inc reserves the right to make changes to any product in this specification without notice.
- Zhejiang TRR Microelectronics Inc does not assure any liability arising out of the applications or use of any product described in this specification.
- Zhejiang TRR Microelectronics Inc advises customers to obtain the latest version of the device information before placing orders to verify that the required information is current.