




Typical Applications

The HMC1106 is ideal for:

- Microwave Point-to-Point Radios
- VSAT & SATCOM
- Test Equipment & Sensors
- Military End-Use
- Automotive Radar

Functional Diagram



Features

Passive: No DC Bias Required Low LO Power: +15 dBm LO/RF Isolation: 38 dB LO/IF Isolation: 32 dB RF/IF Isolation: 25 dB Wide IF Bandwidth: DC to 24 GHz Die Size: 1.79 x 1.46 x 0.1 mm

General Description

The HMC1106 is a double-balanced mixer which can be used as a downconverter with DC to 24 GHz at the IF port, 20 to 50 GHz at the LO port, and 15 to 36 GHz at the RF port. This passive MMIC mixer is fabricated with GaAs Shottky diode technology. All bond pads and the die backside are Ti/Au metallized and the Shottky devices are fully passivated for reliable operation. All data shown herein is measured with the chip in a 50 Ohm environment and contacted with RF probes.

HMC1106

15 - 36 GHz

GaAs MMIC MIXER

Electrical Specifications, $T_A = +25^{\circ}$ C, LO = 36.1 GHz, LO = +15 dBm, LSB^[1]

Parameter	Min.	Тур.	Max.	Min.	Тур.	Max	Min.	Тур.	Max	Units
RF Frequency Range		15 -24			24 - 27			27 - 36		GHz
LO Frequency Range	20 - 50				GHz					
IF Frequency Range					DC - 24					GHz
Conversion Loss		9	12		11	14		10	14	dB
LO to RF Isolation		38			38			38		dB
LO to IF Isolation ^[2]	25	32		25	32		25	32		dB
RF to IF Isolation ^[3]	15	22		15	18		15	25		dB
IP3 (Input)		16			16			22		dBm

[1] Unless otherwise noted , all measurements performed as downconverter with LO Frequency = 36.1 GHz and LO Power = +15 dBm [2] Typical value = 22 dB at LO = 20 GHz

[3] Data taken with LO = 30 GHz

Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective owners.




GaAs MMIC MIXER


32 34 36

17 dBm


v01.0314








Conversion Loss vs. Temperature IF = 12.1 GHz [2]




Conversion Loss vs. Temperature IF = 16.1 GHz [2]



[1] Measurement taken at fixed LO frequency, LSB [2] Measurement taken at fixed IF frequency, LSB

Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective owners.



28 30

15 dBm

RF FREQUENCY (GHz)

-2

-6

-8

-10

-12

-16

-18

14

18

20


13 dBm


16

22 24 26

(qB) -4

CONVERSION LOSS (








15 - 36 GHz

GaAs MMIC MIXER




Conversion Loss vs. IF [1]




v01.0314












Measurement taken at fixed IF frequency, LSB
Measurement taken at fixed LO frequency, LSB

Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective owners.












v01.0314








RF Return Loss vs. Temperature LO = 30GHz




LO Return Loss vs. Temperature [2]




[1] Measurement taken at fixed IF frequency, LSB [2] Measurement taken at LO power = +14 dBm


Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective owners.








LO Return Loss vs. LO Power







15 - 36 GHz


17 dBm

GaAs MMIC MIXER





LO/RF Isolation vs. Temperature


v01.0314




LO/IF Isolation vs. Temperature












15 dBm



13 dBm





(qB)

Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective owners.




15 - 36 GHz

17 dBm

GaAs MMIC MIXER

v01.0314

RoHS√



MxN Spurious Outputs, RF = 20GHz

	nLO					
mRF	0	1	2	3	4	
0	xx	1	0	0	0	
1	9.8	0	0	0	0	
2	58.5	30.3	41.7	0	0	
3	0	35	46.6	56	0	
4	0 78.5		62.6	57.4	0	
RF = 20 GHz @ -4 dBm						
LO = 35 GHz @ +13 dBm						
Data taken without IF hybrid						
All values in dBc below IF power level						

RF/IF Isolation vs. LO Power 0

LO = 30 GHz-10 (dB) -20 ISOLATION -30 -40 -50 10 15 25 35 40 20 30 RF FREQUENCY (GHz)

13 dBm

MIXERS - CHIP

MxN Spurious Outputs, RF = 25 GHz

15 dBm

	nLO					
mRF	0 1		2	3	4	
0	xx	0	0	0	0	
1	12.5	0	22.5	0	0	
2	56.5	25	33.3	0	0	
3	0	53.7	55.8	57	0	
4	0 0 73.6 64.4 68.8					
RF = 25 GHz @ -4 dBm LO = 35 GHz @ +13 dBm Data taken without IF hybrid All values in dBc below IF power level						

• • • • •						
	nLO					
mRF	0	1	2	3	4	
0	хх	5	0	0	0	
1	16.5	0.2	22.7	0	0	
2	0 42.6 57.3 45.5 0				0	
3	0	0	50.5	60.1	0	
4	0 0 63.2 68.5 67.3					
RF = 30 GHz @ -4 dBm						
LO = 35 GHz @ +13 dBm						
Data taken without IF hybrid						
All values in dBc below IF power level						

MxN Spurious Outputs, RF = 30 GHz

Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective owners.





GaAs MMIC MIXER

15 - 36 GHz


HMC1106

Absolute Maximum Ratings

LO Input Power	+17 dBm
Maximum Junction Temperature	175 °C
Continuous Pdiss (T= 85 °C) (derate 1.75 mW/°C above 85°C)	157 mW
Thermal Resistance (R _{TH}) (junction to die bottom)	570 °C/W
Operating Temperature	-55 to +85 °C
Storage Temperature	-65 to 150 °C
ESD Sensitivity (HBM)	Class1A, passed 250V



Outline Drawing



Die Packaging Information^[1]

Standard	Alternate
GP-2 (Gel Pack)	[2]

[1] For more information refer to the "Packaging information" Document in the Product Support Section of our website.

[2] For alternate packaging information contact Hittite Microwave Corporation.

NOTES:

1. ALL DIMENSIONS ARE IN INCHES [MM].

2. DIE THICKNESS IS 0.004"

- 3. BOND PADS 1, 2 & 3 are 0.0059" [0.150] X 0.0039" [0.099].
- 4. BACKSIDE METALLIZATION: GOLD.

5. BOND PAD METALLIZATION: GOLD.

BACKSIDE METAL IS GROUND.
CONNECTION NOT REQUIRED FOR UNLABELED BOND PADS.

8. OVERALL DIE SIZE ± 0.002

Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective owners.






GaAs MMIC MIXER 15 - 36 GHz

Pad Descriptions

Pad Number	Function	Description	Pad Schematic
1	LO	This pad is AC coupled and Matched to 50 Ohms.	L0 0
2	RF	This pad is AC coupled and Matched to 50 Ohms.	RF ○
3	IF	This pad is DC coupled and Matched to 50 Ohms.	IF O
Die Bottom	GND	Die bottom must be connected to RF/DC ground	

v01.0314

Assembly Diagram



Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective owners.



HMC1106

ROHS

GaAs MMIC MIXER 15 - 36 GHz

Mounting & Bonding Techniques for Millimeterwave GaAs MMICs

The die should be attached directly to the ground plane eutectically or with conductive epoxy (see HMC general Handling, Mounting, Bonding Note).

50 Ohm Microstrip transmission lines on 0.127mm (5 mil) thick alumina thin film substrates are recommended for bringing RF to and from the chip (Figure 1). One way to accomplish this is to attach the 0.102mm (4 mil) thick die to a 0.150mm (6 mil) thick molybdenum heat spreader (molytab) which is then attached to the ground plane (Figure 2). Microstrip substrates should be located as close to the die as possible in order to minimize bond wire length. Typical die-to-substrate spacing is 0.076mm to 0.152 mm (3 to 6 mils).



Follow these precautions to avoid permanent damage.

Storage: All bare die are placed in either Waffle or Gel based ESD protective containers, and then sealed in an ESD protective bag for shipment. Once the sealed ESD protective bag has been opened, all die should be stored in a dry nitrogen environment.

Cleanliness: Handle the chips in a clean environment. DO NOT attempt to clean the chip using liquid cleaning systems.

Static Sensitivity: Follow ESD precautions to protect against > \pm 250V ESD strikes.

Transients: Suppress instrument and bias supply transients while bias is applied. Use shielded signal and bias cables to minimize inductive pick-up.

General Handling: Handle the chip along the edges with a vacuum collet or with a sharp pair of bent tweezers. The surface of the chip may have fragile air bridges and should not be touched with vacuum collet, tweezers, or fingers.

Mounting


The chip is back-metallized and can be die mounted with AuSn eutectic preforms or with electrically conductive epoxy. The mounting surface should be clean and flat.


Eutectic Die Attach: A 80/20 gold tin preform is recommended with a work surface temperature of 255 °C and a tool temperature of 265 °C. When hot 90/10 nitrogen/hydrogen gas is applied, tool tip temperature should be 290 °C. DO NOT expose the chip to a temperature greater than 320 °C for more than 20 seconds. No more than 3 seconds of scrubbing should be required for attachment.

Epoxy Die Attach: Apply a minimum amount of epoxy to the mounting surface so that a thin epoxy fillet is observed around the perimeter of the chip once it is placed into position. Cure epoxy per the manufacturer's schedule.

Wire Bonding

Ball or wedge bond with 0.025mm (1 mil) diameter pure gold wire. Thermosonic wirebonding with a nominal stage temperature of 150 °C and a ball bonding force of 40 to 50 grams or wedge bonding force of 18 to 22 grams is recommended. Use the minimum level of ultrasonic energy to achieve reliable wirebonds. Wirebonds should be started on the chip and terminated on the package or substrate. All bonds should be as short as possible <0.31mm (12 mils).







HMC1106



Notes:

GaAs MMIC MIXER 15 - 36 GHz

Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective owners.