

40V N+P-Channel Enhancement Mode MOSFET

Description

The AP25G04GD uses advanced trench technology to provide excellent $R_{DS(ON)}$, low gate charge and operation with gate voltages as low as 4.5V. This device is suitable for use as a Battery protection or in other Switching application.

General Features

V_{DS} = 40V I_D = 28 A

 $R_{DS(ON)} < 24m\Omega @ V_{GS}=10V$ (Type: $18m\Omega$)


V_{DS} = -40V I_D =25A


 $R_{DS(ON)} < 40m\Omega @ V_{GS}=10V (Type: 32m\Omega)$

Application

Boost driver

Brushless motor





Package Marking and Ordering Information

Product ID	Pack	Marking	Qty(PCS)
AP25G04GD	TO-252-4L	AP25G04GD XXX YYYY	2500

Absolute Maximum Ratings (Tc=25°C unless otherwise noted)

Cumhal	Deservedes	Ra	Unite	
Symbol	Parameter	N-Ch	P-Ch	Units
Vds	Drain-Source Voltage	40	-40	V
Vgs	Gate-Source Voltage ±20 ±20		V	
I₀@Tc=25°C	Continuous Drain Current, V _{GS} @ 10V ¹	28	-25	А
ID@Tc=100°C	Continuous Drain Current, V _{GS} @ 10V ¹	18	-16	А
Ідм	Pulsed Drain Current ²	46	-40	А
EAS	Single Pulse Avalanche Energy ³	28	66	mJ
las	Avalanche Current	17.8	-27.2	А
P _D @T _C =25°C	Total Power Dissipation ⁴	25	31.3	W
Tstg	Storage Temperature Range	-55 to 150	-55 to 150	°C
TJ	Operating Junction Temperature Range	e -55 to 150 -55 to 150		°C
R _θ JA	Thermal Resistance Junction-Ambient ¹	62		°C/W
Rejc	Thermal Resistance Junction-Case ¹	5		°C/W



40V N+P-Channel Enhancement Mode MOSFET

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit
BVDSS	Drain-Source Breakdown Voltage	V _{GS} =0V , I _D =250uA	40	44		V
$\triangle BVDSS / \triangle TJ$	BVDSS Temperature Coefficient	Reference to 25° C , I _D =1mA		0.034		V/℃
RDS(ON)	Static Drain-Source On-Resistance ²	V _{GS} =10V , I _D =5A	18 26		26	mΩ
NDS(ON)		V _{GS} =4.5V , I _D =4A		25.0	35	11152
VGS(th)	Gate Threshold Voltage	V _{GS} =V _{DS} , I _D =250uA	1.2	1.6	2.5	V
$ riangle V_{GS(th)}$	V _{GS(th)} Temperature Coefficient	VGS-VDS, ID -2300A		-4.56		mV/℃
IDSS	Drain-Source Leakage Current	$V_{\text{DS}}\text{=}32V$, $V_{\text{GS}}\text{=}0V$, $T_{\text{J}}\text{=}25^\circ\!\mathrm{C}$			1	1 5 uA
1033	Drain-Source Leakage Current	$V_{\text{DS}}\text{=}32V$, $V_{\text{GS}}\text{=}0V$, $T_{\text{J}}\text{=}55^\circ\!\mathrm{C}$			5	
IGSS	Gate-Source Leakage Current	V _{GS} =±20V , V _{DS} =0V			±100	nA
gfs	Forward Transconductance	V _{DS} =5V , I _D =5A		14		S
Rg	Gate Resistance	V _{DS} =0V , V _{GS} =0V , f=1MHz		2.6		Ω
Qg	Total Gate Charge (4.5V)			5.5		
Qgs	Gate-Source Charge	V _{DS} =20V , V _{GS} =4.5V , I _D =5A		1.25		nC
Q_{gd}	Gate-Drain Charge			2.5		
Td(on)	Turn-On Delay Time			8.9		
Tr	Rise Time	V_{DD} =20V , V_{GS} =10V , R_{G} =3.3 Ω		2.2		
Td(off)	Turn-Off Delay Time	I _D =1A		41		ns
T _f	Fall Time			2.7		
Ciss	Input Capacitance			593		
Coss	Output Capacitance	V _{DS} =15V , V _{GS} =0V , f=1MHz		76		pF
Crss	Reverse Transfer Capacitance			56		
ls	Continuous Source Current ^{1,5}				6.1	Α
ISM	Pulsed Source Current ^{2,5}	$V_G=V_D=0V$, Force Current			23	Α
VSD	Diode Forward Voltage ²	V _{GS} =0V , I _S =1A , T _J =25℃			1.2	V

Electrical Characteristics (Tc=25°Cunless otherwise noted)

Note :

1. The data tested by surface mounted on a 1 inch² FR-4 board with 2OZ copper.

2、The data tested by pulsed , pulse width $\,\leq\,$ 300us , duty cycle $\,\leq\,$ 2%

3. The EAS data shows Max. rating . The test condition is V_DD=25V,V_GS=10V,L=0.1mH,I_{AS}=20A

 4_{\circ} The power dissipation is limited by 150° C junction temperature

5 \sim The data is theoretically the same as I_D and I_{DM}, in real applications, should be limited by total power dissipation.



40V N+P-Channel Enhancement Mode MOSFET

Electrical Characteristics (Tc=25°C unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit
BVDSS	Drain-Source Breakdown Voltage	V _{GS} =0V , I _D =-250uA	-40	-44		V
∆BVDSS/∆TJ	BV _{DSS} Temperature Coefficient	Reference to 25° C , I _D =-1mA		-0.02		V/℃
		V _{GS} =-10V , I _D =-6A		32	42	mΩ
RDS(ON)	Static Drain-Source On-Resistance ²	V _{GS} =-4.5V , I _D =-3A		48	60	11122
VGS(th)	Gate Threshold Voltage	V _{GS} =V _{DS} , I _D =-250uA	-1.2	-1.7	-2.5	V
$ riangle V_{GS(th)}$	V _{GS(th)} Temperature Coefficient	VGS-VDS, 102300A		3.72		mV/℃
IDSS	Drain Source Lookage Current	$V_{\text{DS}}\text{=-}32V$, $V_{\text{GS}}\text{=}0V$, $T_{\text{J}}\text{=}25^\circ\!\!\mathbb{C}$			1	uA
1033	Drain-Source Leakage Current	$V_{\text{DS}}\text{=-}32V$, $V_{\text{GS}}\text{=}0V$, $T_{\text{J}}\text{=}55^\circ\!\!\mathbb{C}$			5	
IGSS	Gate-Source Leakage Current	V _{GS} =±20V , V _{DS} =0V			±100	nA
gfs	Forward Transconductance	V _{DS} =-5V , I _D =-6A		13		S
Qg	Total Gate Charge (-4.5V)			11.5		
Qgs	Gate-Source Charge	V _{DS} =-20V , V _{GS} =-4.5V , I _D =-6A		3.5		nC
Q_gd	Gate-Drain Charge			3.3		
Td(on)	Turn-On Delay Time			22		
Tr	Rise Time	V_{DD} =-15V , V_{GS} =-10V , R_G =3.3 Ω ,		15.7		
Td(off)	Turn-Off Delay Time	I _D =-1A		59		ns
T _f	Fall Time			5.5		
Ciss	Input Capacitance			1415		
Coss Output Capacitance		V _{DS} =-15V , V _{GS} =0V , f=1MHz		134		pF
Crss	Reverse Transfer Capacitance			102		
ls	Continuous Source Current ^{1,5}	$V_G=V_D=0V$, Force Current			-6	А
ISM	Pulsed Source Current ^{2,5}				-22	А
VSD	Diode Forward Voltage ²	V _{GS} =0V , I _S =-1A , TJ=25℃			-1.2	V

Note :

 $1_{\mbox{\tiny V}}$ The data tested by surface mounted on a 1 inch2 FR-4 board with 2OZ copper.

 $2\,{\scriptstyle\smallsetminus}\,$ The data tested by pulsed , pulse width $\leq 300 us$, duty cycle $\leq 2\%$

3、The EAS data shows Max. rating . The test condition is VDD=-25V,VGS=-10V,L=0.1mH,IAS=-24A


4. The power dissipation is limited by 150°C junction temperature


5 、The data is theoretically the same as ID and IDM, in real applications, should be limited by total power dissipation.



40V N+P-Channel Enhancement Mode MOSFET

N-Channel Typical Characteristics







100

150

50

T_J, Junction Temperature (°C)

0



40V N+P-Channel Enhancement Mode MOSFET




Fig.9 Normalized Maximum Transient Thermal Impedance




Fig.10 Switching Time Waveform





Fig.11 Unclamped Inductive Switching Wave

СЛ



40V N+P-Channel Enhancement Mode MOSFET

P-Channel Typical Characteristics










Fig.3 Forward Characteristics of Reverse





σ



40V N+P-Channel Enhancement Mode MOSFET




Fig.9 Normalized Maximum Transient Thermal Impedance





Fig.10 Switching Time Waveform








40V N+P-Channel Enhancement Mode MOSFET


Package Mechanical Data:TO-252-4L




SYMBOLS	Millimeters				
	MIN	NOM	MAX		
D	6.30	6.55	6.80		
D1	4.80	5.35	5.90		
С	9.30	9.75	10.20		
E	5.30	5.80	6.30		
E3	4.50	5.15	5.80		
L	0.90	1.35	1.80		
Ll	2.00	2.53	3.05		
L2	0.50	0.85	1.20		
b	0.30	0.50	0.70		
bl	0.40	0.60	0.80		
A	2.10	2.30	2.50		
A2	0.40	0.53	0.65		
A1	0.00	0.10	0.20		
e	1.20	1.30	1.40		

1.All Dimensions Are in Millimeters.

2.Dimension Does Not Include Mold Protrusions.



Reel Spectification-TO-252-4



	Dimensions					
Ref.	Millimete		eters		Inches	
	Min.	Тур.	Max.	Min.	Тур.	Max.
W	15.90	16.00	16.10	0.626	0.630	0.634
Е	1.65	1.75	1.85	0.065	0.069	0.073
F	7.40	7.50	7.60	0.291	0.295	0.299
D0	1.40	1.50	1.60	0.055	0.059	0.063
D1	1.40	1.50	1.60	0.055	0.059	0.063
P0	3.90	4.00	4.10	0.154	0.157	0.161
P1	7.90	8.00	8.10	0.311	0.315	0.319
P2	1.90	2.00	2.10	0.075	0.079	0.083
A0	6.85	6.90	7.00	0.270	0.271	0.276
B0	10.45	10.50	10.60	0.411	0.413	0.417
K0	2.68	2.78	2.88	0.105	0.109	0.113
Т	0.24		0.27	0.009		0.011
t1	0.10			0.004		
10P0	39.80	40.00	40.20	1.567	1.575	1.583

00



40V N+P-Channel Enhancement Mode MOSFET

Attention

1,Any and all APM Microelectronics products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your APM Microelectronics representative nearest you before using any APM Microelectronics products described or contained herein in such applications.

2,APM Microelectronics assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all APM Microelectronics products described or contained herein.

3, Specifications of any and all APM Microelectronics products described or contained here instipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.

4, APM Microelectronics Semiconductor CO., LTD. strives to supply high quality high reliabilityproducts. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives that could give rise to smoke or fire, or that could cause damage to other property. Whendesigning equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.

5, In the event that any or all APM Microelectronics products (including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.

6, No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of APM Microelectronics Semiconductor CO., LTD.

7, Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production. APM Microelectronics believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.

8, Any and all information described or contained herein are subject to change without notice due to product/technology improvement,etc. When designing equipment, refer to the "DeliverySpecification" for the APM Microelectronics product that you Intend to use.

永源微電子科技有限公司

ഥ



40V N+P-Channel Enhancement Mode MOSFET

Edition	Date	Change
RVE1.0	2018/1/31	Initial release

Copyright Attribution"APM-Microelectronice"