

## N-Channel MOSFET

#### **Applications:**

- Adaptor
- Charger
- .SMPS

# Lead Free Package and Finish


$V_{DSS}$	R <sub>DS(ON)</sub> (Typ.)	I <sub>D</sub>
650V	0.49Ω	16A

#### Features:

- RoHS Compliant
- Low ON Resistance
- Low Gate Charge
- Peak Current vs Pulse Width Curve
- Inductive Switching Curves

**Ordering Information** 

PART NUMBER	PART NUMBER   PACKAGE	
ITA16N65A	TO-220F	IPS



**Absolute Maximum Ratings**  $T_C=25^{\circ}C$  unless otherwise specified

Symbol	Parameter	ITA16N65A	Units
V <sub>DSS</sub>	Drain-to-Source Voltage	650	V
I <sub>D</sub>	Continuous Drain Current	16	А
	Continuous Drain Current T <sub>C</sub> =100°C	11.5	А
I <sub>DM</sub>	Pulsed Drain Current, V <sub>GS</sub> @10V (NOTE *1)	64	Α
D	Power Dissipation	70	W
$P_D$	Derating Factor above 25℃	0.56	W/℃
V <sub>GS</sub>	Gate-to-Source Voltage	±30	V
E <sub>AS</sub>	Single Pulse Avalanche Energy(NOTE *2)	800	mJ
dv/dt	Peak Diode Recovery dv/dt(NOTE *3)	5	V/ns
TL	Maximum Temperature for Soldering	300	
$T_J$ and $T_{STG}$	Operating Junction and Storage Temperature Range	150,-55 to150	${\mathbb C}$

### **Thermal Resistance**

Symbol	Parameter	Тур.	Units	Test Conditions
R <sub>θJC</sub>	Junction-to-Case	1.79	°CXW	Water cooled heatsink, P <sub>D</sub> adjusted for a peak junction temperature of +150 ℃.
$R_{\theta JA}$	Junction-to-Ambient	100		1 cubic foot chamber, free air.



## **OFF Characteristics** T<sub>C</sub>=25°C unless otherwise specified

Symbol	Parameter	Min.	Тур.	Max.	Units	Test Conditions
BV <sub>DSS</sub>	Drain-to-Source Breakdown Voltage	650			V	V <sub>GS</sub> =0V, I <sub>D</sub> =250μA
	Drain to Source Lagkage Current			10		$V_{DS}$ =650V, $V_{GS}$ =0V $T_{J}$ =25 $^{\circ}$ C
I <sub>DSS</sub>	Drain-to-Source Leakage Current			100	μA	$V_{DS}$ =520V, $V_{GS}$ =0V $T_{J}$ =125 $^{\circ}$ C
1	Gate-to-Source Forward Leakage			+100	n 1	V <sub>GS</sub> =+30V
I <sub>GSS</sub>	Gate-to-Source Reverse Leakage			-100	- nA	V <sub>GS</sub> = -30V

## ON Characteristics T<sub>J</sub>=25 °C unless otherwise specified

Symbol	Parameter	Min.	Тур.	Max.	Units	Test Conditions
R <sub>DS(ON)</sub>	StaticDrain-to-Source On-Resistance		0.49	0.55	Ω	V <sub>GS</sub> =10V, I <sub>D</sub> =8A
$V_{GS(TH)}$	Gate Threshold Voltage	2		4	V	$V_{DS}=V_{GS}$ , $I_{D}=250\mu A$
g <sub>fs</sub>	Forward Transconductance		15		S	V <sub>DS</sub> =15V, I <sub>D</sub> =8A
Pulse width	≲300µs; duty cycle≲ 2%					

### **Dynamic Characteristics** Essentially independent of operating temperature

Symbol	Parameter	Min.	Тур.	Max.	Units	Test Conditions
C <sub>iss</sub>	Input Capacitance		2450			\\ - 0\\\\ - 25\\
C <sub>oss</sub>	Output Capacitance		218		pF	$V_{GS}$ = 0V, $V_{DS}$ = 25V f =1.0MHz
C <sub>rss</sub>	Reverse Transfer Capacitance		18.5			
Q <sub>g</sub>	Total Gate Charge		54			L =46A \/ =22E\/
Q <sub>gs</sub>	Gate-to-Source Charge		10		nC	$I_D = 16A, V_{DD} = 325V$ $V_{GS} = 10V$
$Q_{gd}$	Gate-to-Drain ("Miller") Charge		21			

## 

Symbol	Parameter	Min.	Тур.	Max.	Units	Test Conditions
t <sub>d(ON)</sub>	Turn-on Delay Time		30		-	V <sub>DD</sub> =325V, I <sub>D</sub> =16A,
t <sub>rise</sub>	Rise Time		70			
t <sub>d(OFF)</sub>	Turn-Off Delay Time		145		ns	$V_G$ =10V $R_G$ =25 $\Omega$
t <sub>fall</sub>	Fall Time		74			



## Source-Drain Diode Characteristics Tc=25 ℃ unless otherwise specified

Symbol	Parameter	Min.	Тур.	Max.	Units	Test Conditions
	Continuous Source Current		16	_		
IS	(Body Diode)			10	Α	T -25°
	Maximum Pulsed Current			64	64 A	T <sub>C</sub> =25℃
I <sub>SM</sub>	(Body Diode)					
V <sub>SD</sub>	Diode Forward Voltage			1.5	V	I <sub>SD</sub> =16A, V <sub>GS</sub> =0V
t <sub>rr</sub>	Reverse Recovery Time		410		ns	I <sub>F</sub> = I <sub>S</sub>
Q <sub>rr</sub>	Reverse Recovery Charge		3.5		uC	di/dt=100A/us
Pulse width ≤300µs; duty cycle ≤ 2%						

#### Notes:

<sup>\*1.</sup> Repetitive rating; pulse width limited by maximum junction temperature.

**<sup>\*2</sup>**. L=10mH,  $I_D$ =12.6A, Start  $T_J$ =25°C

<sup>\*3.</sup>  $I_{SD} = 16A$ ,  $di/dt \le 100A/us$ ,  $V_{DD} \le BV_{DS}$ , Start  $T_J = 25$ °C



#### **Characteristics Curve:**




Figure 2. Max. Power Dissipation vs Case Temperature






Figure 3. Max. Drain Current vs Case Temperature



**Figure 4.Typical Output Characteristics** 



**Figure 5. Typical Transfer Characteristics** 






Figure 6. Typical Body Diode Transfer Characteristics




Figure 7. Typical on Resistance VS Drain Current




Figure 8. Capacitance VS Drain-to-Source Voltage




Figure 9. Gate Charge VS Gate-to-Source Voltage






Figure 10. Breakdown Voltage VS Temperature




Figure 11. on-Resistance VS Temperature




Figure 12 The shold Voltage vs Junction Temperature





Figure 13. Safe Operating Area





### **Test Circuits and Waveforms**

Figure 14. Gate Charge Test Circuit




Figure 15. Gate Charge Waveforms  $\mathsf{V}_{\mathsf{DS}}$ 





Figure 16. Resistive Switching Test Circuit

Figure 17. Resistive Switching Waveforms








Figure 18. Diode Reverse Recovery Test Circuit




Figure 19. Diode Reverse Recovery Waveform






Figure 20. Unclamped Inductive Switching Test Circuit

Figure 21. Unclamped Inductive Switching Waveform







#### **Disclaimers:**

InPower Semiconductor Co., Ltd (IPS) reserves the right to make changes without notice in order to improve reliability, function or design and to discontinue any product or service without notice. Customers should obtain the latest relevant information before orders and should verify that such information is current and complete. All products are sold subject to IPS's terms and conditions supplied at the time of order acknowledgement.

InPower Semiconductor Co., Ltd warrants performance of its hardware products to the specifications at the time of sale, Testing reliability and quality control are used to the extent IPS deems necessary to support this warrantee. Except where agreed upon by contractual agreement, testing of all parameters of each product is not necessarily performed.

InPower Semiconductor Co., Ltd does not assume any liability arising from the use of any product or circuit designs described herein. Customers are responsible for their products and applications using IPS's components. To minimize risk, customers must provide adequate design and operating safeguards.

InPower Semiconductor Co., Ltd does not warrant or convey any license either expressed or implied under its patent rights, nor the rights of others. Reproduction of information in IPS's data sheets or data books is permissible only if reproduction is without modification or alteration. Reproduction of this information with any alteration is an unfair and deceptive business practice. InPower Semiconductor Co., Ltd is not responsible or liable for such altered documentation.

Resale of IPS's products with statements different from or beyond the parameters stated by InPower Semiconductor Co., Ltd for that product or service voids all express or implied warrantees for the associated IPS's product or service and is unfair and deceptive business practice. InPower Semiconductor Co., Ltd is not responsible or liable for any such statements.

#### **Life Support Policy:**

InPower Semiconductor Co., Ltd's products are not authorized for use as critical components in life support devices or systems without the expressed written approval of InPower Semiconductor Co., Ltd.

#### As used herein:

- 1. Life support devices or systems are devices or systems which:
  - a. are intended for surgical implant into the human body,
  - b. support or sustain life,
  - c. whose failure to perform when properly used in accordance with instructions for used provided in the labeling, can be reasonably expected to result in significant injury to the user.
- 2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.