ISO9001: 2015 ISO14001: 2015

APPROVAL SPECIFICATIONS

Title. TACT SWITCH

Product Model. KAN1211-0431C

Customer's Part NO.

Customer's Model:

Customer's Approval Requested.

Please return this copy as a certification of your approval.

Checked by: Date:

Approved by: Date:

温州港源电子有限公司

Wenzhou Gangyuan Electronics Co.,Ltd Address:No.2 Yonghe Yi Road,Chengdong Street,Yueqing City,Zhejiang Province,China. Tel:0577-06571538 Fax:0577-62573066 Website:http://www.gangyuan.com





Product name	P/N	Version	Document No.	Page
Tact switch	KAN1211-0431C	A/01		2/11

变更履历表:

版本	变更记录	变更人	变更日期
A/01	变更存储方法	林云龙	2018.11.03



Product name	P/N	Version	Document No.	Page
Tact switch	KAN1211-0431C	A/01		3/11

1、 概述

GENERAL

1.1 适用范围

APPLICATION

此规格书适用于机械式轻触开关的相关要求

This specification is applied to the requirements for tactile switch (mechanical contact)

1.2 工作温度范围

Operating Temperature Range

- -30℃~80℃(在标准大气压、标准湿度条件下)
- -30°C~80°C(Normal humidity, normal air pressure)
- 1.3 贮藏温度范围

Storage Temperature Range

- -40℃~90℃(在标准大气压、标准湿度条件下)
- -40°C~90°C(Normal humidity, normal air pressure)
- 1.4 测试条件

Test Conditions

在没有其它特定的条件下,应该在以下的条件下进行测试和测量:

Unless otherwise specified, tests and measurement shall be made in the following standard conditions:

常温......5℃~35℃

Normal temperature......5°C~35°C

标准湿度......相对湿度 25%~85%

Normal humidity.....relative humidity 25%~85%

标准大气压......86Kpa~106Kpa

Normal air pressure......86Kpa~106Kpa

在制造过程中,测试和测量应该在以下的条件下进行:

If any doubt arise from the judgment, tests shall be conducted at the following conditions:

温度......20°C±2°C

Temperature...... $20^{\circ}\text{C}\pm2^{\circ}\text{C}$

相对湿度......65%±5%

Relative humidity......65% \pm 5%

环境气压......86Kpa~106Kpa

Air pressure......86Kpa~106Kpa

1.5 存储方法

Storage method

1. 使用前确保包装完整无破损, 无浸湿.

Ensure that the product without package breaking or wetting before use.

2. 存储条件 Storage conditions:

储存温度 Storage temperature: -5~35 C;

储存湿度 Storage humidity: 25%~80%;

未开封状态: 6个月内使用完毕(从发货日开始计算); 超过6个月后再使用的,使用前请先验证:端脚无氧化、无发黑、塑料件无吸湿起泡,确保焊接的适宜性;

Unopened status: Use up the product as soon as possible before 6 months. (calculated from shipment date). Over 6 months, please make sure below before use it: terminal without oxidation or blackening, plastic parts without moisture absorption or bubble, ensure solderability.

己开封状态: 1个月内使用完毕;

Opened status: use up within 1 month;

储存注意事项: 避开高湿高温和有腐蚀性气体的环境及阳光直射;

Storage precautions: Please avoid the following environment: with high humidity, high temperature, corrosive gases and direct sunlight.

3. 请勿超重叠放.

Do not stack too many switches.



Product name	P/N	Version	Document No.	Page
Tact switch	KAN1211-0431C	A/01		4/11

2、 详细说明

Detailed specification

2.1 外观:应无影响、降低产品性能的缺陷;

Appearance: There should be no defects that affect the serviceability of product.

2.2 结构尺寸和安装尺寸:应符合装配图要求;

Style and dimension: shall conform to the assemble drawings.

2.3 操作形式: 有触觉反应的操作

Type of actuating: Tactile feedback.

2.4 开关结构: 单回路单输出(具体的触点结构在装配图中已绘出);

Contact arrangement: 1 pole, 1 throw

(Details of contact arrangement are given in the assembly drawings.)

2.5 开关工作额定值: DC 12V 50mA (最大值) DC 1V 10μA (最小值)

Ratings: DC 12V 50mA (Max) DC 1V 10µA (Min)

3. 电气性能:

ELECTRICAL SPECIFICATION

75 D					
项	目	试 验 条 件	要求		
IT	EM	TEST CONDITIONS	REQUIREMENTS		
3.1	接触电阻 Contact Resistance	在以 5V 10mA的直流电源或不低于1KHz的交流电源的电路中,以一个等于 2 倍按力的静负荷施加于手柄中心 Applying a static load of 2 times operating force to the center of the stem, measurements shall be made by 5V DC 10mA or more than 1KHz AC small-current contact resistance meter.	≤100mΩ		
3.2	绝缘电阻 Insulation Resistance	在端子之间施加 DC 100V /min 的条件下,测量端子之间底座、盖板的电阻值 Measurement shall be made following application of 100V DC potential, across terminals, and across terminals and cover, for one minute.	≥100MΩ		
3.3	介质耐压 Dielectric voltage proof	在端子之间施加 250V AC(50Hz 或 60Hz)/min 250V AC (50Hz or 60Hz) shall be applied across terminals, for one minute.	无击穿、无飞弧 There should be no breakdown and flashover		



最大行程

Full Travel

shall be measured.

4.2

	GAN	SPECIFICA	TIONS		
Product name Tact switch		P/N	Version	Document No.	Page
		KAN1211-0431C	KAN1211-0431C A/01		5/11
	项目 ITEM		验条件 CONDITIONS		要求 REQUIREMENTS
3.4	触点抖动 Bounce	按照正常使用时的力度轻按是在导通和断开过程中测试开关。Lightly striking the center of the use (3 to 4 times per second), "OFF" Switch DC3-5V t 为触点	关抖动 he stem at a rate end	countered in normal	ON-10ms max OFF-10ms max
. 机械(IECHA	性能: MICAL SPEC	CIFICATION			
4.1	按力 Operating Force	开关垂直于操作方向放置,是一种大导通所需的最大力度。Placing the switch such that vertical and then gradually inc the stem, the maximum load reshall be measured.	the direction of s	witch operation is lied to the center of	260±50 gf
	最大行程	开关垂直于操作方向放置, 开关驱动件顶端中心,测量J	页端移动的距离。		

Placing the switch such that the direction of switch operation is

vertical and then applying static load of 2times operating force to the center of the stem; the travel distance for the switch to come to a stop $0.35 \pm 0.1 mm$



Pr	oduct name	P/N	Version	Document No.	Page
7	Tact switch	KAN1211-0431C	A/01		6/11
	项目		L 验条件		要求
	ITEM	TEST C	ONDITIONS		REQUIREMENTS
4.3	回弹力 Return Force	开关垂直于操作方向放置,在后,测量顶端向自由位置转换 The sample switch is installed operation is vertical and upon d whole travel distance, the force of shall be measured.	lirection of switch in its center to the	20gf Min	
4.4	停止强度 Stop Strength	开关垂直于操作方向放置,从 荷持续 1min。 Placing the switch such that vertical, and then a static load o of stem operation for a period of	无机械和电气损坏 There shall be no sign of damage mechanically and electrically.		
4.5	手柄拔出 强度 Stem Strength	开关垂直于操作方向放置,反的行程范围。 Placing the switch such that vertical, and then the maximus opposite to the direction of stem	witch operation is	20N min.	
4.6	振动 Vibration	根据以下给定条件进行测试: Measurement shall be made following the test set forth below: (1) 振动频率范围: 10~55~10Hz Vibration frequency range: 10 to 55 to 10Hz (2) 振幅(峰一峰): 1.5mm Amplitude: 1.5mm (3) 振动方向: 包括手柄行程方向在内的三个相互垂直的方向Direction of vibration:Three mutually perpendicular direction including the direction of stem travel (4) 测试时间: 每次 2 小时 Duration: Each 2 hours.			Item 3 Item4.1 Item4.2 Item4.3
4.7	冲击 Shock	根据下列条件进行冲击试验 Test by following conditions (1)安装方法: 正常安装 (1)installation method: normal (2)加速度: 784m/s² (2)Acceleration: 784m/s² (3)作用时间: 11ms (3)Acting time: 11ms (4)测试方向: 6个方向 冲击次数: 每个方向 3 次, 共计 18 次 (4)Test direction: 6 directions Times: 3 times/direction, total 18 times			Item3 Item4.1 Item4.2 Item4.3



Product name	P/N	Version	Document No.	Page
Tact switch	KAN1211-0431C	A/01		7/11

5、环境耐久性:

ETAAT	RONMENTAL SPE	试验条件	要求
	项目		
5.1	低温测试 Resistance to low temperature	TEST CONDITIONS 样品应按照以下实验条件进行测试,实验后样品应放在常温及标准湿度的环境中 1 小时后做性能测试: Following the test set forth below the sample shall be left in normal temperature and humidity conditions for 1 h before measurements are made: (1) 温度: -40±2°C Temperature: -40±2°C (2) 时间: 96h Time: 96h	REQUIREMENTS Item3 Item4.1 Item4.2 Item4.3
5.2	高温测试 Heat resistance	样品应按照以下实验条件进行测试,实验后样品应放在常温及标准湿度的环境中 1 小时后做性能测试: Following the test set forth below the sample shall be left in normal temperature and humidity conditions for 1 h before measurements are made: (1) 温度: 90±2°C temperature:90±2°C (2) 时间: 96h time: 96h	Item3 Item4.1 Item4.2 Item4.3
5.3	温度周期性测试 Change of temperature	根据下面的测试要求进行 5 次循环的温度周期性测试, 实验后 样品应放在常温及标准湿度的环境中 1 小时后做性能测试。测试期间样品应保持干燥. After 5 cycles of following conditions, the sample shall be allowed to stand under normal temperature and humidity conditions for 1 h. and measurements shall be made. During the test water drops shall be removed. A: +90±2°C B: -40±2°C C: 2小时 D: 1小时 E: 2小时 F: 1小时	Item3 Item4.1 Item4.2 Item4.3
5.4	湿温测试 Moisture resistance	样品应按照以下实验条件进行测试,实验后样品应放在常温及标准湿度的环境中 1 小时后做性能测试: Following the test set forth below the sample shall be left in normal temperature and humidity conditions for 1 h before measurements are made: (1) 温度: 60±2°C temperature: 60±2°C (2) 相对湿度: 90%~95% relative humidity:90% to 95% (3) 时间: 96h time: 96h	接触电阻: ≤200mΩ Contact resistance≤200mΩ 绝缘电阻: ≥10MΩ Insulation Resistance≥10MΩ Item3.3 Item3.4 Item4.1 Item4.2 Item4.3



	Product name P/N Versian Decument N				
Pr	roduct name	P/N	Version	Document No.	Page
7	Tact switch	KAN1211-0431C	A/01		8/11
	项目	试	验条件		要求
	ITEM	TEST C	CONDITIONS		REQUIREMENTS
5.5	硫化试验 Sulfuration resistance	样品应按照以下实验条件进行测试,实验后样品应放在常温及标准湿度的环境中 1 小时后做性能测试: Following the test set forth below the sample shall be left in normal temperature and humidity conditions for 1 h before measurements are made: (1) H2S 气体浓度: 3ppm±1ppm H2S gas concentration: 3ppm±1ppm (2) 时间: 72h Time: 72h (3) 温度: 40±2℃(90~95%RH) temperature: 40±2℃(90~95%RH)			接触电阻: ≤200mΩ Contact resistance≤200mΩ Item3.3 Item3.4 Item4.1 Item4.2 Item4.3
5.6	盐雾试验 Salt Mist	在以下设定条件下进行测量: The switch shall be checked after following test: (1) 温度: 35°C±2°C temperature: 35°C±2°C (2) 盐溶液浓度: 5±1% (质量百分比) salt solution: 5±1%(solids by mass) (3) 时间: 48±1h Time: 48±1h 实验后的盐沉积物后水冲掉 After test, salt deposit shall be removed by running water.			金属件上没有腐蚀斑点 No remarkable corrosion shall be recognized in metal part.
5.7	动作寿命 Operation life	根据下面的测试要求进行测试: Measurement shall be made following the test set forth below: (1) DC 12V, 50mA 带负载			接触电阻≤1Ω Contact resistance≤1Ω 绝缘电阻≥10MΩ Insulation Resistance≥10MΩ 触点抖动 ON-20ms max Bounce OFF-20ms max 按力: 初值的±30% Operating Force: initial value±30% Item3.3 Item4.2



Pr	oduct name	P/N	Version	Document No.	Page
Т	Cact switch	KAN1211-0431C	A/01		9/11
	项目	Ìā	、 验 条 件		要求
	ITEM TEST CONDITIONS			REQUIREMENTS	
5.8	可焊性 Solderability	在以下设定条件下进行测量: Measurements shall be made following the test set forth below: (1) 焊接温度:235±5°C Solder temperature: 235±5°C (2) 浸入时间:3s±0.5s Immersion time: 3s±0.5s			除边缘外涂层应均匀覆盖 90%以上 Except for the edge, the coating should cover a minimum 90%
	接条件: ERING CONDITIO	ONS:			
6.1	手工焊接 Hand soldering	请按以下条件进行 (1) 焊锡温度: ≤ (2) 连续焊接时间 Please practice acc (1) Soldering temp	350°C		



Pr	oduct name	P/N	Version	rsion Document No. Page		
7	Tact switch KAN1211-0431C A/				10/11	
	项目 ITEM Re			荐条件 nended conditions		
项目 Items				条件 Cond	dition	
		助焊剂附着量 Flux built-up		不附着于零部件贴装面的程度 Mounting surface should not be coated with flax 印刷电路板焊接面的周围温度 100℃ max. Ambient temperature of the soldered surface of board. 100℃ max.		
	自动浸焊	预热温度 Preheating temperature	Aml			
6.2	Conditions for Auto-dip	预热温度时间 Preheating time		60s ma	IX.	
	/tato-dip	焊接温度 Soldering temperatur	e	260°C max.		
		焊接浸渍时间 Continuous dipping time	e	5s ma	x.	
		焊接次数 Number of soldering		最多两次 2times max.		

注意事项(Notes):

a、印刷基板的焊盘尺寸参见产品图。

The pad size of the printed substrate is shown in the product diagram.

b、在使用烙铁的情况下,焊锡温度应在350℃以下、3秒以内。

In the case of using soldering iron, soldering conditions shall be 350°C max and 3 sec.max.

c、防止助焊剂从开关的顶端渗入

Prevent flux penetration from the top of the switch

d、开关浸焊后,注意不要用溶剂或类似品清洗开关。

After switches were soldered, please be careful not to clean switches with solvent or other similar products.

e、浸焊后,注意不要在顶部施加负荷。

Right after switches were soldered; please be careful not to load to on the knobs of switches.

f、注意不要施加超负荷的压力或晃动开关。


Please be cautions not to give excessive static load or shock to switches.

g、开关浸焊后,印刷基板注意不要叠放。

Please be careful not to pile up P.W.B.after switches were soldered



Product name	P/N	Version	Document No.	Page
Tact switch	KAN1211-0431C	A/01		11/11



General tolerance:	± 0.2 mm	H=4.3mm
--------------------	--------------	---------

NO.	NAME	MATERIAL	QTY.	FINISHING
1	Terminal	Brass	1	Silver plating
2	Case	PA66	1	Black
3	Contact	Phosphor bronze	1	Contact side silver plating
4	Cover	SUS	1	
5	Stem	PA66	1	Black