

### Features

- 10 $\mu$ A Ground Current at no Load
- $\pm 2\%$  Output Accuracy
- 600mA Output Current
- 10nA Disable Current ( by option )
- Wide Operating Input Voltage Range: 1.2V to 5.5V
- Dropout Voltage: 0.32V at 600mA/ V<sub>OUT</sub> 3.3V
- Support Fixed Output Voltage 1.2V, 1.5V, 1.6V, 1.8V, 2.5V, 2.8V, 3.0V, 3.3V
- Stable with Ceramic or Tantalum Capacitor
- Current Limit Protection
- Over Temperature Protection
- SOT23-5 Packages

### General Description

This production is group of low -dropout ( LDO ) voltage regulators offering the benefits of wide input voltage range from 1.2V to 5.5V, low dropout voltage, low power consumption, and miniaturized packaging. Quiescent current of only 10 $\mu$ A makes these devices ideal for powering the battery-powered, always-on systems that require very little idle-state power dissipation to a longer service life. There is an option of

### Ordering Information

**TPAP2112K-3.3TRG1**

### Applications

- Portable, Battery Powered Equipment
- Low Power Microcontrollers
- Laptop, Palmtops and PDAs
- Wireless Communication Equipment
- Audio/Video Equipment
- Car Navigation Systems

shutdown mode by selecting the parts with the EN pin and pulling it low. The shutdown current in this mode goes down to only 10nA ( typical ).

This production is of linear regulators are stable with the ceramic output capacitor over its wide input range from 1.2V to 5.5V and the entire range of output load current ( 0mA to 600mA ).

### Marking Information



**P**:Logo

XXX: Marking ID

Output voltage: 1.2=1.2V

1.8=1.8V

3.0=3.0V

3.3=3.3V

3.6=3.6V

## PIN CONFIGURATION



## Typical Application Circuit




Figure 2: Application circuit of Fixed V<sub>OUT</sub> LDO with enable function

## ABSOLUTE MAXIMUM RATINGS

VIN Pin to GND Pin Voltage .....	-0.3V to 6.5V
V <sub>OUT</sub> Pin and EN Pin Voltage .....	-0.3V to 6V
V <sub>OUT</sub> Pin to VIN Pin Voltage .....	-6V to 0.3V
Storage Temperature Range .....	-60°C~150°C
Lead Temperature (Soldering, 10 sec) .....	260°C
Junction Temperature .....	150°C
Operating Ambient Temperature Range T <sub>A</sub> .....	-40°C~85°C
Thermal Resistance Junction to Case, R <sub>θJC</sub>	SOT23-3 ..... 115°C/W SOT23-5 ..... 115°C/W DFN-4(1x1) ..... 65°C/W DFN-6(2x2) ..... 30°C/W
Thermal Resistance Junction to Ambient, R <sub>θJA</sub>	SOT23-3 ..... 250°C/W SOT23-5 ..... 250°C/W DFN-4(1x1) ..... 195°C/W DFN-6(2x2) ..... 165°C/W

**Electrical Characteristics (TA=25°C unless otherwise noted)**

(V<sub>IN</sub> =5V, V<sub>EN</sub> = 5V T<sub>A</sub>=25°C unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit	
Supply Voltage	V <sub>IN</sub>		1.2	--	5.5	V	
DC Output Voltage Accuracy		I <sub>LOAD</sub> =0.1mA	-2		2	%	
Dropout Voltage (I <sub>LOAD</sub> =600mA) (Note 3)	V <sub>DROP_3V</sub>	V <sub>OUT</sub> ≥ 3V		0.32		V	
	V <sub>DROP_2.8V</sub>	V <sub>OUT</sub> = 2.8V		0.36			
	V <sub>DROP_2.5V</sub>	V <sub>OUT</sub> = 2.5V		0.36			
	V <sub>DROP_1.8V</sub>	V <sub>OUT</sub> = 1.8V		0.57			
	V <sub>DROP_1.5V</sub>	V <sub>OUT</sub> = 1.5V		0.71			
	V	V = 1.2V		0.8			
Ground Current	I <sub>Q</sub>	I <sub>LOAD</sub> = 0mA		10		μA	
Shutdown Ground Current	I <sub>SD</sub>	V <sub>EN</sub> = 0V,		0.01	0.5	μA	
V <sub>OUT</sub> Shutdown Leakage Current	I <sub>LEAK</sub>	V <sub>OUT</sub> = 0V		0.01	0.5		
Enable Threshold Voltage	V <sub>IH</sub>	EN Rising			2	V	
	V <sub>IL</sub>	EN Falling	0.6				
EN Input Current	I <sub>EN</sub>	V <sub>EN</sub> = 5V		10	100	nA	
Line Regulation	ΔLINE	I <sub>LOAD</sub> =30mA, 1.5V ≤ V <sub>IN</sub> ≤ 5.5V or (V <sub>OUT</sub> + 0.2V) ≤ V <sub>IN</sub> ≤ 5.5V		0.2		%	
Load Regulation	ΔLOAD	10mA ≤ I <sub>LOAD</sub> ≤ 0.3A		0.2		%	
Output Current Limit	I <sub>LIM</sub>	V <sub>OUT</sub> =0	601	1100		mA	
Power Supply Rejection Ratio (I <sub>LOAD</sub> =5mA)	PSRR	V <sub>OUT</sub> =1.2V, V <sub>IN</sub> = 2V	f = 100Hz	--	80	--	dB
			f = 1kHz	--	75	--	
Output Voltage Noise (BW = 10Hz to 100kHz, C <sub>OUT</sub> =1μF,)		V <sub>IN</sub> = 3.5V	V <sub>OUT</sub> =0.9V	--	40	--	μVRMS
		I <sub>LOAD</sub> =0.1A	V <sub>OUT</sub> =2.8V	--	50	--	
Thermal Shutdown Temperature	T <sub>SD</sub>	I <sub>LOAD</sub> =10mA		--	155	--	°C
Thermal Shutdown Hysteresis	ΔT <sub>SD</sub>			--	15	--	°C
Discharge Resistance		EN = 0V , V <sub>OUT</sub> = 0.1V	--	100	--	Ω	

**Note 1.** Stresses beyond those listed “Absolute Maximum Ratings” may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions may affect device reliability.

**Note 2.**  $\theta_{JA}$  is measured at  $T_A = 25^\circ\text{C}$  on a TECH PUBLICboard.

**Note 3.**  $V_{\text{DROP}} = V_{\text{IN}} - V_{\text{OUT}}$  when the  $V_{\text{OUT}}$  is 98% of its target value.

### Typical Characteristics




Fig. 5 Output Voltage vs. Temperature




Fig. 6 Output Voltage vs. Input Voltage




Fig. 7 Output Voltage vs. Load Current




Fig. 8 Dropout Voltage vs. Temperature




Fig. 9 Ground Current vs. Input Voltage













Fig. 10 Ground Current vs. Loading Current






**BLOCK DIAGRAM**



**Package information**  
**SOT23-5**



<b>Symbol</b>	<b>Dimensions In Millimeters</b>		<b>Dimensions In Inches</b>	
	<b>Min</b>	<b>Max</b>	<b>Min</b>	<b>Max</b>
A	1.050	1.250	0.041	0.049
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.041	0.045
b	0.300	0.500	0.012	0.020
c	0.100	0.200	0.004	0.008
D	2.820	3.020	0.111	0.119
E	1.500	1.700	0.059	0.067
E1	2.650	2.950	0.104	0.116
e	0.950(BSC)		0.037(BSC)	
e1	1.800	2.000	0.071	0.079
L	0.300	0.600	0.012	0.024
θ	0°	8°	0°	8°