



VIS30039

## 30V N-Channel Power Trench MOSFET

**General Description**

- Trench Power MOSFET Technology
- Low  $R_{DS(ON)}$
- Optimized for High Reliable Switch Application
- High Current Capability
- RoHS and Halogen-Free Compliant

**Applications**


- Motor Drive
- Load Switch
- Battery Protection
- General DC/DC Converters

**Product Summary**


$V_{DS}$	30V
$I_D$ (at $V_{GS}=10V$ )	32A
$R_{DS(ON)}$ (at $V_{GS}=10V$ , typ)	3.7mΩ
$R_{DS(ON)}$ (at $V_{GS}=4.5V$ , typ)	4.9mΩ

100% UIS Tested


100% RG Tested




Top View



Top View



Bottom View



PIN1

Orderable Part Number	Package Type	Form	Minimum Order Quantity
VIS30039	DFN3.3x3.3	Tape & Reel	5000

**Absolute Maximum Ratings  $T_A=25^\circ C$  unless otherwise noted**

Parameter	Symbol	Maximum	Units
Drain-Source Voltage	$V_{DS}$	30	V
Gate-Source Voltage	$V_{GS}$	$\pm 20$	V
Continuous Drain Current (5)	$I_D$	32	A
		32	A
Pulsed Drain Current (3)	$I_{DM}$	250	A
Continuous Drain Current	$I_{DSM}$	21	A
		17	A
Avalanche Current (3)	$I_{AS}$	33.3	A
Avalanche Energy $L=0.1mH$ (3)	$E_{AS}$	55	mJ
Power Dissipation (2)	$P_D$	36	W
		13	W
Power Dissipation (1)	$P_{DSM}$	3.1	W
		1.25	W
Junction and Storage Temperature Range	$T_J, T_{STG}$	-55 to 150	°C

**Thermal Characteristics**

Parameter	Symbol	Typ	Max	Units
Maximum Junction-to-Ambient (1)	$R_{\theta JA}$	30	40	°C/W
Maximum Junction-to-Ambient (1,4)		60	75	°C/W
Maximum Junction-to-Case	$R_{\theta JC}$	2.8	3.4	°C/W



**VIS30039**

# 30V N-Channel Power Trench MOSFET

## Electrical Characteristics ( $T_J=25^\circ\text{C}$ unless otherwise noted)

Symbol	Parameter	Conditions	Min	Typ	Max	Units
<b>STATIC PARAMETERS</b>						
$\text{BV}_{\text{DSS}}$	Drain-Source Breakdown Voltage	$I_D=250\mu\text{A}, V_{GS}=0\text{V}$	30			V
$I_{\text{DSS}}$	Zero Gate Voltage Drain Current	$V_{DS}=30\text{V}, V_{GS}=0\text{V}$		1		$\mu\text{A}$
		$T_J=55^\circ\text{C}$		5		
$I_{\text{GSS}}$	Gate-Body leakage current	$V_{DS}=0\text{V}, V_{GS}=\pm 20\text{V}$			$\pm 100$	nA
$V_{GS(\text{th})}$	Gate Threshold Voltage	$V_{DS}=V_{GS}, I_D=250\mu\text{A}$	1.4	1.8	2.2	V
$R_{DS(\text{ON})}$	Static Drain-Source On-Resistance	$V_{GS}=10\text{V}, I_D=20\text{A}$		3.7	4.5	$\text{m}\Omega$
		$T_J=125^\circ$		5.3		
		$V_{GS}=4.5\text{V}, I_D=20\text{A}$		4.9	6.7	
$g_{FS}$	Forward Transconductance	$V_{DS}=5\text{V}, I_D=20\text{A}$		71		S
$V_{SD}$	Diode Forward Voltage	$I_S=1\text{A}, V_{GS}=0\text{V}$		0.71		V
$I_S$	Maximum Body-Diode Continuous Current				48	A
<b>DYNAMIC PARAMETERS</b>						
$C_{iss}$	Input Capacitance	$V_{GS}=0\text{V}, V_{DS}=15\text{V}, f=1\text{MHz}$		2366		pF
$C_{oss}$	Output Capacitance			350		pF
$C_{rss}$	Reverse Transfer Capacitance			225		pF
$R_g$	Gate resistance	$f=1\text{MHz}$		0.7		$\Omega$
<b>SWITCHING PARAMETERS</b>						
$Q_g(10\text{V})$	Total Gate Charge	$V_{GS}=10\text{V}, V_{DS}=15\text{V}, I_D=20\text{A}$		45.5		nC
$Q_g(4.5\text{V})$	Total Gate Charge			21.6		nC
$Q_{gs}$	Gate Source Charge			9.7		nC
$Q_{gd}$	Gate Drain Charge			9.4		nC
$t_{D(\text{on})}$	Turn-On Delay Time	$V_{GS}=10\text{V}, V_{DS}=15\text{V}, R_L=0.75\Omega, R_{\text{GEN}}=3\Omega$		12.3		ns
$t_r$	Turn-On Rise Time			9.4		ns
$t_{D(\text{off})}$	Turn-Off Delay Time			28.5		ns
$t_f$	Turn-Off Fall Time			9.8		ns
$t_{rr}$	Body Diode Reverse Recovery Time	$I_F=20\text{A}, di/dt=200\text{A}/\mu\text{s}$		6.8		ns
$Q_{rr}$	Body Diode Reverse Recovery Charge	$I_F=20\text{A}, di/dt=200\text{A}/\mu\text{s}$		10.2		nC
1) $R_{\text{BJA}}$ is measured with the device mounted on 1in <sup>2</sup> FR-4 board with 2oz. Copper, in a still air environment with $T_A=25^\circ\text{C}$ . The Power dissipation $P_{\text{DSM}}$ is based on $R_{\text{BJA}} \leq 10\text{s}$ and the maximum allowed junction temperature of $150^\circ\text{C}$ . The value in any given application depends on the user's specific board design. 2) The power dissipation $P_D$ is based on $T_{J(\text{MAX})}=150^\circ\text{C}$ , using junction-to-case thermal resistance, and is more useful in setting the upper dissipation limit for cases where additional heatsinking is used. 3) Single pulse width limited by junction temperature $T_{J(\text{MAX})}=150^\circ\text{C}$ . 4) $R_{\text{BJA}}$ is the sum of the thermal impedance from junction to case $R_{\text{BJC}}$ and case to ambient. 5) The maximum current rating is package limited.						



# VIS30039

## 30V N-Channel Power Trench MOSFET

### TYPICAL ELECTRICAL AND THERMAL CHARACTERISTICS




Fig 1. Typical Output Characteristics




Fig 2. Typical Transfer Characteristics




Fig 3. Normalized On-Resistance vs. Temperature




Fig 4. Typical Capacitance vs.  $V_{DS}$




Fig 5. Typical Gate Charge vs.  $V_{GS}$





Fig 6. Typical Source-Drain Diode Forward Voltage




# VIS30039

## 30V N-Channel Power Trench MOSFET


### TYPICAL ELECTRICAL AND THERMAL CHARACTERISTICS




**Fig 7.** Maximum Safe Operating Area



**Fig 8.** Maximum Drain Current vs. Case Temperature



**Fig 9.** Normalized Maximum Transient Thermal Impedance, Junction-to-Case




**Fig 10.** Normalized Maximum Transient Thermal Impedance, Junction-to-Ambient




# VIS30039

## 30V N-Channel Power Trench MOSFET


### TYPICAL ELECTRICAL AND THERMAL CHARACTERISTICS




**Fig 11.** Single Pulse Power Rating Junction-to-Case




**Fig 12.** Single Pulse Power Rating Junction-to-Ambient



**Fig 13.** Maximum Power Rating vs. Temperature



**Fig 14.** On-Resistance vs.  $V_{GS}$





**Fig 15.** On-Resistance vs. Drain Current



# VIS30039



## 30V N-Channel Power Trench MOSFET

### TEST CIRCUIT





**Fig16.** Unclamped Inductive Test Circuit

**Fig17.** Unclamped Inductive Waveform



**Fig18.** Q<sub>g</sub> Test Circuit

**Fig19.** Q<sub>g</sub> Waveform



**Fig18.** Resistive Switching Test Circuit


**Fig19.** Switching Time Waveform




# VIS30039

## 30V N-Channel Power Trench MOSFET

### TEST CIRCUIT




**Fig20.** Diode Recovery Test Circuit



**Fig21.** Diode Recovery Test Waveform

### DFN3.3x3.3 OUTLINE



DIM SYMBOL	MILLIMITERS	
	MIN [mm]	MAX [mm]
A	0.650	0.850
A1	0.152 REF	
A2	0~0.05	
D	2.900	3.100
D1	2.300	2.600
E	2.900	3.100
E1	3.150	3.450
E2	1.535	1.935
b	0.200	0.400
e	0.550	0.750
L	0.300	0.500
L1	0.180	0.480
L2	0~0.100	
L3	0~0.100	
H	0.315	0.515
θ	9°	13°