



# VIS30040

## 30V N-Channel Power Trench MOSFET

### General Description

- Trench Power MOSFET Technology
- Low  $R_{DS(ON)}$
- Optimized for High Reliable Switch Application
- High Current Capability
- RoHS and Halogen-Free Compliant

### Applications



- Motor Drive
- Load Switch
- Battery Protection
- General DC/DC Converters

### Product Summary


$V_{DS}$		30V
$I_D$	(at $V_{GS}=10V$ )	90A
$R_{DS(ON)}$	(at $V_{GS}=10V$ , typ)	4.1m $\Omega$
$R_{DS(ON)}$	(at $V_{GS}=4.5V$ , typ)	5.4m $\Omega$

100% UIS Tested

100% RG Tested



TO-252



### Orderable Part Number

VIS30040

### Package Type

TO-252

### Form

Tape & Reel

### Minimum Order Quantity

2500

### Absolute Maximum Ratings $T_A=25^\circ\text{C}$ unless otherwise noted

Parameter	Symbol	Maximum	Units
Drain-Source Voltage	$V_{DS}$	30	V
Gate-Source Voltage	$V_{GS}$	$\pm 20$	V
Continuous Drain Current <sup>(5)</sup>	$I_D$	$T_C=25^\circ\text{C}$	90
		$T_C=100^\circ\text{C}$	66
Pulsed Drain Current <sup>(3)</sup>	$I_{DM}$	230	A
Continuous Drain Current	$I_{DSM}$	$T_A=25^\circ\text{C}$	30
		$T_A=100^\circ\text{C}$	19
Avalanche Current <sup>(3)</sup>	$I_{AS}$	33.3	A
Avalanche Energy $L=0.1\text{mH}$ <sup>(3)</sup>	$E_{AS}$	55	mJ
Power Dissipation <sup>(2)</sup>	$P_D$	$T_C=25^\circ\text{C}$	83.3
		$T_C=100^\circ\text{C}$	33.3
Power Dissipation <sup>(1)</sup>	$P_{DSM}$	$T_A=25^\circ\text{C}$	6.25
		$T_A=100^\circ\text{C}$	2.5
Junction and Storage Temperature Range	$T_J, T_{STG}$	-55 to 150	$^\circ\text{C}$

### Thermal Characteristics

Parameter	Symbol	Typ	Max	Units
Maximum Junction-to-Ambient <sup>(1)</sup>	$R_{\theta JA}$	16	20	$^\circ\text{C/W}$
Maximum Junction-to-Ambient <sup>(1,4)</sup>		41	50	$^\circ\text{C/W}$
Maximum Junction-to-Case	$R_{\theta JC}$	1.2	1.5	$^\circ\text{C/W}$



# VIS30040

## 30V N-Channel Power Trench MOSFET

### Electrical Characteristics (T<sub>J</sub>=25°C unless otherwise noted)

Symbol	Parameter	Conditions	Min	Typ	Max	Units
<b>STATIC PARAMETERS</b>						
BV <sub>DSS</sub>	Drain-Source Breakdown Voltage	I <sub>D</sub> =250μA, V <sub>GS</sub> =0V	30			V
I <sub>DSS</sub>	Zero Gate Voltage Drain Current	V <sub>DS</sub> =30V, V <sub>GS</sub> =0V T <sub>J</sub> =55°C			1 5	μA
I <sub>GSS</sub>	Gate-Body leakage current	V <sub>DS</sub> =0V, V <sub>GS</sub> =±20V			±100	nA
V <sub>GS(th)</sub>	Gate Threshold Voltage	V <sub>DS</sub> =V <sub>GS</sub> , I <sub>D</sub> =250μA	1.4	1.8	2.2	V
R <sub>DS(on)</sub>	Static Drain-Source On-Resistance	V <sub>GS</sub> =10V, I <sub>D</sub> =20A T <sub>J</sub> =125° V <sub>GS</sub> =4.5V, I <sub>D</sub> =20A		4.1 5.8 5.4	4.9 7.3	mΩ
g <sub>FS</sub>	Forward Transconductance	V <sub>DS</sub> =5V, I <sub>D</sub> =20A		71		S
V <sub>SD</sub>	Diode Forward Voltage	I <sub>S</sub> =1A, V <sub>GS</sub> =0V		0.71		V
I <sub>S</sub>	Maximum Body-Diode Continuous Current				81	A
<b>DYNAMIC PARAMETERS</b>						
C <sub>iss</sub>	Input Capacitance	V <sub>GS</sub> =0V, V <sub>DS</sub> =15V, f=1MHz		2366		pF
C <sub>oss</sub>	Output Capacitance			350		pF
C <sub>rss</sub>	Reverse Transfer Capacitance			225		pF
R <sub>g</sub>	Gate resistance	f=1MHz		0.6		Ω
<b>SWITCHING PARAMETERS</b>						
Q <sub>g</sub> (10V)	Total Gate Charge	V <sub>GS</sub> =10V, V <sub>DS</sub> =15V, I <sub>D</sub> =20A		45.5		nC
Q <sub>g</sub> (4.5V)	Total Gate Charge			21.6		nC
Q <sub>gs</sub>	Gate Source Charge			9.7		nC
Q <sub>gd</sub>	Gate Drain Charge			9.4		nC
t <sub>D(on)</sub>	Turn-On Delay Time	V <sub>GS</sub> =10V, V <sub>DS</sub> =15V, R <sub>L</sub> =0.75Ω, R <sub>GEN</sub> =3Ω		12.3		ns
t <sub>r</sub>	Turn-On Rise Time			9.4		ns
t <sub>D(off)</sub>	Turn-Off Delay Time			28.5		ns
t <sub>f</sub>	Turn-Off Fall Time			9.8		ns
t <sub>rr</sub>	Body Diode Reverse Recovery Time	I <sub>F</sub> =20A, di/dt=200A/μs		6.8		ns
Q <sub>rr</sub>	Body Diode Reverse Recovery Charge	I <sub>F</sub> =20A, di/dt=200A/μs		10.2		nC

- 1) R<sub>θJA</sub> is measured with the device mounted on 1in<sup>2</sup> FR-4 board with 2oz. Copper, in a still air environment with T<sub>A</sub> =25°C. The Power dissipation P<sub>DSM</sub> is based on R<sub>θJA</sub> ≤ 10s and the maximum allowed junction temperature of 150°C. The value in any given application depends on the user's specific board design.
- 2) The power dissipation P<sub>D</sub> is based on T<sub>J(MAX)</sub>=150°C, using junction-to-case thermal resistance, and is more useful in setting the upper dissipation limit for cases where additional heatsinking is used.
- 3) Single pulse width limited by junction temperature T<sub>J(MAX)</sub>=150°C.
- 4) R<sub>θJA</sub> is the sum of the thermal impedance from junction to case R<sub>θJC</sub> and case to ambient.
- 5) The maximum current rating is package limited.



# VIS30040

## 30V N-Channel Power Trench MOSFET

### TYPICAL ELECTRICAL AND THERMAL CHARACTERISTICS




Fig 1. Typical Output Characteristics




Fig 2. Typical Transfer Characteristics




Fig 3. Normalized On-Resistance vs. Temperature




Fig 4. Typical Capacitance vs.  $V_{DS}$




Fig 5. Typical Gate Charge vs.  $V_{GS}$





Fig 6. Typical Source-Drain Diode Forward Voltage




# VIS30040

## 30V N-Channel Power Trench MOSFET


### TYPICAL ELECTRICAL AND THERMAL CHARACTERISTICS




**Fig 7. Maximum Safe Operating Area**



**Fig 8. Maximum Drain Current vs. Case Temperature**



**Fig 9. Normalized Maximum Transient Thermal Impedance, Junction-to-Case**




**Fig 10. Normalized Maximum Transient Thermal Impedance, Junction-to-Ambient**




# VIS30040

## 30V N-Channel Power Trench MOSFET


### TYPICAL ELECTRICAL AND THERMAL CHARACTERISTICS




**Fig 11.** Single Pulse Power Rating Junction-to-Case




**Fig 12.** Single Pulse Power Rating Junction-to-Ambient



**Fig 13.** Maximum Power Rating vs. Temperature




**Fig 14.** On-Resistance vs.  $V_{GS}$




**Fig 15.** On-Resistance vs. Drain Current


### TEST CIRCUIT




**Fig16.** Unclamped Inductive Test Circuit




**Fig17.** Unclamped Inductive Waveform




**Fig18.**  $Q_g$  Test Circuit



**Fig19.**  $Q_g$  Waveform



**Fig18.** Resistive Switching Test Circuit



**Fig19.** Switching Time Waveform

### TEST CIRCUIT




Fig20. Diode Recovery Test Circuit






Fig21. Diode Recovery Test Waveform

### TO-252 OUTLINE



DIM SYMBOL	MILLIMETERS	
	MIN [mm]	MAX [mm]
A	6.50	6.70
B	2.30	2.50
C	5°	
D	5.50	5.70
a1	5.20	5.40
a2	2.30	
a3	2.30	
b1	0.52	
b2	0.50	
b3	0.60	0.80
b4	1.80	2.00
L	8.80	9.20
K	7.00	7.40
d1	1.15	1.35
d2	0.45	0.85
d3	2.45	2.85