

# **KBP4005 THRU KBP410**

## **BRIDGE RECTIFIERS**

### **FEATURES**

- · UL Recognized File # E469616
- · Reliable low cost construction utilizing molded plastic technique
- · Ideal for printed circuit board
- · Low forward voltage drop
- · Low reverse leakage current
- · High surge current capability
- · Glass passivated chip junction


### **MECHANICAL DATA**

Case: Molded plastic, KBP

Epoxy: UL 94V-O rate flame retardant

Terminals: Leads solderable per MIL-STD-202,

method 208 guaranteed Mounting position: Any Weight: 0.053ounce, 1.5gram



Dimensions in inches and (millimeters)



## Maximum Ratings and Electrical Characteristics

Ratings at 25 ambient temperature unless otherwise specified.

Single phase, half wave, 60Hz, resistive or inductive load.

For capacitive load, derate current by 20%.

	Symbols	KBP4005	KBP401	KBP402	KBP404	KBP406	KBP408	KBP410	Units
Maximum Recurrent Peak Reverse Voltage	$V_{RRM}$	50	100	200	400	600	800	1000	Volts
Maximum RMS Voltage	$V_{RMS}$	35	70	140	280	420	560	700	Volts
Maximum DC Blocking Voltage	V <sub>DC</sub>	50	100	200	400	600	800	1000	Volts
Maximum Average Forward Rectified Current .375"(9.5mm) Lead Length at $T_A$ =50	I <sub>(AV)</sub>				4.0				Amp
Peak Forward Surge Current,									
8.3ms single half-sine-wave	$I_{FSM}$	I <sub>FSM</sub> 80							Amp
superimposed on rated load (JEDEC method)									
Maximum Forward Voltage at 4.0A DC and 25	$V_{\mathrm{F}}$	1.1							Volts
Maximum Reverse Current at T <sub>A</sub> =25		10.0							
at Rated DC Blocking Voltage T <sub>A</sub> =100	$I_R$		500						uAmp
Typical Junction Capacitance (Note 1)	$C_{J}$	25							pF
Typical Thermal Resistance (Note 2)	$R_{\theta JA}$	30							/W
Typical Thermal Resistance (Note 2)	$R_{\theta JL}$	11							/W
Operating and Storage Temperature Range	T <sub>J</sub> , Tstg	-55 to +150							

#### NOTES:

- 1- Measured at 1 MHz and applied reverse voltage of 4.0 VDC.
- $\hbox{2- Thermal Resistance Junction to Ambient and form junction to lead at 0.375" (9.5 mm) lead length P.C.B.\ Mounted.}$





# **BRIDGE RECTIFIERS**

## 

Fig. 1 Forward Current Derating Curve




Fig. 2 Typical Fwd Characteristics




Fig. 3 Max Non-Repetitive Peak Fwd Surge Current




Fig. 4 Typical Junction Capacitance

