



Part No	Pin	A	B	C
WAFER-PH2.0-2PWB	2	2.00	8.00	6.80
WAFER-PH2.0-3PWB	3	4.00	10.00	8.80
WAFER-PH2.0-4PWB	4	6.00	12.00	10.80
WAFER-PH2.0-5PWB	5	8.00	14.00	12.80
WAFER-PH2.0-6PWB	6	10.00	16.00	14.80
WAFER-PH2.0-7PWB	7	12.00	18.00	16.80
WAFER-PH2.0-8PWB	8	14.00	20.00	18.80
WAFER-PH2.0-9PWB	9	16.00	22.00	20.80
WAFER-PH2.0-10PWB	10	18.00	24.00	22.80
WAFER-PH2.0-11PWB	11	20.00	26.00	24.80
WAFER-PH2.0-12PWB	12	22.00	28.00	26.80
WAFER-PH2.0-13PWB	13	24.00	30.00	28.80
WAFER-PH2.0-14PWB	14	26.00	32.00	30.80
WAFER-PH2.0-15PWB	15	28.00	34.00	32.80
WAFER-PH2.0-16PWB	16	30.00	36.00	34.80

NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 2.0
- 2.Voltage Rating: 250V AC DC
- 3.Current Rating: 2A AC DC
- 4.Insulation Resistance: 800MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 500V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃

MANUFACTURE DWG			 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: WAFER 2.00 贴片	
DECIMALS:	ANGLES:	PAR	WAFER-PH2.0-NPWB	
X.:±0.2	X'.:±5°	DWN		
.X:±0.1	X.X':±3°	CHKD		
.XX:±0.05	X.XX':±1°	APVD		
CUSTOMER COPY		SCALE1:1	UNIT:MM	
		SIZE:A4	SHEET:1F1	REV:A