

N-Channel Super Junction Power MOSFET III

General Description

The series of devices use advanced trench gate super junction technology and design to provide excellent R_{DS(ON)} with low gate charge. This super junction MOSFET fits the industry's AC-DC SMPS requirements for PFC, AC/DC power conversion, and industrial power applications.


Features

- New technology for high voltage device
- Low on-resistance and low conduction losses
- ●Small package
- Ultra Low Gate Charge cause lower driving requirements
- ●100% Avalanche Tested
- ●ROHS compliant

Application

- Power factor correction (PFC)
- Switched mode power supplies(SMPS)
- Uninterruptible Power Supply (UPS)

V _{DS}	700	V
R _{DS(ON)TYP}	540	mΩ
I_D	8	A



Schematic diagram

Package Marking And Ordering Information

Device	Device Package	Marking
NCE70T540D	TO-263	NCE70T540D
NCE70T540	TO-220	NCE70T540
NCE70T540F	TO-220F	NCE70T540F







TO-263

TO-220

TO-220F

Table 1. Absolute Maximum Ratings (T_c=25℃)

Parameter	Symbol	NCE70T540D NCE70T540	NCE70T540F	Unit
Drain-Source Voltage (Vgs=0V)	V _{DS}	700		V
Gate-Source Voltage (V _{DS} =0V) AC (f>1 Hz)	V _{GS}	土	30	V
Continuous Drain Current at Tc=25°C	I _{D (DC)}	8	8*	Α
Continuous Drain Current at Tc=100°C	I _{D (DC)}	5.2	5.2*	Α
Pulsed drain current (Note 1)	I _{DM (pluse)}	32	32*	Α
Maximum Power Dissipation(Tc=25℃)	P _D	69	31.6	W
Derate above 25°C		0.55	0.25	W/°C
Single pulse avalanche energy (Note 2)	Eas	156		mJ
Avalanche current ^(Note 1)	I _{AR}	1.7		Α
Repetitive Avalanche energy , t_{AR} limited by T_{jmax} (Note 1)	E _{AR}	0.3		mJ



Parameter	Symbol	NCE70T540D NCE70T540	NCE70T540F	Unit
Drain Source voltage slope, V _{DS} ≤480 V,	dv/dt	50		V/ns
Reverse diode dv/dt, V _{DS} ≤480 V,I _{SD} <i<sub>D</i<sub>	dv/dt	15		V/ns
Operating Junction and Storage Temperature Range	T_J, T_{STG}	-55	+150	°C

^{*} limited by maximum junction temperature

Table 2. Thermal Characteristic

Parameter	Symbol	NCE70T540D NCE70T540	NCE70T540F	Unit
Thermal Resistance, Junction-to-Case (Maximum)	R _{thJC}	1.81	3.95	°C /W
Thermal Resistance, Junction-to-Ambient (Maximum)	R _{thJA}	62	80	°C /W

Table 3. Electrical Characteristics (TA=25°C unless otherwise noted)

Parameter	Symbol	Condition	Min	Тур	Max	Unit
On/off states			•	•		
Drain-Source Breakdown Voltage	BV _{DSS}	V _{GS} =0V I _D =250μA	700			V
Zero Gate Voltage Drain Current(Tc=25℃)	I _{DSS}	V _{DS} =700V,V _{GS} =0V			1	μA
Zero Gate Voltage Drain Current(Tc=125℃)	I _{DSS}	V _{DS} =700V,V _{GS} =0V			100	μA
Gate-Body Leakage Current	I _{GSS}	V _{GS} =±20V,V _{DS} =0V			±100	nA
Gate Threshold Voltage	V _{GS(th)}	V _{DS} =V _{GS} ,I _D =250μA	3		4	V
Drain-Source On-State Resistance	R _{DS(ON)}	V _{GS} =10V, I _D =4A		540	600	mΩ
Dynamic Characteristics			•			•
Input Capacitance	C _{lss}	V 50VVV 0V		590		pF
Output Capacitance	Coss	V_{DS} =50V, V_{GS} =0V, F=1.0MHz		37		pF
Reverse Transfer Capacitance	C _{rss}	F=1.UMHZ		0.9		pF
Total Gate Charge	Qg	\/ 400\/ L 0A		14.6	22	nC
Gate-Source Charge	Q _{gs}	V_{DS} =480V, I_{D} =8A, V_{GS} =10V		4		nC
Gate-Drain Charge	Q_{gd}	VGS=1UV		6.7		nC
Switching times			•			•
Turn-on Delay Time	t _{d(on)}			9		nS
Turn-on Rise Time	t _r	V_{DD} =420 V , I_{D} =4 A ,		6.5		nS
Turn-Off Delay Time	t _{d(off)}	$R_G=4.7\Omega, V_{GS}=10V$		61		nS
Turn-Off Fall Time	t _f			10		nS
Source- Drain Diode Characteristics			•			
Source-drain current(Body Diode)	I _{SD}	T -05°C			8	Α
Pulsed Source-drain current(Body Diode)	I _{SDM}	T _C =25°C			32	Α
Forward On Voltage	V _{SD}	Tj=25°C,I _{SD} =8A,V _{GS} =0V		0.9	1.2	V
Reverse Recovery Time	t _{rr}			230		nS
Reverse Recovery Charge	Q _{rr}	Tj=25°C,I _F =4A,di/dt=100A/µs		1.2		uC
Peak Reverse Recovery Current	I _{rrm}			10.5		Α

Notes 1.Repetitive Rating: Pulse width limited by maximum junction temperature

2. Tj=25°C,VDD=50V,VG=10V, R_G=25 Ω



TYPICAL ELECTRICAL AND THERMAL CHARACTERISTICS (curves)

Figure 1. Safe operating area




Figure 3. Source-Drain Diode Forward Voltage




Figure 5. Transfer characteristics




Figure 2. Safe operating area for TO-220F




Figure 4. Output characteristics




Figure 6. Static drain-source on resistance






Figure 7. R_{DS(ON)} vs Junction Temperature




Figure8. BV_{DSS} vs Junction Temperature




Figure 9. Maximum ID vs Junction Temperature




Figure 10. Capacitance




Figure 11. Gate charge waveforms




Figure 12. Transient Thermal Impedance








Figure 13. Transient Thermal Impedance for TO-220F






Test circuit


1) Gate charge test circuit & Waveform







2) Switch Time Test Circuit:


Wuxi NCE Power Co., Ltd






3) Unclamped Inductive Switching Test Circuit & Waveforms








TO-263-3L Package Information



Sumb al	Dimensions	In Millimeters	Dimensions In Inches		
Symbol	Min.	Max.	Min.	Max.	
А	4.32	4.57	0.170	0.180	
A1	-	0.25		0.010	
b	0.71	0.94	0.028	0.037	
b2	1.15	1.40	0.045	0.055	
С	0.46	0.61	0.018	0.024	
c2	1.22	1.40	0.048	0.055	
D	8.89	9.40	0.350	0.370	
D1	8.01	8.23	0.315	0.324	
Е	10.04	10.28	0.395	0.405	
E1	7.88	8.08	0.310	0.318	
е	2.54	2.54 BSC		BSC	
L	14.73	15.75	0.580	0.620	
L1	2.29	2.79	0.090	0.110	
L2	1.15	1.39	0.045	0.055	
L3	1.27	1.77	0.050	0.070	




TO-220-3L-C Package Information





Complete al	Dimensions I	n Millimeters	Dimensions In Inches		
Symbol	Min.	Max.	Min.	Max.	
А	4.400	4.600	0.173	0.181	
A1	2.250	2.550	0.089	0.100	
b	0.710	0.910	0.028	0.036	
b1	1.170	1.370	0.046	0.054	
С	0.330	0.650	0.013	0.026	
c1	1.200	1.400	0.047	0.055	
D	9.910	10.250	0.390	0.404	
E	8.9500	9.750	0.352	0.384	
E1	12.650	12.950	0.498	0.510	
е	2.540	TYP.	0.100	TYP.	
e1	4.980	5.180	0.196	0.204	
F	2.650	2.950	0.104	0.116	
Н	7.900	8.100	0.311	0.319	
h	0.000	0.300	0.000	0.012	
L	12.900	13.400	0.508	0.528	
L1	2.850	3.250	0.112	0.128	
V	7.500	REF.	0.295	REF.	
Ф	3.400	3.800	0.134	0.150	



TO-220F Package Information







Symbol	Dimensions	In Millimeters	Dimension	s In Inches	
	Min.	Max.	Min.	Max.	
Α	4.500	4.900	0.177	0.193	
A1	2.340	2.740	0.092	0.108	
A2	2.560	2.960	0.101	0.117	
b1	0.700	0.900	0.028	0.035	
b2	1.180	1.580	0.046	0.062	
С	0.400	0.600	0.016	0.024	
D	9.960	10.360	0.392	0.408	
E	15.670	15.970	0.617	0.629	
E1	6.500	6.900	0.256	0.272	
E2	15.500	16.100	0.610	0.634	
е	2.540) TYP	0.100) TYP	
Ф	3.080	3.280	0.121	0.129	
L	12.640	13.240	0.498	0.521	
L1	3.030	3.430	0.119	0.135	



ATTENTION:

- Any and all NCE products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your NCE representative nearest you before using any NCE products described or contained herein in such applications.
- NCE assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all NCE products described or contained herein.
- Specifications of any and all NCE products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- NCE Power Semiconductor CO.,LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- In the event that any or all NCE products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.
- No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of NCE Power Semiconductor CO.,LTD.
- Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production. NCE believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.
- Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the NCE product that you intend to use.
- This catalog provides information as of Mar. 2010. Specifications and information herein are subject to change without notice.